

WEATHERPROOF ROUND BOXES



Die cast aluminum round boxes with sturdy lugs for wall or ceiling mounting.

Sturdy mounting lugs for wall or ceiling mounting

Brass screws



Green hex slotted washer head ground screw in pre-tapped hole

Available with 1/2" and 3/4" holes in 4 sides and in back

Heavy, die cast aluminum

Close-up plugs allow Phillips or slotted screwdrivers for easy installation

1/8" thick weatherseal gasket is closed cell silicone rubber for long lasting seal that won't crumple or break

Thick **RAB** Gasket
Actual size

"others"

Round Box Without Cover

Die cast aluminum wiring box with weatherproof gasket, ground screw, and two sturdy lugs for wall or ceiling mounting. Supplied with four color matched close-up plugs.

Finish:

- Architectural Bronze
- Black
- White
- Natural
- Silver Gray
- Verde Green



RAB's distinctive see-thru Weatherproof packaging has all the information you need and keeps parts organized



Catalog Numbers

Box Diameter	Thread size (of side holes)
4"	1/2"
4"	3/4"
3"	1/2"
3"	3/4"

No Cover			Verde Green	
Bronze	Black	White	Natural	Green
VXCA	VXCB	VXCW	VXC	VXCVG
VXCA-3/4	VXCB-3/4	VXCW-3/4	VXC-3/4	VXCVG-3/4
				LRTC
				LRTC-3/4

Specifications

UL Listing:

Suitable for wet locations

Box Material:

Precision die cast aluminum

Gasket:

1/8" thick closed cell EPDM Foam for long lasting seal that won't crumple or break.

Thick **RAB** Gasket
Actual size

"others"

Screws:

10-24 Brass Round Head Phillips/slotted

Gasket:

1/8" thick closed cell silicone rubber

Ground Screw:

#10-24 Green corrosion protected steel slotted washer head screw provided in pre-tapped hole.

Patents:

The designs of RAB products are protected under U.S. and international intellectual property laws.


Info Online 24/7

Spec Sheets

www.rabweb.com > click "PRODUCTS"

Dimensions

4" Boxes



Round Box with Blank Cover

Die cast aluminum wiring box with weatherproof gasket, ground screw, and two sturdy lugs for wall or ceiling mounting. Die cast aluminum cover without center hole supplied with 4 brass screws.

Finish: ● Natural



Round Box with One 1/2" Cover Hole

Die cast aluminum wiring box with weatherproof gasket, ground screw, and two sturdy lugs for wall or ceiling mounting. Die cast aluminum cover with one 1/2" hole supplied with 4 brass screws.

Finish: ● Natural



Round Box with One 3/4" Cover Hole

Die cast aluminum wiring box with weatherproof gasket, ground screw, and two sturdy lugs for wall or ceiling mounting. Die cast aluminum cover with one 3/4" hole supplied with 4 brass screws.

Finish: ● Natural



Round Box with 3 1/2" Cover Holes

Die cast aluminum wiring box with weatherproof gasket, ground screw, and two sturdy lugs for wall or ceiling mounting. Die cast aluminum cover with three 1/2" holes supplied with 2 brass screws and one close-up plug.

Finish: ● Architectural Bronze
● Black
● White
● Natural
● Verde Green



Box Diameter	Thread Size	Blank Cover Natural
4"	1/2"	VXJ
4"	3/4"	VXJ-3/4
3"	1/2"	LRT4
3"	3/4"	LRT4-3/4

One 1/2" Cover Hole Natural
VXJ1
VXJ1-3/4
LRT5
LRT5-3/4

One 3/4" Cover Hole Natural
VXJ2
VXJ2-3/4

Three 1/2" Cover Holes	Verde Green
Architectural Bronze: VX3A	VX3VG
Black: VX3B	
White: VX3W	
Natural: VX3	
	LRT3
	LRT3-3/4

