


Wire Hangers | PC 5100

- 10 Gauge Steel
- Plain (Uncoated)
- Plastic Coated
- Caution! Always Wear Eye Protection

Wire Hangers are a plumbing item which are used to secure pipe or tubing transverse from wood beams.



CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
Plain						
WH124	27200	1/2 x 4"	100	500	4.38#	M
WH126	27202	1/2 x 6"	100	500	6.22#	M
WH344	27204	3/4 x 4"	100	500	4.36#	M
WH346	27206	3/4 x 6"	100	500	7.40#	M
Plastic Coated						
PC124	27208	1/2 x 4"	100	500	4.52#	M
PC126	27210	1/2 x 6"	100	500	6.20#	M
PC344	27212	3/4 x 4"	100	500	4.60#	M
PC346	27214	3/4 x 6"	100	500	6.30#	M

Hook on Clips • Hook on Straps | PC 5110, 5120

- Hook on Clips & Straps
- Formed Wire
- Supplied With Insulator
- Caution! Always Wear Eye Protection

Hook on Straps & Clips are used to secure pipe or tubing running parallel with studs. The hook on straps are nailed across two studs. The hook on clips with insulator snap into holes in the strap and tubing or pipe is then secured perpendicular to the strap.



CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
14 Gauge PC 5110						
HC50	27220	1/2" Pipe	100	1000	1.66#	M
HC75	27225	3/4" Pipe	100	1000	1.75#	M
12 Gauge PC 5120						
5818	27230	18" Length	100	100	21.08#	C
5826	27235	26" Length	100	100	30.58#	C

Plumber's Tape | PC 5130, 5140

- Galvanized Steel
- Solid Copper

Plumber's Tape is 3/4" wide and is perforated with alternating size holes to accommodate nails or bolts. It is used to strap or support pipe, ducts & other fastening applications. Copper strap also used for grounding.



CAT NO	UPC	LENGTH	GAUGE	STD	MSTR	WT/STD	UNIT
Galvanized Steel PC 5130							
PT28 *	30945	3/4 x 10'	28	100	100	35.16#	Ea
PT26 *	30940	3/4 x 10'	26	100	100	46.24#	Ea
PT22 *	30935	3/4 x 10'	22	50	50	37.64#	Ea
Solid Copper PC 5140							
CU10	27550	3/4 x 10'	23	1	10	0.58#	Ea
CU25	27555	3/4 x 25'	23	1	6	1.48#	Ea
CU50	27560	3/4 x 50'	23	1	6	2.97#	Ea

*  UPC Approved (Plumbing Code)

See new products at www.lhdottie.com

UPC Vendor ID Code: 78-1002

