

Conduit/Cable/Wire

One-Hole Strap - Jiffy Clip


•MinE® clips have an inverted rib providing more strength at the bend of the clip. Snap-on feature leaves both hands free to work.

•Pre-Galvanized Steel

MINE30



MED30



MIN-E® Series

| Catalog Number | Fits EMT | Std Pkg |
|----------------|----------|---------|
| MINE30 | 1/2" | 100 |
| MINE45 | 3/4" | 100 |
| MINE55 | 1" | 100 |

| Catalog Number | Fits Rigid | Flexible Conduit | Std Pkg |
|----------------|------------|------------------|---------|
| MINE28 | --- | 3/8" | 100 |
| MINE40 | 1/2" | 1/2" | 100 |
| MINE50 | 3/4" | 3/4" | 100 |

Parts above also available Copper Plated. Call Customer Service for pricing and minimum order quantities.

•Our best-selling precision made one-hole conduit and pipe straps

•Clips have an inverted rib providing more strength at the bend of the clip and holding the clip on the conduit, leaving both hands free to work.

•Both zinc plated steel and stainless steel Medium Jiffy Clips are available.

MEDIUM Series

| Catalog Number | Zinc Plated Steel | | Std Pkg |
|----------------|-------------------|----------------|---------|
| | Fits EMT | Fits Rigid/IMC | |
| MED30 | 1/2" | --- | 100 |
| MED40 | --- | 1/2" | 100 |
| MED45 | 3/4" | --- | 100 |
| MED50 | --- | 3/4" | 100 |
| MED55 | 1" | --- | 100 |
| MED60 | --- | 1" | 100 |
| MED65 | 1-1/4" | --- | 100 |
| MED70 | --- | 1-1/4" | 100 |
| MED75 | 1-1/2" | --- | 50 |
| MED80 | --- | 1-1/2" | 50 |
| MED85 | 2" | --- | 50 |
| MED90 | --- | 2" | 50 |

| Catalog Number | STAINLESS STEEL | | Std Pkg |
|----------------|-----------------|----------------|---------|
| | Fits EMT | Fits Rigid/IMC | |
| MED30SS | 1/2" | --- | 100 |
| MED40SS | --- | 1/2" | 100 |
| MED45SS | 3/4" | --- | 100 |
| MED50SS | 3/4" | 3/4" | 100 |
| MED55SS | 1" | --- | 100 |
| MED60SS | --- | 1" | 100 |
| MED70SS | --- | 1-1/4" | 100 |
| MED80SS | --- | 1-1/2" | 50 |
| MED90SS | --- | 2" | 50 |

Also available hot dip galvanized steel. Call Customer Service for pricing and minimum order quantities.