

Field Modification Kits

Pilot Lights

Selection

	Class	Enclosure Type	Controller Size or (Lighting Rating)	Lens Color(s)	Legend(s)	Voltage	Catalog Number	List Price \$
 49SBLBF	14, 40, 22, ^② 43, ^② 30 (2S2W), ^③ LEN, CLM	1	00-4 or (20-200A)	Red, Green, Amber	ON, RUN, OFF ^① , OL TRIPPED, FORWARD, REVERSE, LOW, HIGH	24 Vac	49SBLBJ	
						120 Vac	49SBLBF	
						208/240/277 Vac	49SBLBG	
						480 Vac	49SBLBH	
						600 Vac	49SBLBE	
		1	5-6 or (300-400A)	Red (Transformer Type)	ON	24 Vac (Full Voltage)	49SPL0BRJ	
						120 Vac	49SPL0BRF	
						240 Vac	49SPL0BRG	
						480 Vac	49SPL0BRH	
						600 Vac	49SPL0BRE	
		12, 4/4X	0-6 ^③ or (20-400A)	Green (Transformer Type)	OFF ^④	24 Vac (Full Voltage)	49SPL0AGJ	
						120 Vac	49SPL0AGF	
						240 Vac	49SPL0AGG	
						480 Vac	49SPL0AGH	
						600 Vac	49SPL0AGE	
	30 (2S1W) ^②	1	0-1 3/4	Red, Green, Amber	ON, RUN, OFF ^① , OL TRIPPED, FORWARD, REVERSE, LOW, HIGH	24 Vac	49SBLBJ	
						120 Vac	49SBLBF	
						208/240/277 Vac	49SBLBG	
						480 Vac	49SBLBH	
						600 Vac	49SBLBE	
		1	2-4	Red (Transformer Type)	ON	24 Vac (Full Voltage)	49SPL0BRJ	
						120 Vac	49SPL0BRF	
						240 Vac	49SPL0BRG	
						480 Vac	49SPL0BRH	
						600 Vac	49SPL0BRE	
		12, 4/4X	0-4	Green (Transformer Type)	OFF ^④	24 Vac (Full Voltage)	49SPL0AGJ	
						120 Vac	49SPL0AGF	
						240 Vac	49SPL0AGG	
						480 Vac	49SPL0AGH	
						600 Vac	49SPL0AGE	
 49SPL0BRF	17, 18, 25, ^② 26, ^② 32, ^② 36, 37, 70, 71, LED, LEF, LEB, CMN, CMF, CMB	1	0-6 (20-400A)	Red ^② (Transformer Type)	ON	24 Vac (Full Voltage)	49SPL0BRJ	
						120 Vac	49SPL0BRF	
						240 Vac	49SPL0BRG	
						480 Vac	49SPL0BRH	
						600 Vac	49SPL0BRE	
				Green (Transformer Type)	OFF ^④	24 Vac (Full Voltage)	49SPL0AGJ	
						120 Vac	49SPL0AGF	
						240 Vac	49SPL0AGG	
						480 Vac	49SPL0AGH	
						600 Vac	49SPL0AGE	
						24 Vac (Full Voltage)	49SPL0AGJ	
						120 Vac	49SPL0AGF	
						240 Vac	49SPL0AGG	
						480 Vac	49SPL0AGH	
						600 Vac	49SPL0AGE	
 49SBLBL	Lens Kit ONLY (30 (2S1W)) (14, 40, 22, 43, 30 (2S2W), LEN, CLM)	1	0-1 3/4 00-4 or (20-200A)	Red, Green, Amber	—	—	49SBLBL	

① "Off" PL requires: (1) N.C. aux contact, 49AB01 "OL" TRIPPED" PL requires: For ESP 100OL, (1) N.O. OLaux. contact, 49ASNO. For amb. Comp. Bimetal OL, use CL. 14 starter with the "91" suffix or change the OL to 48DC39AA3.

② Class 22, 43, 25, 26, 30 & 32 requires qty. of (2) pilot light kits. Select appropriate legend plate as a separate item per type of starter; either "FORWARD" & "REVERSE" or "LOW" & "HIGH".

③ 2S2W is starter Size 0-4.

④ Includes NC aux contact for NEMA starter Size 0-4.