

Cover Finishes

Elegant hand-mitered edging on covers blend with any decor or color combination. For use with virtually all choices of floor covering.



Available in brass, aluminum or painted edging to compliment floor covering.



The new U-Access cover design features a handle to easily lift the cover. All corner fasteners have been removed.


See a larger view at bit.ly/1aKZzT6 or scan this QR Code

Back Boxes

The steel construction makes FSR back boxes extremely sturdy. They are your solution for power, audio, video, telecommunications and data.

FL-500P, 540P, 600P and 640P have reconfigurable internal brackets. 6" and deeper back boxes also have cable "pass-through" capability.

LITE-it add it to every box!



Model #	FL-200	FL-500P (*)	FL-540P	FL-600P (*)
Size:	8 3/4" X 6"	10" X 12"	10" X 12"	13.5" X 12"
Depth:	3", 4"	2-1/4", 3", 4", 6", 8", 10"	4", 6", 8", 10"	3", 4", 6", 8", 10"
Cover Size:	8 3/4" X 6" X 1/8"	10-1/2" X 12-1/2" X 1/8"	10-1/2" X 12-1/2" X 1/8"	14" X 12-1/2" X 1/8"
Knockouts:	8 total, either 1" and 1-1/4"	12 total, either 1" and 1-1/4"	8 total either 1" and 1-1/4"	2 Sloping field transformable
Brackets:	1 Sloping field transformable, 1 Sloping Decora Opening	2 Sloping field transformable	2 Sloping field transformable	14 total either 1" and 1-1/4"
Floor Type:	Concrete	Concrete	Raised access, stage & computer floors	Concrete



Model #	FL-640P	FL-700 (*)	FL-710 (*)	FL-2000
Size:	13.5" X 12"	8" X 14"	8" X 9"	10" X 12"
Depth:	4", 6", 8", 10"	5-1/4"	5-1/4"	6"
Cover Size:	14" X 12-1/2" X 1/8"	8" X 14" X 1/8"	8" X 9" X 1/8"	10-1/2" X 12-1/2"
Knockouts:	14 either 1" and 1-1/4"	6 either 1/2" and 3/4"	6 either 1/2" and 3/4"	2 total in AC section: 1 rear either 1/2" and 3/4"
Brackets:	2 Sloping field transformable	1 Sloping	1 Sloping	4 total in AV section: 3 rear and 1 right side either 1" and 1-1/4"
Floor Type:	Raised access, stage & computer floors	Concrete	Concrete	1 Sloping

Pour Pan

The FSR Pour Pan is the answer to Floor Box installations that are on grade. If your application is a poured concrete floor and the box rests on soil, rock or gravel, you must first install the Pour Pan.



Touchboards
 205 Westwood Ave, Long Branch, NJ 07740
 Phone: 908-94 BOARDS (26273) | (732)-222-1511
 Fax: (732)-222-7088 | E-mail: sales@touchboards.com


Fire-Resistant Floor Box Solutions

NEW

Our Fire-Resistant floor solutions expand the versatility of our floor box line by providing enhanced, fire-resistant versions of our existing products.

The Fire-Resistant Kit is offered in two sizes: the FL-500P-6-FRK and FL-605P-6-FRK. Both models include a UL listed 3-hour Fire-Resistant Floor Box system comprised of a FireStop box, and four FL-FRK 1 1/2" Intumescent-lined Conduit Assemblies, hardware and installation instructions. A temporary construction cover is included to protect the floor box's interior during installation. Order your finished cover separately.

Watch the video at bit.ly/1j7yT0Z or scan this QR code



SmartFit™ (Poke-Thru)

It's Not Just Power Anymore

FSR SmartFit is an innovative system that provides flexible power and AV solutions for fire rated Poke-Thrus'. The SmartFit system features a universal cover assembly and multiple sub-plates that install in the fire rated Poke-Thrus' and are now available in 4", 6", and 8" sizes.

The system offers three architectural finishes: Aluminum, Brass, and Black, providing an attractive appearance with superior durability.

With the SmartFit system, FSR delivers one consistent look for installations with power and audio/video requirements. There are sub-plates available in the SmartFit line, including a Dual Decora and 3-IPS-insert sub-plate.

Buy American Compliant
FIRE RATED



The FLH20 "Super" Floor Box

The FLH20 High Load Capacity Floor Box combines rugged construction and elegant design for carpeted and non-carpeted floors.

Perfect for ballrooms, convention spaces, and high traffic areas where heavy equipment such as forklifts, automobiles, scissor lifts, and portable stages are used.



U.S. PAT. 7,989,710

Compartment Dividers:
Remove or arrange as needed to isolate compartments.

Center Dividers:
Remove to run cables across compartments.

Field Configurable Interior



Raised Floor Boxes

The all metal construction provides one or two cable access doors, or a solid metal cover.

FSR's Raised Access Floor Boxes are designed to handle a variety of connections and applications.

The RFL Series of Floor Boxes is available in many sizes and depths. The all-metal construction is built to handle the rigors of a floor environment, yet blends into the floor pattern.

The beveled steel carpet rim is available standard in gray, black or clay. We will provide custom finishes to match your design. Covers are available with one or two access doors, or a solid metal cover.



The RFL-AVs

Stage Boxes

One piece all welded design providing both strength and ease of installation. Cover is painted with Sandtex for a non-skid finish, available in black or oak.



Model #	FP-2-BLK	FL-1200	FL-1300	FL-1500
Size:	7-3/4" X 5-3/4"	3-3/8" X 4-5/8"	5-1/8" X 7-1/8"	11 7/8" X 8"
Depth:	4-3/4"	4-1/2"	4-7/8"	6"
Cover Size:	7-3/4 X 5-3/4" X 1/8"	4-3/4 X 6" X 1/8"	6-1/8" X 8-1/2" X 1/8"	13-1/2" X 9-1/2" X 3/16"
Knockouts:	Open area for a two gang box. (Customer supplied)	1 rear either 1/2" and 3/4" 1 bottom either 1/2" and 3/4" 1 Sloping	2 rear concentric either 1/2" and 3/4" 1 bottom concentric either 1/2" and 3/4" 1 each left and right sides concentric 1/2" and 3/4"	4 rear either 1" and 1-1/4", 4 bottom either 1" and 1-1/4"
Brackets:	1 Sloping	1 Sloping	1 Sloping	1 Sloping
Floor Type:	Raised access, stage & computer floors	Raised access, stage & computer floors	Raised access, stage & computer floors	Wood or linoleum over raised access, stage & computer floors

New UL Requirements

UL has added a new requirement for UL listing. Boxes to be installed in concrete must pass a "scrub water" test. FSR passed the test and exceeded the specs. Our boxes are approved, not only for carpet over concrete, but wood and tile as well. This requirement is only for boxes in concrete, it is not required for raised access or stage floors.

LITE-it

NEW



LITE-it easily provides lighting in floor, wall and ceiling boxes, or anywhere a work light is needed. LITE-it can be used with all our Core Solutions. Add LITE-it to every box!

Look for this symbol to see where LITE-it can be installed.

