


HR-3LED-R22D

3.5" Tesla™ Remodel Housing

Non-IC

WAC LIGHTING

Responsible Lighting®



Fixture Type:

Catalog Number:

Project: _____

Location: _____

PRODUCT DESCRIPTION

Non-IC, remodel housing.
For use with HR-3LED Tesla 3.5" series trims.

FEATURES

- Provided with push-in wire connector for easy installation
- 5 year WAC Lighting product warranty

SPECIFICATIONS

Construction: Housing and junction box are 20 gauge steel

J-Box: Three knockouts for ease of installation. Rated for branch wiring.

Driver: Electronic driver, 120 - 277VAC input, 21.5W output.
Power factor >0.9 Dimming with thermal protection.

Mounting: Accommodates surface thickness 1/2"-2"
4 5/8" cutout hole.

Dimming: 0-10V Dimming: 100%-10%
ELV Dimming: 100%-15% (120V only)

Standards: Non-IC - insulation must be kept at least 3" away from the housing
ETL & cETL Listed.

ORDER NUMBER

HR-3LED-R22D

*Remodel
Non-IC*

COMPATIBLE TRIMS See trim spec sheets for complete order number and specifications.

Tesla Pro 3.5"

HR3LD-ET118P Series <i>Round, High Brightness Wet Location Listed Energy Star®</i>	HR3LEDT718P Series <i>Square, Open Reflector Energy Star®</i>
HR3LEDT118P Series <i>Round, Downlight Energy Star®</i>	HR3LEDT518P Series <i>Square, 0°- 30° Adjustable Energy Star®</i>
HR3LEDT318P Series <i>Round, 0°- 30° Adjustable Energy Star®</i>	HR3LEDT918P Series <i>Square, 30°- 45° Adjustable Energy Star®</i>
HR3LEDT418P Series <i>Round, 30°- 45° Adjustable Energy Star®</i>	HR3LEDT818P Series <i>Square, Shower Light Wet Location Listed Energy Star®</i>
HR3LEDT218P Series <i>Round, Shower Light Wet Location Listed Energy Star®</i>	

Tesla 3.5"

HR-3LD-ET118 Series <i>Round, High Brightness Energy Star®</i>	HR-3LED-T218 Series <i>Round, Shower Light Wet Location Listed</i>
HR-3LED-T118 Series <i>Round, Open Reflector</i>	HR-3LED-T718 Series <i>Square, Open Reflector</i>
HR-3LED-T318 Series <i>Round, 0°- 30° Adjustable</i>	HR-3LED-T818 Series <i>Square, Shower Light Wet Location Listed</i>
HR-3LED-T618 <i>Round, Pin Hole 0°- 30° Adjustable</i>	HR-3LED-T518 Series <i>Square, 0°- 30° Adjustable</i>
HR-3LED-T418 Series <i>Round, 30°- 45° Adjustable</i>	HR-3LED-T918 Series <i>Square, 30°- 45° Adjustable</i>

wacighting.com

Phone (800) 526.2588

Fax (800) 526.2585

Headquarters/Eastern Distribution Center

44 Harbor Park Drive

Port Washington, NY 11050

Central Distribution Center

1600 Distribution Ct

Lithia Springs, GA 30122

Western Distribution Center

1750 Archibald Avenue

Ontario, CA 91760