


SOURCE I® SERVICE FITTINGS



Source I® Series Flush Activations offer a wide variety of single and dual service power and communications for infloor raceways in both new construction and renovations.

CODE REFERENCE


cULus Listed Underfloor Raceway Fittings:

File E11912, Guide RQKX

Meets Article 390 of NEC


Source 1 Series Service Fittings Ordering Information

S175 Double Duplex Power Activation




Double duplex polycarbonate assembly, 7/8" to 3 3/8" [22.2mm to 86mm] concrete topping. 15A, 125V receptacles included. Available in black (S175BLK) or brown (S175BRN).

S166 Complete Flush Activation




Flush polycarbonate communication slides black (S166BLK) or brown (S166BRN).

S165 Complete Flush Activation




Flush polycarbonate power – single duplex black (S165BLK) or brown (S165BRN). 15A, 125V receptacles included.

S166B Complete Flush Activation




Flush brass communication (slides). Used for data cable pass-through.

S165B Complete Flush Activation



Flush brass power – single duplex flip lids. May be used with 106 type adapters for data applications.

S124 Carpet Flange



Flush polycarbonate carpet flange only with mounting screws. Black (S124BLK) or brown (S124BRN).


COLOR OPTIONS




Source I® Series Service Fittings are available in brass, brown polycarbonate or black as indicated in the part number description.

SOURCE I® SERVICE FITTINGS


Source 1 Series Service Fittings Ordering Information (continued)

S124B Carpet Flange


Flush brass carpet flange only with mounting screws.

S125B Cover Plate


Flush brass power cover plate only (flip lid) with four mounting screws.

S125 Cover Plate


Nonmetallic double duplex membrane cover plate. Available in black (S125BLK) or brown (S125BRN).

S130 Cover Plate


Nonmetallic double duplex membrane cover plate. Available in black (S130BLK) or brown (S130BRN).

829PSTC Cover Plate


Flush polycarbonate communication cover plate with slides and four mounting screws. Black (829PSTC-BLK) or brown (829PSTC-BRN).

829STC Cover Plate


Flush brass communication cover plate with slides and four mounting screws.

829CK Cover Plate


Flush brass communication cover plate (2 5/8" and 2 1/4" diameter trade size screw plugs) with four mounting screws.

829CK-3/4 Cover Plate


Flush brass communication cover plate (2 5/8" and 3/4" diameter trade size screw plugs) with four mounting screws.

829CK-1 Cover Plate

Flush brass communication cover plate (2 5/8" and 1" diameter trade size screw plugs) with four mounting screws.

829CK-1/2 Cover Plate

Flush brass communication cover plate (2 5/8" and 1/2" diameter trade size screw plugs) with four mounting screws.

828SPTC Cover Plate

Flush brass communication cover plate. 1 1/2" diameter trade size screw plugs.

437 Attaching Rings

Attaching Rings for Source I (Preset or Afterset) zinc die-cast. 4" [102mm] O.D. Add suffix to Cat. No. to indicate ring depth: 7/8", 1 1/8", 1 1/2", 2", 2 3/8", or 3 1/8".