- 105° C
- Snap In
- Reusable

Nylon KO bushings are snapped into punched holes in panels to protect wires from the rough edges.



CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
1210D 1211D 1212D 1213D	12100 12110 12120 12130	1/2" 3/4" 1" 1-1/4"	100 100 100 50	1000 1000 1000 500	0.45# 0.66# 0.99# 0.70#	CCCC
1214D 1215D 1216D	12140 12150 12160	1-1/2" 2" 2-1/2"	25 25 25	250 250 250	0.46# 0.93# 1.20#	C C

K.O. Seals | PC 5440

- Snap In
- Steel
- Zinc Plated

Snap in K.O. seals are used to seal up holes punched in panels or knockouts from outlet boxes. They are held in place by spring tension. Available in sizes from 1/2" thru 2".



CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
KO50	16000	1/2"	100	1000	1.44#	С
KO75	16010	3/4"	100	1000	1.62#	č
KO100	16020	1"	100	500	2.10#	С
KO125	16030	1-1/4"	50	100	1.45#	С
KO150	16040	1-1/2"	50	50	2.14#	С
KO200	16050	2"	25	25	1.44#	С

3 Piece K.O. Seals | PC 5450

- Assembled*
- Includes Screw and Threaded Strap
- Steel
- Zinc Plated

Three piece K.O. seals are used to seal up holes punched in panels or knockouts from outlet boxes, They are held in place by a screw inserted through the seal into a threaded strap on the opposite side of the opening. Available in sizes from 1/2" thru 6". 3 piece K.O. seals are embossed to centralize in knockout. Installs from the inside or outside of any box without disarranging wires. One screw secures unit. Size is stamped into seal.



CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
D10S* D20S*	10240 10242	1/2" 3/4"	100 50	100 50	2.62# 1.73#	C
D30S* D40S D50S	10244 10246 10248	1-1/4" 1-1/2"	25 25 10	25 25 10	1.33# 1.74# 1.03#	CC
D60S D70S D80S	10250 10252 10254	2" 2-1/2" 3"	10 10 10	10 10 10	1.46# 2.16# 3.11#	CCC
D90S D100S D110S	10256 10258 10260	3-1/2" 4" 4-1/2"	10 10 10	10 10 10	3.97# 5.81# 10.45#	CCC
D120S D130S	10262 10264	5" 6"	10 10	10 10	13.33# 14.10#	C C

