



Eaton's Arrow Hart
0-10V dimmers

Arrow Hart

Eaton's 0-10V dimming solutions

Compatible with 0-10V dimmable LED
& Fluorescent ballasts



Powering Business Worldwide

Eaton's Arrow Hart 0-10V dimmers



DF10P



SF10P

Decorator & Slide Dimmers

Product description

Single pole & 3-Way
1200W @ 120V/AC
1600W @ 277V/AC
0-10VDC with integrated ON/OFF switch

Design features

- Preset feature allows user to return to previous light level when turning lights ON
- Integrated full-slide control for easy, precise operation
- Can be wired as single-pole or 3-Way
- Neutral is not required for installation of device
- Adjustable high-level trim setting for optimal lamp compatibility
- Decorator dimmers have removable faceplates to allow for color changes and each package includes three colors
- Color change kits (DF10P only)
- Compatible with dimmable LED and Fluorescent 0-10V ballasts
- Compatible with any decorator wallplate or screwless decorator wallplate

Decorator dimmers

Catalog No.	Description	Compatible Lamp Types	Rating Watt	V/AC	Color Suffix
<input type="checkbox"/> DF10P-__	Decorator dimmer Single pole/3-Way preset	0-10VDC LED/FLR	1200 1600	120 277	C1, C2, C4, C5
<input type="checkbox"/> DCK1-__	Color change faceplate for DF10P	—	—	—	A, B, BK, GY, LA, V, W

Slide dimmers

Catalog No.	Description	Compatible Lamp Types	Rating Watt	V/AC	Color Suffix
<input type="checkbox"/> SF10P-__	Slide dimmer Single pole/ 3-Way preset	0-10VDC LED/FLR	1200 1600	120 277	A, B, BK, GY, LA, V, W

Color ordering information

For ordering devices, include Catalog no. followed by the color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C1 (Color Change Kit: A, W, V), C2 (Color Change Kit: LA, W, V), C4 (Color Change Kit: BK, W, V), C5 (Color Change Kit: BK, W, GY),

A	B	BK	GY	LA	V	W					
(Almond)	(Brown)	(Black)	(Gray)	(Light Almond)	(Ivory)	(White)					
C1 Color Kit			C2 Color Kit			C4 Color Kit			C5 Color Kit		
A (Almond), W (White), V (Ivory)			LA (Light Almond), W (White), V (Ivory)			BK (Black), W (White), V (Ivory)			BK (Black), W (White), GY (Gray)		

Compliances, specifications and availability are subject to change without notice.



Powering Business Worldwide

Eaton's Arrow Hart 0-10V dimmers



OS10D7

Occupancy & Vacancy Dimmer Sensor

Product description

Single pole & 3-Way
10A @ 120V/AC
8A @ 277V/AC
0-10VDC **FLR** and **LED** ballasts

Design features

- 3 in 1 device combining dimming, switching and motion sensing
- Digital PIR sensor for occupancy (Auto ON/Auto OFF) and vacancy (Manual ON/Auto OFF) sensing
- Provides 180 degree field of view and 1000 sq. ft. of major motion coverage
- Full-range Preset dimming control provided with horizontal dim/bright bar
- Green LED indicates motion detection
- Selectable ambient light override in occupancy sensor models
- Selectable time delay of 15 seconds (Test mode, changes to 2 minutes after 2 minutes of powering up), 5 minutes (factory default), 15 minutes and 20 minutes
- Occupancy Sensor version can be toggled between Auto ON/Auto OFF or Manual ON/Auto OFF
- Vacancy sensor meets California Title 20 (VS10D7 only)
- Compatible with any decorator wallplate or screwless decorator wallplate
- Neutral required for installation of device
- California Title 20 compliant

Occupancy & vacancy dimmer sensor

Catalog No.	Description	Compatible Lamp Types	Rating Watt	V/AC	Color Suffix
<input type="checkbox"/> OS10D7__	Occupancy sensor & dimmer with LED Single pole/3-Way preset	0-10VDC LED/FLR	1200	120	BK, GY, LA, V, W
<input type="checkbox"/> VS10D7__	Vacancy sensor & dimmer with LED Single pole/3-Way preset	0-10VDC LED/FLR	1200	120	BK, GY, LA, V, W

Color ordering information

For ordering devices, include Catalog no. followed by the color suffix:
BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)

BK	GY	LA	V	W
(Black)	(Gray)	(Light Almond)	(Ivory)	(White)

Compliances, specifications and availability are subject to change without notice.

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Eaton.com/arrowhart

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Eaton.com/arrowhart

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlán Km 17.8 s/n
Col. Villa Jardín esq.
Cerrada 8 de Mayo
Cuautitlán, Mexico CP 54800
México
Eaton.mx
Eaton.com/arrowhart