

## Ground Clamps With Hubs | PC 5560



Grounding clamps with hubs are used to connect grounding conductor in conduit to water pipe for grounding. Cast from high strength, highly conductive copper alloy with steel or bronze screws.

- UL Listed
- Bronze
- With 1/2", 3/4" or 1" Hubs

CAT NO	UPC	PHOTO	WIRE RANGE	HUB SIZE	PIPE SIZE	STD	MSTR	WT/STD	UNIT
29L	10051	E	10-6	1/2"	1/2 to 1"	25	125	9.80#	C
29BRZ	10054	E	10-6	1/2"	1/2 to 1"	25	125	10.06#	C
30L	10053	D	10-2/0	3/4"	1/2 to 1"	25	125	11.35#	C
31L	10056	D	10-3/0	1"	1/2 to 1"	25	125	12.33#	C
270L	10057	E	10-6	1/2"	1-1/4 to 2"	25	25	14.87#	C
271L	10059	D	10-2/0	3/4"	1-1/4 to 2"	25	25	16.63#	C
272L	10061	D	10-3/0	1"	1-1/4 to 2"	25	25	17.44#	C
280L	10063	E	10-6	1/2"	2-1/2 to 4"	5	5	6.23#	C
281L	10064	D	10-2/0	3/4"	2-1/2 to 4"	5	5	6.63#	C
282L	10066	D	10-3/0	1"	2-1/2 to 4"	5	5	6.64#	C

All clamps provided with steel screws except 29BRZ (bronze screws)

## Ground Rod Clamps | PC 5570



Ground rod clamps are used to connect conductor to a driven ground rod. Cast from high strength, highly conductive copper alloy, they are approved for direct burial in ground and concrete and are assembled with a bronze hex head bolt.

- UL Listed
- Direct Burial
- Bronze
- With Bronze Hex Head Bolt

CAT NO	UPC	SIZE	GROUND WIRE	STD	MSTR	WT/STD	UNIT
GR12	10500	1/2"	10 Sol to 2 Str	50	250	8.83#	C
GR58	10505	5/8"	10 Sol to 2 Str	50	250	4.65#	C
GR34	10510	3/4"	10 Sol to 2 Str	25	100	2.96#	C

## Ground Rod Clamps / Universal | PC 5570



Universal Ground Rod Clamp is UL Listed for all sizes of Ground Rods constructed of Bronze Alloy and a High Performance Stainless Steel. Bolt for direct Burial in Earth or Concrete.

- UL Listed
- Direct Burial
- Bronze
- One Size Fits All

CAT NO	UPC	ROD SIZES	WIRE RANGE	STD	MSTR	WT/STD	UNIT
UGRC	16450	3/8" 1/2" 5/8" 3/4"	10 Sol - 1/0 Str 10 Sol - 1/0 Str 10 Sol - 1/0 Str 8 Sol - 1/0 Str	50	250	4.65#	C

## Hubs | PC 5580



Hubs are used with ground clamps to connect rigid conduit to water pipe for grounding. 360° swing type hub provides flexibility. They are cast from high strength, highly conductive copper alloy with zinc plated screws.

- UL Listed
- Bronze

CAT NO	UPC	SIZE	PHOTO	GROUND WIRE	STD	MSTR	WT/STD	UNIT
HUB50L	10171	1/2"	F	10 Sol to 6 Str	25	250	5.04#	C
HUB75L	10176	3/4"	G	10 Sol to 2/0 Str	25	250	7.23#	C
HUB100L	10181	1"	G	10 Sol to 3/0 Str	10	100	3.00#	C

To Order: Phone (323) 725-1000 / Fax (323) 721-0000

