

Plug Into Safety® with Tamper-Resistant (TR) Receptacles



A full line of products to meet your every need.

Child safety is a priority at Leviton and that's why we offer our entire line of receptacles in Tamper-Resistant (TR) models. The National Electrical Code® requires TR Receptacles in new or renovated housing, childcare facilities, guest rooms and suites, and when replacing existing receptacles in required locations. TR devices have a shutter mechanism inside the receptacle that blocks access to the contacts from most foreign objects. Leviton leads the way in safety advances with a wide range of tamper-resistant devices in Residential, Commercial, Hospital and Industrial Grades.

Applications

- New or renovated single- and multi-family housing
- Schools, libraries, childcare and healthcare facilities
- Guest rooms and guest suites



Features and Benefits

- Shutter mechanism inside the receptacle blocks access to the contacts unless a two- or three-prong plug is inserted, helping ensure hairpins, keys, etc., will be locked out
- TR Symbol on the strap or body of device meets NEC requirement
- Selection includes Residential, Commercial, Hospital and Industrial Grade receptacles
- Heavy-duty construction offers long, trouble-free service life

Agency Certifications TR Receptacles

- UL/CULus
 - GFCI (File# E-48380)
 - AFCI (File# E-342815)
 - Dual Function AFCI/GFCI (File# E-480630)
 - Combination (File# E-7458)
 - Weather-Resistant (File# E-13399)
- CSA/cCSAus (File# 152105)
 - TR Receptacles
 - GFCI, AFCI Receptacles
 - USB Receptacles

SmartlockPro® GFCI and AFCI Duplex Receptacles

RATING		Residential Grade		Commercial Grade		Hospital Grade		Industrial Grade	
		15-125V	20-125V	15-125V	20-125V	15-125V	20-125V	15-125V	20-125V
Description	Color	Catalog Numbers							
Decora Duplex GFCI Receptacle Self-Grounding	White Ivory Lt Almond Gray Black Brown Red			GFTR1-W GFTR1-I GFTR1-T GFTR1-GY GFTR1-E GFTR1	GFTR2-W GFTR2-I GFTR2-T GFTR2-GY GFTR2-E GFTR2	GFTR1-HGW GFTR1-HGI GFTR1-HGT GFTR1-HGG GFTR1-HGE GFTR1-HG GFTR1-HGR	GFTR2-HGW GFTR2-HGI GFTR2-HGT GFTR2-HGG GFTR2-HGE GFTR2-HG GFTR2-HGR		
Decora Duplex GFCI Receptacle NAFTA Compliant Self-Grounding	White Ivory Lt Almond Gray Black Brown Red			GFTR1-FW GFTR1-FI - - - -	GFTR2-FW GFTR2-FI - - - -	GFTR1-HFW GFTR1-HFI GFTR1-HFT GFTR1-HFG GFTR1-HFE GFTR1-HF GFTR1-HFR	GFTR2-HFW GFTR2-HFI GFTR2-HFT GFTR2-HFG GFTR2-HFE GFTR2-HF GFTR2-HFR		
Decora Duplex GFCI Receptacle with Isolated Ground Self-Grounding	Orange							GFTR1-IGO - -	GFTR2-IGO - -
Decora Duplex GFCI Receptacle with Pilot Light Self-Grounding	White Ivory Lt Almond Gray Black Brown Red							GFPL1-PLW GFPL1-PLI GFPL1-PLT GFPL1-PLG GFPL1-PLE GFPL1-PL GFPL1-PLR	GFPL2-PLW GFPL2-PLI GFPL2-PLT GFPL2-PLG GFPL2-PLE GFPL2-PL GFPL2-PLR
Decora Duplex GFCI Receptacle with Audible Trip Alert Self-Grounding	White Ivory Lt Almond			GFTA1-W GFTA1-I GFTA1-T	GFTA2-W GFTA2-I GFTA2-T				
Decora Duplex GFCI Receptacle with LED Guide Light Self-Grounding	White Ivory Lt Almond Gray Black Brown Red			GFNL1-W GFNL1-I GFNL1-T - GFNL1-E -	GFNL2-W GFNL2-I GFNL2-T - - -	GFNL1-HGW GFNL1-HGI GFNL1-HGT GFNL1-HGG GFNL1-HGE GFNL1-HG GFNL1-HGR	GFNL2-HGW GFNL2-HGI GFNL2-HGT GFNL2-HGG GFNL2-HGE GFNL2-HG GFNL2-HGR		
Decora Weather-Resistant Duplex GFCI Receptacle Outdoor Grade Back and Side Wired	White Ivory Lt Almond Gray Black			GFWT1-W GFWT1-I GFWT1-T GFWT1-GY GFWT1-E	GFWT2-W GFWT2-I GFWT2-T GFWT2-GY GFWT2-E				
Decora Weather-Resistant Duplex GFCI Receptacle Outdoor Grade Back and Side Wired Self-Grounding	White Ivory Lt Almond Gray Black Brown Red					GFWT1-HGW GFWT1-HGI GFWT1-HGT GFWT1-HGG GFWT1-HGE GFWT1-HG GFWT1-HGR	GFWT2-HGW GFWT2-HGI GFWT2-HGT GFWT2-HGG GFWT2-HGE GFWT2-HG GFWT2-HGR	G5262-WTW G5262-WTI G5262-WTT G5262-WTG G5262-WTE G5262-WT G5262-WTR	G5362-WTW G5362-WTI G5362-WTT G5362-WTG G5362-WTE G5362-WT G5362-WTR
Decora Outlet Branch Circuit AFCI Receptacle Self-Grounding	White Ivory Lt Almond Gray Black Brown Red			AFTR1-W AFTR1-I AFTR1-T AFTR1-GY AFTR1-E AFTR1	AFTR2-W AFTR2-I AFTR2-T AFTR2-GY AFTR2-E AFTR2	AFTR1-HGW AFTR1-HGI AFTR1-HGT AFTR1-HGG AFTR1-HGE AFTR1-HG AFTR1-HGR	AFTR2-HGW AFTR2-HGI AFTR2-HGT AFTR2-HGG AFTR2-HGE AFTR2-HG AFTR2-HGR		
Decora Dual Function AFCI/GFCI Receptacle Self-Grounding	White Ivory Lt Almond Gray Black Brown			AGTR1-W AGTR1-I AGTR1-T AGTR1-GY AGTR1-E AGTR1	AGTR2-W AGTR2-I AGTR2-T AGTR2-GY AGTR2-E AGTR2				

Single and Duplex Receptacles

		Residential Grade		Commercial Grade		Hospital Grade		Industrial Grade	
RATING		15-125V	20-125V	15-125V	20-125V	15-125V	20-125V	15-125V	20-125V
Description	Color	Catalog Numbers							
Standard Duplex Receptacle Quickwire Push-In and Side-Wired	White Ivory Lt Almond Black Brown	T5320-W T5320-I T5320-T T5320-E T5320							
Standard Duplex Receptacle Quickwire Push-In and Side-Wired Self-Grounding	White Ivory Lt Almond	T5320-SW T5320-SI T5320-ST							
Standard Duplex Receptacle Back and Side-Wired Self-Grounding	White Ivory Lt Almond Gray Black Brown Red			TBR15-W TBR15-I TBR15-T TBR15-GY TBR15-E TBR15	TBR20-W TBR20-I TBR20-T TBR20-GY TBR20-E TBR20	8200-SGW 8200-SGI - 8200-SGG - 8200-SG 8200-SGR	8300-SGW 8300-SGI 8300-SGT 8300-SGG - 8300-SG 8300-SGR	5262-SGW 5262-SGI 5262-SGT 5262-SGG 5262-SGE 5262-SG 5262-SGR	5362-SGW 5362-SGI 5362-SGT 5362-SGG 5362-SGE 5362-SG 5362-SGR
Standard Duplex Receptacle Side-Wired Self-Grounding	White Ivory Lt Almond Gray Black Brown		T5820-W T5820-I T5820-T T5820-GY T5820-E T5820	TCR15-W TCR15-I TCR15-T TCR15-GY TCR15-E TCR15	TCR20-W TCR20-I TCR20-T TCR20-GY TCR20-E TCR20				
Standard Duplex Receptacle 8-Hole, Quick Wire Push-In Self-Grounding	White Ivory Brown	T5248-WCP T5248-ICP T5248-CP							
Standard Duplex Weather-Resistant Receptacle, Self-Grounding	White Ivory Gray Yellow	W5320-TW W5320-TI W5320-TG -	W5820-TW - - -	TWR15-W - TWR15-GY -	TWR20-W - TWR20-GY TWR20-Y				
Decora Duplex Receptacle Quickwire Push-In and Side-Wired	White Ivory Lt Almond Gray Black Brown	T5325-W T5325-I T5325-T T5325-GY T5325-E T5325							
Decora Duplex Receptacle Quickwire Push-In and Side-Wired Self-Grounding	White Ivory Lt Almond	T5325-SW T5325-SI T5325-ST							
Decora Duplex Receptacle Back and Side-Wired Self-Grounding	White Ivory Lt Almond Gray Black Brown Red Blue			TDR15-W TDR15-I TDR15-T TDR15-GY TDR15-E TDR15 TDR15-R TDR15-BU	TDR20-W TDR20-I TDR20-T TDR20-GY TDR20-E TDR20 -	16262-SGW 16262-SGI 16262-SGT - - 16262-SG 16262-SGR -	16362-SGW 16362-SGI 16362-SGT 16362-SGG - - 16362-SGR -		
Decora Duplex Receptacle Side-Wired Self-Grounding	White Ivory Lt Almond Gray Black Brown		T5825-W T5825-I T5825-T T5825-GY T5825-E T5825						
Single Receptacle Side-Wired Self-Grounding	White Ivory Lt Almond Gray Black Brown			T5015W T5015-I T5015-T T5015-GY T5015-E T5015	T5020W T5020-I T5020-T T5020-GY T5020-E T5020				
Single Receptacle Floor Box, 2-Pole, 3-Wire with Brass Plate	Ivory			5249-TFB	5349-TFB				
Duplex Receptacle Floor Box 1-Gang, 2-Pole, 3-Wire	Ivory w/Brass WP Ivory w/Nickel WP			25249-TFB 25249-TFN	25349-TFB 25349-TFN				
Duplex Receptacle Floor Box 2-Gang, 2-Pole, 3-Wire	Ivory w/Brass WP Ivory w/Nickel WP			35249-TFB 35249-TFN	35349-TFB 35349-TFN				
Low Voltage Duplex Receptacle Floor Box 2-Gang 1 Duplex Receptacle/ 1 Quickport Insert 2-Pole, 3-Wire	Ivory w/Brass WP Ivory w/Nickel WP			35249-TLB 35249-TLN	35349-TLB 35349-TLN				
Single Clockhanger Receptacle, 2-Pole, 3-Wire	White w/Painted WP Ivory w/Painted Steel WP White w/Stainless Steel WP			T5015-CHW T5015-CHI T5261-CH	T5020-CHW T5020-CHI T5361-CH				

Combination Receptacles

RATING	Description	Color	Residential Grade		Commercial Grade		Hospital Grade	
			15-125V	20-125V	15-125V	20-125V	15-125V	20-125V
			Catalog Numbers					
	Decora USB Charger/Single Receptacle	White Lt Almond Black	T5631-W T5631-T T5631-E					
	Decora USB Charger/Duplex Receptacle	White Ivory Lt Almond Gray Black Brown	T5632-W T5632-I T5632-T T5632-GY T5632-E T5632-B	T5832-W T5832-I T5832-T T5832-GY T5832-E T5832-B				
	Decora USB Charger/Duplex Receptacle Self-Grounding	White Ivory Lt Almond Gray Black Brown Red	T5632-SW - T5632-ST - - - -	T5832-SW - T5832-ST - - - -			T5632-HGW T5632-HGI T5632-HGT T5632-HGG T5632-HGE T5632-HG T5632-HGR	T5832-HGW T5832-HGI T5832-HGT T5832-HGG T5832-HGE T5832-HG T5832-HGR
	Decora LED Guide Light/ Receptacle	White Ivory Lt Almond	T6525-W T6525-I T6525-T					
	Single Pole Switch/ Standard Receptacle Self-Grounding	White Ivory Lt Almond Brown	T5225-W T5225-I T5225-T T5225					
	Single Pole Switch/Decora Receptacle Self-Grounding	White Ivory Lt Almond Black	T5625-W T5625-I T5625-T T5625-E					
	Single Pole Switch/Decora GFCI Receptacle Self-Grounding	White Lt Almond	GFSW1-W GFSW1-T					



Leviton Manufacturing Co., Inc.

201 North Service Road, Melville, NY 11747-3138
 Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
 Tech Line (8:30AM-7:00PM E.T. Monday-Friday): 1-800-824-3005

Visit our Website at: www.leviton.com/safety

© 2016 Leviton Manufacturing Co., Inc. All rights reserved.
 All trademarks are the property of their respective owners.

