

# 1200/1400/1600 SERIES™ RACEWAYS

Wiremold® 1200/1400/1600 Series Overfloor Raceway Systems provide permanent or temporary protection for overfloor cabling in high traffic areas.

1200/1400/1600 Series™ Raceway UL Code Reference ..... 87  
 1200/1400/1600 Series™ Raceway Color Options..... 87  
 1200 Series™ Raceway Ordering Information ..... 87  
 1400 Series™ Raceway Ordering Information ..... 88  
 1600 Series™ Raceway Ordering Information ..... 88

### CODE REFERENCE

1200, 1400, and 1600 Series Raceway is not UL Listed and is designed for use in protecting wiring and cabling.




1200 Series Pancake Raceway used to protect and retain power cords in a typical installation.



### 1200/1400/1600 SERIES RACEWAY COLOR OPTIONS

1200/1400/1600 Series Raceways are available in gray, black, beige, brown and high visibility yellow.

Custom color options are also available. Consult the factory for more information.




1200 SERIES — CHANNEL CAPACITY UP TO 5/16" [7.9MM] CABLE DIAMETER		
CATALOG NUMBER	COLOR	LENGTH
BE1200-5	Beige	5' [1.5m]
BE1200-5R	Beige	5' [1.5m]
BE1200-10	Beige	10' [3.0m]
BE1200-50	Beige	50' [15.2m]
BK1200-5	Black	5' [1.5m]
BK1200-10	Black	10' [3.0m]
BK1200-50	Black	50' [15.2m]
BR1200-5R	Brown	5' [1.5m]
BR1200-5	Brown	5' [1.5m]
BR1200-10	Brown	10' [3.0m]
BR1200-50	Brown	50' [15.2m]
GR1200-5	Gray	5' [1.5m]
GR1200-5R	Gray	5' [1.5m]
GR1200-10	Gray	10' [3.0m]
GR1200-50	Gray	50' [15.2m]
YL1200-50	High Visibility Yellow	50' [15.2m]





1400 SERIES — CHANNEL CAPACITY UP TO 1/2" [12.7MM] CABLE DIAMETER

CATALOG NUMBER	COLOR	LENGTH	
BE1400-5	Beige	5'	[1.5m]
BE1400-10	Beige	10'	[3.0m]
BE1400-50	Beige	50'	[15.2m]
BK1400-5	Black	5'	[1.5m]
BK1400-10	Black	10'	[3.0m]
BK1400-50	Black	50'	[15.2m]
BR1400-5	Brown	5'	[1.5m]
BR1400-10	Brown	10'	[3.0m]
BR1400-50	Brown	50'	[15.2m]
GR1400-5	Gray	5'	[1.5m]
GR1400-10	Gray	10'	[3.0m]
GR1400-50	Gray	50'	[15.2m]
YL1400-50	High Visibility Yellow	50'	[15.2m]




1600 SERIES — CHANNEL CAPACITY UP TO 3/4" [19.1MM] CABLE DIAMETER

CATALOG NUMBER	COLOR	LENGTH	
BE1600-5	Beige	5'	[1.5m]
BE1600-10	Beige	10'	[3.0m]
BE1600-25	Beige	25'	[7.6m]
BK1600-5	Black	5'	[1.5m]
BK1600-10	Black	10'	[3.0m]
BK1600-25	Black	25'	[7.6m]
BR1600-5	Brown	5'	[1.5m]
BR1600-10	Brown	10'	[3.0m]
BR1600-25	Brown	25'	[7.6m]
GR1600-5	Gray	5'	[1.5m]
GR1600-10	Gray	10'	[3.0m]
GR1600-25	Gray	25'	[7.6m]
YL1600-25	High Visibility Yellow	25'	[7.6m]



DST2



**DOUBLE-SIDED TAPE –**  
For long term installation.  
2" wide x 17 yds.