Non Adhesive Polyethylene

· Continuous Warning

• 4 Mil

• 3" or 6" Widths x 1,000 Ft.

 Custom Legends Available Underground Tape protects buried utility lines and is placed 12" above buried pipes, cables and conduits before final backfilling. Other legends, colors available on request.



CAT NO	UPC	LEGEND	COLOR	STD	MSTR	WT/STD	UNIT						
3" x 1,000 Ft. 4 Mil													
UT4D	16704	Caution Buried Cable TV Line Below	Orange	1	12	4.49#	Ea						
UT7D	16340	Caution Buried Electric Line Below	Yellow	1	12	4.49#	Ea						
UT8D	16342	Caution Buried Electric Line Below	Red	1	12	4.49#	Ea						
UT11D	16711	Caution Buried High Voltage Line Below	Yellow	1	12	4.49#	Ea						
UT12D	16712	Caution Buried High Voltage Line Below	Red	1	12	4.49#	Ea						
UT17D	16717	Caution Buried Telephone Line Below	Orange	1	12	4.49#	Ea						
UT19D	16719	Caution Buried Utilities Underground	Yellow	1	12	4.49#	Ea						
UT20D	16720	Caution Buried Utility Line Below	Yellow	1	12	4.49#	Ea						
UT43D	16743	Caution Buried Cable Line Below	Orange	1	12	4.49#	Ea						
UT44D	16744	Caution Buried Fiber Optic Line Below	Orange	1	12	4.49#	Ea						
6" x 1,00	6" x 1,000 Ft. 4 Mil												
UT25D	16725	Caution Buried Cable TV Line Below	Orange	1	6	9.02#	Ea						
UT28D	16344	Caution Buried Electric Line Below	Yellow	1	6	9.02#	Ea						
UT29D	16346	Caution Buried Electric Line Below	Red	1	6	9.02#	Ea						
UT32D	16732	Caution Buried High Voltage Line Below	Yellow	1	6	9.02#	Ea						
UT33D	16733	Caution Buried High Voltage Line Below	Red	1	6	9.02#	Ea						
UT38D	16738	Caution Buried Telephone Line Below	Orange	1	6	9.02#	Ea						
UT40D	16740	Caution Buried Utilities Underground	Yellow	1	6	9.02#	Ea						
UT41D	16741	Caution Buried Utility Line Below	Yellow	1	6	9.02#	Ea						
UT46D	16746	Caution Buried Cable Line Below	Orange	1	6	9.02#	Ea						
UT47D	16747	Caution Buried Fiber Optic Line Below	Orange	1	6	9.02#	Ea						

Detectable Tape PC 5325




· Continuous Warning

• 4.5 Mil

• 3" and 6" Widths x 1,000 Ft.

 Custom Legends Available



CAT NO	UPC	LEGEND	COLOR	STD	MSTR	WT/STD	UNIT					
3" x 1,000 Ft.												
DU01	16350	Caution Buried Electric Line Below	Red	1	12	6.07#	Ea					
DU05	16360	Caution Buried Telephone Line Below	Orange	1	12	6.07#	Ea					
DU08	16364	Caution Buried CATV Line Below	Orange	1	12	6.07#	Ea					
DU09	16366	Caution Buried High Voltage Line Below	Red	1	12	6.07#	Ea					
DU10	16368	Caution Buried Fiber Optic Line Below	Orange	1	12	6.07#	Ea					
6" x 1,000 Ft.												
DU601	16352	Caution Buried Electric Line Below	Red	1	6	13.72#	Ea					
DU605	16370	Caution Buried Telephone Line Below	Orange	1	6	13.72#	Ea					
DU608	16372	Caution Buried CATV Line Below	Orange	1	6	13.72#	Ea					
DU609	16374	Caution Buried High Voltage Line Below	Red	1	6	13.72#	Ea					
DU610	16376	Caution Buried Fiber Optic Line Below	Orange	1	6	13.72#	Ea					

TECH TALK

Barricade Tape: Barricade tapes will consist of high visibility safety yellow or red polyethylene with bold black letters. Standard Letter height is two inches (2"). Tape helps prevent accidents by increasing visibility of hazards and can be tied, stapled or nailed in place.

Underground Tape: Non-Detectable warning tape for the protection, location and identification of underground utility installations. Consists of a nominal 4.0 mil overall thickness inert plastic film formulated to resist degradation due to acid and alkalies found in soils. Product is lead free.

Detectable Tape: Detectable warning tape consists of nominal 4.5 mil (.0045") overall thickness, with a solid aluminum foil core. The imprinted warning message is "Buried, or Encased" to prevent ink rub-off, and is impervious to acid, alkalis and other destructive elements found in soil. The imprint is as such that it allows for total reflectivity. Use of an industrial grade non-ferrous metal detector is used when location is needed.