



# Cable Management Panels

Slotted Ducts Allow Patch Cords to be Placed Vertically to Designated Ports

Bracket is Equipped with Several Velcro® Tie Anchor Points

Finger Duct Panel with Cover Provides a Clean Appearance

Extended Cable Management Bracket Provides Excellent Strain Relief and Cabling Routing Options

90° Outside Corner Maintains Minimum Bend Radius



## Installation Benefits

- Rack Mount Rear Panel Mounts Directly on the Rack to Support Terminated Cable from the Rear



- "L" Bracket Allow Quick and Easy Cable Management



### Finger Duct Panel

Slotted ducts allow for vertical placement of horizontally routed cable. Includes #12 rack screws.

PART NUMBER	DESCRIPTION
<b>ICCMSCMA41</b>	24-Slots, 1 RMS



### Rack Mount Rear Panel

Designed for mounting behind rack to provide cable support. Rack screws not included.

PART NUMBER	DESCRIPTION
<b>ICMPP35RMB</b>	Rear Bar



ICMPP35RMB

### Finger Duct Panel

Slotted ducts allow for vertical placement of horizontally routed cable. Includes #12 rack screws.

PART NUMBER	DESCRIPTION
<b>ICCMSCMA42</b>	24-Slots, 2 RMS



ICCMSCMA42

### Extended Bracket Panel

Bracket is designed to provide cable support on the front and rear of rack and over rack panels for more strain relief protection. Includes #12 rack screws.

PART NUMBER	DESCRIPTION
<b>ICCMSE45RB</b>	Extended Bracket



ICCMSE45RB

### Finger Duct Panel

48-slotted finger ducts are designed for front and rear cable routing. Includes #12 rack screws.

PART NUMBER	DESCRIPTION
<b>ICCMSCMA61</b>	48-Slots, 1 RMS



ICCMSCMA61

Bracket is designed to mount to any standard EIA-compliant hole spacing for custom vertical and horizontal cable management. Includes #12 rack screws.

PART NUMBER	DESCRIPTION
<b>ICCMSCMPL1</b>	Bracket, Aluminum Black
<b>ICCMSCMPL2</b>	Bracket, Aluminum Polished



ICCMSCMPL1

### Finger Duct Panel

48-slotted finger ducts are designed for front and rear bulk cable routing. Includes #12 rack screws.

PART NUMBER	DESCRIPTION
<b>ICCMSCMA62</b>	48-Slots, 2 RMS



ICCMSCMA62



ICCMSCMPL2

Sold by:

  
**TWAccomm.com**  
http://www.TWAccomm.com  
Toll Free: (877) 892-2666