

ICS Ordering Guide

Kit Supplied with Sender, Receiver and Fan Switch Housing

ICS Conversion Kit:

A Replacement Hub converts a Fan to an ICS system. Fan speed adjustment, direction and light intensity (for non-CFL lamps). See Ordering Guide below for the system that's right for you.



ICS Wall/Remote Control System:

- 3 Speed Fan Control and Reverse
- Light On/Off or 300 Watt Full Range Dimmer (Dimming feature for non-CFL lamps)
- 1.5 Amp (One Fan per Control System)
- ICS Wall Control with 3 Decorator Style Faceplate Inserts (Almond, White, Black)
- ICS CLAMSHELL included to Convert your Wall Control to a Hand-Held Remote Control
- Replacement Hub Included
- Additional Wall Controls and Clamshells Available
- 1-12V Battery Included
- Large Decorator Style Switch Plate Included (White)
- See Ordering Guide for Series Availability

Full Learning or Partial Learning System.

ICS = Full Learning System: Both transmitter and receiver have no DIP switches and transmitters are assigned a unique identifier code.

ICS2 = Partial Learning System: Transmitter has traditional 4 DIP switches but receiver has learning function to learn the switch setting of the transmitter.

New Clamshell system allows one transmitter to function as either a wall control or a hand-held remote control. Just add the CLAMSHELL-ICS to either the ICS-WALL (Full Learning) or ICS2-WALL (Partial Learning) to create your Hand-Held Remote Control. Up to 3 ICS transmitters can be used in conjunction with the ICS conversion system.

Model	Series	ICS Remote Kit	Component 1	Component 2	Component 3	Component 4	Component 5
AT52	American Tradition	AT-ICS-(Finish)	ICS-WALL	ICS-CLAMSHELL	AT-MODULE-ICS	BX-ICS	AT-9(Finish)-ICS
CP52	Chaparral	CP-ICS2-(Finish)	ICS2-WALL	ICS-CLAMSHELL	RT52-MODULE-ICS2	BX-ICS	CP-9(Finish)-ICS2
CV52	Cordova	CV-ICS-(Finish)	ICS-WALL	ICS-CLAMSHELL	CXL-MODULE-ICS	BX-ICS	CV-9(Finish)-ICS
CXL52	CXL	CXL-ICS-(Finish)	ICS-WALL	ICS-CLAMSHELL	CXL-MODULE-ICS	BX-ICS	CXL-9(Finish)-ICS
K52	Kona Bay	K52-ICS-(Finish)	ICS-WALL	ICS-CLAMSHELL	K52-MODULE-ICS	BX-ICS	K52-9(Finish)-ICS
ME52	Metro	ME-ICS-(Finish)	ICS-WALL	ICS-CLAMSHELL	ME-MODULE-ICS	BX-ICS	ME-9(Finish)-ICS
MI52	Mia	MI-ICS-(Finish)	ICS-WALL	ICS-CLAMSHELL	CXL-MODULE-ICS	BX-ICS	MI-9(Finish)-ICS
OA52	Ophelia	OA-ICS2-(Finish)	ICS2-WALL	ICS-CLAMSHELL	RT52-MODULE-ICS2	BX-ICS	OA-9(Finish)-ICS2
P252	Presidential II	P2-ICS-(Finish)	ICS-WALL	ICS-CLAMSHELL	CXL-MODULE-ICS	BX-ICS	P2-9(Finish)-ICS
RT52	Riata 52"	RT-ICS2-(Finish)	ICS2-WALL	ICS-CLAMSHELL	RT52-MODULE-ICS2	BX-ICS	RT-9(Finish)-ICS2
SN52	Sentry	AT-ICS-(Finish)	ICS-WALL	ICS-CLAMSHELL	AT-MODULE-ICS	BX-ICS	AT-9(Finish)-ICS
TO52	Toscana	TO-ICS2-(Finish)	ICS2-WALL	ICS-CLAMSHELL	TO52-MODULE-ICS2	BX-ICS	TO-9(Finish)-ICS2
WD52	Woodward	WD-ICS2-(Finish)	ICS2-WALL	ICS-CLAMSHELL	RT52-MODULE-ICS2	BX-ICS	WD-9(Finish)-ICS2
ZE56	Zena	ZE-ICS-(Finish)	ICS-WALL	ICS-CLAMSHELL	CXL-MODULE-ICS	BX-ICS	ZE-9(Finish)-ICS