



| PLENUM RATED - MULTI-CONDUCTOR OVERALL SHIELDED  |                |                               |     |        |                   |           |        |             |              |           |
|--|----------------|-------------------------------|-----|--------|-------------------|-----------|--------|-------------|--------------|-----------|
| TWC PART NUMBER  | SW PART NUMBER | DESCRIPTION                   | AWG | # COND | NOM. DIAM. (inch) | PACKAGING |        |             | JACKET COLOR | UL/NEC®   |
|  |                |                               |     |        |                   | TYPE      | LENGTH | lbs/1000 ft |              |           |
| Burglar alarm, public address systems, intercoms, telephone stations, speakers, instrumentation, control and other low voltage circuits that are power-limited. For all power-limited circuit use. |                |                               |     |        |                   |           |        |             |              |           |
| P20032.1A  | 57570802       | 22/2C STR BC OAS WHT          | 22  | 2      | 0.118             | REELS     | 1000'  | 11          | WHITE        | CMP/CL3P  |
| P20032.1B  | 57570801       | 22/2C STR BC OAS WHT          | 22  | 2      | 0.118             | REELEX    | 1000'  | 11          | WHITE        | CMP/CL3P  |
| P20032.1D  | 57570803       | 22/2C STR BC OAS WHT          | 22  | 2      | 0.118             | REELEX    | 500'   | 11          | WHITE        | CMP/CL3P  |
| P20043.1B  | 57721101       | 22/3 STR BC OAS WHT           | 22  | 3      | 0.126             | REELEX    | 1000'  | 14          | WHITE        | CMP/CL3P  |
| P20270.1A  | 57571002       | 22/4C STR BC OAS WHT          | 22  | 4      | 0.137             | REELS     | 1000'  | 17          | WHITE        | CMP/CL3P  |
| P20270.1B  | 57571001       | 22/4C STR BC OAS WHT          | 22  | 4      | 0.137             | REELEX    | 1000'  | 17          | WHITE        | CMP/CL3P  |
| P20012.4A  | 57720902       | 22/2 STR BC SHLD + 2/C NS WHT | 22  | 4      | 0.137             | REELS     | 1000'  | 18          | WHITE        | CMP/CL3P  |
| P20012.4B  | 57720901       | 22/2 STR BC SHLD + 2/C NS WHT | 22  | 4      | 0.137             | REELEX    | 1000'  | 18          | WHITE        | CMP/CL3P  |
| P20019.1A  | 57570702       | 22/6C STR BC OAS WHT          | 22  | 6      | 0.155             | REELS     | 1000'  | 23          | WHITE        | CMP/CL3P  |
| P20019.1B  | 57570701       | 22/6C STR BC OAS WHT          | 22  | 6      | 0.155             | REELEX    | 1000'  | 23          | WHITE        | CMP/CL3P  |
| P20037.1A  | 57570902       | 22/8C STR BC OAS WHT          | 22  | 8      | 0.179             | REELS     | 1000'  | 29          | WHITE        | CMP/CL3P  |
| P20023.1A  | 57721002       | 22/12C STR BC OAS WHT         | 22  | 12     | 0.223             | REELS     | 1000'  | 42          | WHITE        | CMP/CL3P  |
| P30006.1A  | 57721502       | 20/2C STR BC OAS WHT          | 20  | 2      | 0.130             | REELS     | 1000'  | 14          | WHITE        | CMP/CL3P  |
| P30045.1A  | 57643502       | 20/3C STR BC OAS WHT          | 20  | 3      | 0.139             | REELS     | 1000'  | 18          | WHITE        | CMP/CL3P  |
| P30003.1A  | 57721402       | 20/4C STR BC OAS WHT          | 20  | 4      | 0.151             | REELS     | 1000'  | 23          | WHITE        | CMP/CL3P  |
| P40133.1A  | 57571602       | 18/2C STR BC OAS WHT          | 18  | 2      | 0.154             | REELS     | 1000'  | 19          | WHITE        | CMP/CL3P  |
| P40133.1B  | 57571601       | 18/2C STR BC OAS WHT          | 18  | 2      | 0.154             | REELEX    | 1000'  | 19          | WHITE        | CMP/CL3P  |
| P40133.1C  | 57571604       | 18/2C STR BC OAS WHT          | 18  | 2      | 0.154             | REELS     | 500'   | 19          | WHITE        | CMP/CL3P  |
| P40133.1D  | 57571605       | 18/2C STR BC OAS WHT          | 18  | 2      | 0.154             | REELEX    | 500'   | 19          | WHITE        | CMP/CL3P  |
| P41111.1A  | 57721602       | 18/2C STR TC OAS FEP/PVC WHT  | 18  | 2      | 0.152             | REELS     | 1000'  | 21          | WHITE        | CMP/CL3P  |
| P40032.1A  | 57571102       | 18/3C STR BC OAS WHT          | 18  | 3      | 0.165             | REELS     | 1000'  | 26          | WHITE        | CMP/CL3P  |
| P40032.1B  | 57571101       | 18/3C STR BC OAS WHT          | 18  | 3      | 0.165             | REELEX    | 1000'  | 26          | WHITE        | CMP/CL3P  |
| P40032.1C  | 57571104       | 18/3C STR BC OAS WHT          | 18  | 3      | 0.165             | REELS     | 500'   | 26          | WHITE        | CMP/CL3P  |
| P40073.1A  | 57571502       | 18/4C STR BC OAS WHT          | 18  | 4      | 0.184             | REELS     | 1000'  | 33          | WHITE        | CMP/CL3P  |
| P40073.1B  | 57571501       | 18/4C STR BC OAS WHT          | 18  | 4      | 0.184             | REELEX    | 1000'  | 33          | WHITE        | CMP/CL3P  |
| P40073.1C  | 57571504       | 18/4C STR BC OAS WHT          | 18  | 4      | 0.184             | REELS     | 500'   | 33          | WHITE        | CMP/CL3P  |
| P40073.1D  | 57571503       | 18/4C STR BC OAS WHT          | 18  | 4      | 0.184             | REELEX    | 500'   | 33          | WHITE        | CMP/CL3P  |
| P40040.1A  | 57571302       | 18/6C STR BC OAS WHT          | 18  | 6      | 0.228             | REELS     | 1000'  | 47          | WHITE        | CMP/CL3P  |
| P40040.1B  | 57571301       | 18/6C STR BC OAS WHT          | 18  | 6      | 0.228             | REELEX    | 1000'  | 47          | WHITE        | CMP/CL3P  |
| P40040.1C  | 57571304       | 18/6C STR BC OAS WHT          | 18  | 6      | 0.228             | REELS     | 500'   | 47          | WHITE        | CMP/CL3P  |
| P40070.1A  | 57571402       | 18/8C STR BC OAS WHT          | 18  | 8      | 0.241             | REELS     | 1000'  | 60          | WHITE        | CMP/CL3P  |
| P40070.1C  | 57571404       | 18/8C STR BC OAS WHT          | 18  | 8      | 0.241             | REELS     | 500'   | 60          | WHITE        | CMP/CL3P  |
| P50002.1A  | 57571702       | 16/2C STR BC OAS WHT          | 16  | 2      | 0.178             | REELS     | 1000'  | 27          | WHITE        | CMP/CL3P  |
| P50002.1B  | 57571701       | 16/2C STR BC OAS WHT          | 16  | 2      | 0.178             | REELEX    | 1000'  | 27          | WHITE        | CMP/CL3P  |
| P50023.1A  | 57571802       | 16/4C STR BC OAS WHT          | 16  | 4      | 0.210             | REELS     | 1000'  | 48          | WHITE        | CMP/CL3P  |
| P60022.1A  | 57571902       | 14/2C STR BC OAS WHT          | 14  | 2      | 0.216             | REELS     | 1000'  | 40          | WHITE        | CL3P/FPLP |