



LAMP HOLDERS

GU24 LAMP HOLDERS



TYPICAL APPLICATIONS:

- Closets
- Garages
- Attics
- Utility Rooms
- Basements
- Car Washes
- Storage Buildings
- Commercial, Industrial, Residential, and Agricultural Lighting
- And more...



Lamp Comparison

	60-watt	13-watt
Annual Energy Cost	\$36.75*	\$7.98*
Lumen Output	890	900

Annual Energy Savings using a 13-watt vs. a 60-watt = 78% or \$28.77 Savings!

*The kWh of electricity used per day is 1.44 kWh for a 60-watt Incandescent Lamp vs. 0.312 kWh for a 13-watt Compact Fluorescent Lamp based on operating 24 hours a day, 365 days at \$0.07 per kWh per day. Your actual savings will vary based on the amount of electricity you use and your supplier's cost per day may be more or less than the estimated savings presented in this example.

- Includes 13-watt Bi-Pin Compact Fluorescent Lamp (CFL) and Polycarbonate Lamp Diffuser.
- Can be used with a standard wall switch.
- Impact resistant construction.
- 7" Conductors simplify installation.
- Suitable for indoor use only.
- Medium Base fits 3.25 inch or 4.0 inch Outlet Box.
- Lamp Holder Rating: 120W-250VAC, 60Hz
- Meets the requirements of the 2017 National Electrical Code: Articles 410.16(A)(1), 410.52, 410.74(A)(B).



Catalog Number	UPC Number	Description	Order Unit	Order Qty	Unit Pkg	Units/Case	TL Case Qty	Min Order Qty	MM Req	Ship Wt (Lbs)
16530	16530	GU24 Lamp Holder: Keyless	EA	1	BX	24	24	24	Yes	11
16535	16535	GU24 Lamp Holder: Pull Chain	EA	1	BX	24	24	24	Yes	11
15675	15675	Compact Fluorescent Lamp: GU24 Bi-Pin Self Ballasted Lamp (2700K)	EA	1	BX	25	25	25	Yes	8

Note: GU24 Lamp Holders are sold ONLY in case quantities of 24 per Carton.

UNITS OF MEASURE KEY

Order Unit: The Unit to be ordered; **Order Qty:** Number of pieces in each Unit; **Unit Pkg:** Packaging types - BG (Bag), BX (Box), BN (Bulk); **Units/Case:** Unit packages contained in the Case; **TL Case Qty:** The total number of items in each Master Case; **Min Order Qty:** The smallest Unit that can be ordered; **MM Req:** Must order multiples of the Unit in the stated quantities; **Ship Wt (Lbs):** Total weight of the Units per Carton

Specifications subject to change without prior notice.

LAMP HOLDERS

PORCELAIN AND PLASTIC LAMP HOLDERS

- UL Listed. File Number: E236781.
- Nickel-plated Brass Screw Shell will not corrode.
- For Commercial, Industrial, Residential and Agricultural Lighting Applications.
- Medium Base fits 3.25 inch or 4.0 inch Outlet Box.
- UV resistant Lamp Holders will not fade or discolor.
- Optional Plastic and Metal Safety Cages fit all Edison Base (E26) Lamp Holders.
- Includes corrosion resistant stainless steel mounting screws.
- Meets the requirements of the 2017 National Electrical Code:
 - Part Numbers: 16500, 16502, 16510, 16512 and 16514 - Articles 410.74(A)(B) and 410.122
 - Part Numbers: 16520, 16522, 16524 and 16526 - Articles 410.52, 410.74(A)(B) and 410.122



Catalog Number	UPC Number	Description	Order Unit	Order Qty	Unit Pkg	Units/Case	TL Case Qty	Min Order Qty	MM Req	Ship Wt (Lbs)
16500	16500	Porcelain Lamp Holder: Keyless, 4-Terminal	EA	1	BX	48	48	48	Yes	33
16502	16502	Porcelain Lamp Holder: Pull Chain	EA	1	BX	48	48	48	Yes	35
16510	16510	Plastic Lamp Holder: Keyless, 4-Terminal	EA	1	BX	48	48	48	Yes	11
16512	16512	Plastic Lamp Holder: Pull Chain	EA	1	BX	48	48	48	Yes	13
16514	16514	Porcelain Lamp Holder: Pull Chain and 15 AMP Receptacle	EA	1	BX	48	48	48	Yes	40
16520	16520	Porcelain Lamp Holder: Keyless, 4-Terminal with 7" Black and White Conductors	EA	1	BX	48	48	48	Yes	33
16522	16522	Porcelain Lamp Holder: Pull Chain with 7" Black and White Conductors	EA	1	BX	48	48	48	Yes	35
16524	16524	Plastic Lamp Holder: Keyless, 4-Terminal with 7" Black and White Conductors	EA	1	BX	48	48	48	Yes	11
16526	16526	Plastic Lamp Holder: Pull Chain with 7" Black and White Conductors	EA	1	BX	48	48	48	Yes	13
16100	16100	Safety Cage: Yellow	EA	1	BX	10	10	10	Yes	1
16501	16501	Safety Cage: Metal	EA	1	BX	12	12	12	Yes	6

Note: Lamp Holders are sold ONLY in case quantities of 48 per Carton.

Specifications subject to change without prior notice.

E02-150-004 D1 (12/14-SP)

©2014 Engineered Products Company. All Rights Reserved.

UNITS OF MEASURE KEY

Order Unit: The Unit to be ordered; **Order Qty:** Number of pieces in each Unit; **Unit Pkg:** Packaging types - BG (Bag), BX (Box), BN (Bulk); **Units/Case:** Unit packages contained in the Case; **TL Case Qty:** The total number of items in each Master Case; **Min Order Qty:** The smallest Unit that can be ordered; **MM Req:** Must order multiples of the Unit in the stated quantities; **Ship Wt (Lbs):** Total weight of the Units per Carton

www.engproducts.com

5401 SMETANA DRIVE | MINNETONKA, MN 55343

P 800.336.1976 | F 800.336.2801



**ENGINEERED
PRODUCTS CO.**