

TOUGH LIGHTING TOOLS

SINCE 1976

7 SERIES

TACTICAL

7 SERIES: ARMED WITH DIVERSITY

In support of the thin blue line, we have innovated flashlight technology. You'll be ready for whatever is on the other side of the dispatch call. Our new 7 Series Tactical Flashlights are diverse, tough and the smartest tactical lights to hit the streets. With wireless or USB rechargeability, battery level indication and up to 1000 plus blinding lumens, you'll

now be in control of the brightest Pelican™ tactical flashlights. And with Type III hard anodized finish, dual switches and Bluetooth™ app programming, these flashlights are engineered to answer any call.

7100

7600

OUR FIRST
USB/COMPACT
MULTI VERSATILE
TACTICAL
FLASHLIGHTS

2016

7600 / 7100:
LAUNCHED 8.2016

7110

7610

7620

OUR NEW
MULTI-BATTERY
TACTICAL
SQUAD

2018

7110 / 7610 / 7620:
LAUNCHING 2.2018

7070R

THE MOST
TECHNOLOGICALLY
ADVANCED
FLASHLIGHT

2018

7070R:
LAUNCHING 3.2018

CAT NO.	BATTERIES		WEIGHT W/ BATTERIES (gr)	LENGTH (cm)	ANSI LIGHT OUTPUT (lumens)		ANSI RUN TIME	ANSI BEAM DISTANCE (meters)	ANSI IP RATING	COLOR
	INCLUDED	ALSO SUPPORTS								
7100	Rechargeable Lithium Ion	1 AA	4.4 oz. (125 gr)	5.12" (13 cm)	695*, 348**, 33***		1h 15m*, 1h 30m**, 9h 15m***	194m*,130m**, 38m***	IPX8	■
7600	Rechargeable Lithium Ion	2 CR123	7.1 oz. (201 gr)	6.19" (15.7 cm)	944*, 479**, 37***		3h 15m*, 4h 30m**, 29h***	225m*, 157m**, 44m***	IPX8	■
7110*	1AA	1 CR123	4.1 oz. (116 gr)	4.63" (11.76cm)	229*, 98**, 17*** Based on 1 AA Battery		30m*, 1h 15m**, 11h*** Based on 1 AA Battery	112m*, 73m**, 29m** Based on 1 AA Battery	IPX8	■
7610*	1AA	1 CR123, 2 CR123, Rechargeable Lithium Ion	5.5 oz. (156 gr)	5.38" (13.67cm)	185*, 119**, 30** Based on 1 AA Battery		45m*, 1h 30m**, 6h 30m*** Based on 1 AA Battery	97m*, 81m**, 37m** Based on 1 AA Battery	IPX8	■
7620*	2 AA	2 CR123, 3 CR123, Rechargeable Lithium Ion	6.9 oz. (194.5 gr)	6.75" (17.15cm)	387*, 193**, 30** Based on 2AA Batteries		1h 45m*, 4h 30m**, 13h*** Based on 2AA Batteries	139m*, 98m**, 39m** Based on 2AA Batteries	IPX8	■
7070R	Rechargeable Lithium-Ion	2 CR123 Rechargeable Lithium Ion	7.9 oz (224 gr)	6.88" (17.5 cm)	1123*, 630**, 18***		2h*, 2h 15m**, 51h***	256m*, 178m**, 29m***	IPX8	■

*High | **Medium | ***Low | *Refer to Pelican.com for full specs. For details go to www.pelican.com



DON'T LOOK BACK

7600 / 7100 / THE PIONEERS PUSHING PELICAN TACTICAL LIGHTING TO THE FOREFRONT

Our 7600 and 7100 are Pelican's first advanced tactical flashlights to set the standard and pave the way for high performance with tough as nails DNA you'll find in the 7 Series family. From selectable and programmable modes - ranging from strobe to super bright lumens, traffic wand options and battery level indications, you'll see that these flashlights are tough and versatile. You'll never look back.




PELICAN™ 7600

- Type III Hard Anodized Finish
 - USB Lithium Ion Rechargeable
 - Programmable
 - Full Time Battery Level Indication
 - Selectable Modes
 - Anti-Reflective (AR) Glass Lens
 - Ingress Protected IPX8 Submersible
- 3 LED Colors: Red, Green, White
 - Traffic Wand and Holster Option Available



PELICAN™ 7100

- USB Lithium Ion Rechargeable
- Programmable
- Full Time Battery Level Indication
- Selectable Modes
- Anti-Reflective (AR) Glass Lens
- Ingress Protected IPX8 Submersible



Don't let low battery power freeze you in your tracks. Our new 7110, 7610, and 7620 tactical lights are compatible with AA, CR123 and rechargeable batteries, giving you the option to reload with more

STAY IN CHARGE

7110 / 7610 / 7620 / OUR NEW MULTI-BATTERY TACTICAL SQUAD

battery options to keep the mission going. Large (7620), medium (7610) and small (7110) flashlight sizes are available for the right fit.



PELICAN™ 7110 | 7610 | 7620

- Type III Hard Anodized Finish
- Multi-Battery Options
- Full Time Battery Level Indication
- Selectable Modes
- Anti-Reflective (AR) Glass Lens
- Ingress Protected IPX8 Submersible

MORE THAN AN ON/OFF SWITCH

7070R / THE MOST TECHNOLOGICALLY ADVANCED FLASHLIGHT

Think of it as Artificial Intelligence in a flashlight. The new 7070R can be programmed via Bluetooth™ app and USB wireless rechargeability keeps the 7070R free from connecting USB cables directly to the flashlight. Dual Switch technology activates the flashlight by forward or rear mounted switches giving you the option to move from duty to tactical situations instantly.

PELICAN™ 7070R

- Bluetooth™ App Programming
- Dual Switches
- Wireless Charging
- Full Time Battery Level Indication
- Anti-Reflective (AR) Glass Lens
- Lithium Ion Rechargeable Battery



COMING SOON



Bluetooth™ App Programmable



Wireless USB Charging Cradle



DISTRIBUTED BY:

For warranty details go to www.pelican.com/warranty
©2018 Pelican Products, Inc. All trademarks are registered and/or
unregistered trademarks of Pelican Products, Inc., its subsidiaries and/or
affiliates. BLUETOOTH is a registered trademark of Bluetooth Sig, Inc.
ENERGIZER is a trademark of Energizer Brands, LLC.
Part No. 0030-STB-000 NV/17