

LED Controllers Chart

DMX DECODER	Description
LV-DMX-IP-RGB-3CH	3CH DMX Decoder 12/24V DC output, <4A MAX, 12<144W, 24v<288W
LV-DMX-IP-RGB-4CH	4CH DMX Decoder 12/24V DC output, <4A MAX, 12<192W, 24v<384W
DMX CABLE	Description
LVL-DMX-3PIN-1FT	1ft Long power cable with XLR waterproof connector
LVL-DMX-3PIN-5FT	5ft Long power cable with XLR waterproof connector
LVL-DMX-3PIN-10FT	10ft Long power cable with XLR waterproof connector
LVL-DMX-3PIN-25ft	25ft Long power cable with XLR waterproof connector
LVL-DMX-3PIN-50FT	50ft Long power cable with XLR waterproof connector
LVL-DMX-3PIN-60FT	60ft Long power cable with XLR waterproof connector
LVL-DMX-3PIN-100FT	100ft Long power cable with XLR waterproof connector
DMX CONTROLLERS	Description
SLESA-U9	Entry level, USB 256 channels
STICK-GA2	Mid range, touch control pad 512 channels
STICK-GU2	DMX, touch control pad, 128 channels
STICK-DE3	Professional, touch control Pad 1024 channels
DMX ACCESSORIES	Description
LV-DMX-XLR3-ST	XLR3 Signal terminator
LV-DMX-3PIN	Power cable XLR waterproof connector
SENSOR	Description
LV-SPIR-1CH-LV	PIR Motion sensor, 1 channel, 12/24V DC
CONTROLLERS & AMPLIFIERS	Description
LT-09S-RF	6 Key RGB "touch" controller 12/24V DC
LT-390A	Signal amplifier for RGB 12/24V DC, 3 channel, indoor
LT-031-RF	6 Key CCT Adjustable "touch" controller 12/24V DC
LT-290A	Signal amplifier for CCT color adjust tape light 12/24V DC
LT-032-RF	6 Key Dimming "touch" controller 12/24V DC
LV-ZJFFS-3CH-6INW	WD Signal amplifier for RGB 12/24V DC, 3 channel, outdoor
LV-RF103	Wireless RF mini RGB controller 24V, 96W
LV-RF103-EXHS	6" Tape Light extension connector for LV-RF103 controller
LN-CON-WIFI-3CH-XV	WiFi controller for RGB, CCT, and dimming, c/w RF remote 12/24VDC
LV-TC101	Mini three button dimmer 24V, 96W



LN-CON-WIFI-3CH-XV



STICK-DE3



STICK-J GA2



SLESA-U9



STICK-GU2



LV-RF103



LV-SPIR-1CH-LV



LT-390A
NOT SHOWN: LT-290A



LV-ZJFFS-3CH-6INW



LV-DMX-IP-RGB-3CH
LV-DMX-IP-RGB-4CH



LT-031-RF



LT-032-RF



LT-09S-RF

LVL-DMX-3PIN



LV-DMX-XLR-ST



LVL-DMX-3PIN-1FT
LVL-DMX-3PIN-5FT
LVL-DMX-3PIN-10FT
LVL-DMX-3PIN-25FT
LVL-DMX-3PIN-50FT
LVL-DMX-3PIN-60FT
LVL-DMX-3PIN-100FT



LV-TC-101



LV-HS-CN-3DC