

OC50143 - 50ft. 14/3 SJTW Orange Extension Cord

Features

- Water Resistant
- Flame Retardant
- Ultra Flexible
- Corrosion Resist Blades

Specifications

- **Length (ft):** 50
- **Color:** Orange
- **Gauge:** 14/3
- **Wire Type:** SJTW
- **Certifications:** UL or equivalent
- **Electrical Ratings:** 15A/ 125V/ 1875W
- **Product Packaging:** Sleeve
- **Unit Measurement (DxWxH):** 2x6.5x14.5
- **Unit Weight (lbs):** 4.75
- **Master Carton Type:** Brown Box
- **Master Carton Measurements:** 13.75x13.75x10
- **Master Carton Weight (lbs):** 39.5
- **Master Carton Qty:** 8

Unit UPC: 752560 660063

Master Carton UPC: 30752560 660064



OC100143 - 100ft. 14/3 SJTW Orange Extension Cord

Features

- Water Resistant
- Flame Retardant
- Ultra Flexible
- Corrosion Resist Blades

Specifications

- **Length (ft):** 100
- **Color:** Orange
- **Gauge:** 14/3
- **Wire Type:** SJTW
- **Certifications:** UL or equivalent
- **Electrical Ratings:** 13A/ 125V/ 1625W
- **Product Packaging:** Sleeve
- **Unit Measurement (DxWxH):** 2.8x9.2x14.2
- **Unit Weight (lbs):** 9.75
- **Master Carton Type:** Brown Box
- **Master Carton Measurements:** 17x16.5x6.5
- **Master Carton Weight (lbs):** 39.2
- **Master Carton Qty:** 4

Unit UPC: 752560 660070

Master Carton UPC: 30752560 660071



OC50123LT - 50ft. 12/3 SJTW Yellow Extension Cord

Features

- Water Resistant
- Flame Retardant
- Ultra Flexible
- Corrosion Resist Blades
- Lighted Ends

Specifications

- **Length (ft):** 50
- **Color:** Yellow
- **Gauge:** 12/3
- **Wire Type:** SJTW
- **Certifications:** UL or equivalent
- **Electrical Ratings:** 15A/ 125V/ 1875W
- **Product Packaging:** Sleeve
- **Unit Measurement (DxWxH):** 2.5x7.5x15
- **Unit Weight (lbs):** 7.65
- **Master Carton Type:** Brown Box
- **Master Carton Measurements:** 16x13.75x8.25
- **Master Carton Weight (lbs):** 47.4
- **Master Carton Qty:** 6

Unit UPC: 752560 660094
Master Carton UPC: 30752560 660095



OC100123LT - 100ft. 12/3 SJTW Yellow Extension Cord

Features

- Water Resistant
- Flame Retardant
- Ultra Flexible
- Corrosion Resist Blades
- Lighted Ends

Specifications

- **Length (ft):** 100
- **Color:** Yellow
- **Gauge:** 12/3
- **Wire Type:** SJTW
- **Certifications:** UL or equivalent
- **Electrical Ratings:** 15A/ 125V/ 1625W
- **Product Packaging:** Sleeve
- **Unit Measurement (DxWxH):** 3x9x15.5
- **Unit Weight (lbs):** 14.5
- **Master Carton Type:** Brown Box
- **Master Carton Measurements:** 18.25x17.3x6.75
- **Master Carton Weight (lbs):** 60.6
- **Master Carton Qty:** 4

Unit UPC: 752560 660100
Master Carton UPC: 30752560 660101



BERGEN INDUSTRIES, INC.

R628104 - 4ft. 6/2 & 8/1 SRDT Gray 50Amp Range Cord

Features

- Cord includes strain relief kit
- 3-wire cord fits more homes built prior to 1996
- Ring terminals for secure connection



Specifications

Length (ft):	4
Color:	Gray
Gauge:	6/2 & 8/1
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.30 x 3.90 x 13.00
Unit Weight (lbs):	1.81
Master Carton Type:	Brown-Box
Master Carton Measurements (DxWxH):	14.43 x 8.84 x 7.37
Master Carton Weight (lbs):	19.61
Master Carton Pack Quantity:	10
Master Carton Cube (cu. ft.):	0.54

Unit UPC: 752560 881000
Master Carton UPC: 50752560 881005

R628106 - 6ft. 6/2 & 8/1 SRDT Gray 50Amp Range Cord

Features

- Cord includes strain relief kit
- 3-wire cord fits more homes built prior to 1996
- Ring terminals for secure connection



Specifications

Length (ft):	6
Color:	Gray
Gauge:	6/2 & 8/1
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.00 x 5.75 x 12.00
Unit Weight (lbs):	2.51
Master Carton Type:	Brown-Box
Master Carton Measurements (DxWxH):	13.43 x 8.89 x 9.05
Master Carton Weight (lbs):	21.75
Master Carton Pack Quantity:	8
Master Carton Cube (cu. ft.):	0.63

Unit UPC: 752560 881017
Master Carton UPC: 50752560 881012

RANGE CORDS 3-WIRE

BERGEN INDUSTRIES, INC.

R628204 - 4ft. 6/2 & 8/2 SRDT Black 50Amp Range Cord

Features

- Cord includes strain relief kit
- 4-wire cord fits most homes built after 1996
- Ring terminals for secure connection



Specifications

Length (ft):	4
Color:	Black
Gauge:	6/2 & 8/2
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.75 x 5.00 x 13.00
Unit Weight (lbs):	2.36
Master Carton Type:	Brown-Box
Master Carton Measurements (DxWxH):	14.43 x 8.40 x 11.27
Master Carton Weight (lbs):	20.82
Master Carton Pack Quantity:	8
Master Carton Cube (cu. ft.):	0.79

Unit UPC: 752560 881024

Master Carton UPC: 50752560 881029

R628205 - 5ft. 6/2 & 8/2 SRDT Black 50Amp Range Cord

Features

- Cord includes strain relief kit
- 4-wire cord fits most homes built after 1996
- Ring terminals for secure connection



Specifications

Length (ft):	5
Color:	Black
Gauge:	6/2 & 8/2
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.75 x 5.00 x 13.00
Unit Weight (lbs):	2.89
Master Carton Type:	Brown-Box
Master Carton Measurements (DxWxH):	14.43 x 6.04 x 11.27
Master Carton Weight (lbs):	18.91
Master Carton Pack Quantity:	6
Master Carton Cube (cu. ft.):	0.57

Unit UPC: 752560 881031

Master Carton UPC: 50752560 881036

RANGE CORDS 4-WIRE

BERGEN INDUSTRIES, INC.

D100304 - 4ft. 10/3 SRDT Gray 30Amp Dryer Cord

Features

- Cord includes strain relief kit
- 3-wire cord fits more homes built prior to 1996
- Ring terminals for secure connection



Specifications

Length (ft):	4
Color:	Gray
Gauge:	10/3
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	0.90 x 3.10 x 13.00
Unit Weight (lbs):	1.12
Master Carton Type:	Bin-Box
Master Carton Measurements (DxWxH):	14.43 x 7.24 x 7.37
Master Carton Weight (lbs):	12.51
Master Carton Pack Quantity:	10
Master Carton Cube (cu. ft.):	0.45

Unit UPC: 752560 880010
Master Carton UPC: 50752560 880015

D100306 - 6ft. 10/3 SRDT Gray 30Amp Dryer Cord

Features

- Cord includes strain relief kit
- 3-wire cord fits more homes built prior to 1996
- Ring terminals for secure connection



Specifications

Length (ft):	6
Color:	Gray
Gauge:	10/3
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.15 x 3.50 x 13.00
Unit Weight (lbs):	1.51
Master Carton Type:	Bin-Box
Master Carton Measurements (DxWxH):	14.43 x 8.04 x 7.37
Master Carton Weight (lbs):	15.61
Master Carton Pack Quantity:	10
Master Carton Cube (cu. ft.):	0.49

Unit UPC: 752560 880027
Master Carton UPC: 50752560 880022

DRYER CORDS 3-WIRE

BERGEN INDUSTRIES, INC.

DRYER CORDS 4-WIRE

D100404 - 4ft. 10/4 SRDT Black 30Amp Dryer Cord

Features

- Cord includes strain relief kit
- 4-wire cord fits most homes built after 1996
- Ring terminals for secure connection



Unit UPC: 752560 880034

Master Carton UPC: 50752560 880039

Specifications

Length (ft):	4
Color:	Black
Gauge:	10/4
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.50 x 5.00 x 13.00
Unit Weight (lbs):	1.58
Master Carton Type:	Bin-Box
Master Carton Measurements (DxWxH):	14.43 x 11.04 x 8.92
Master Carton Weight (lbs):	17.83
Master Carton Pack Quantity:	10
Master Carton Cube (cu. ft.):	0.82

D100405 - 5ft. 10/4 SRDT Black 30Amp Dryer Cord

Features

- Cord includes strain relief kit
- 4-wire cord fits most homes built after 1996
- Ring terminals for secure connection



Unit UPC: 752560 880041

Master Carton UPC: 50752560 880046

Specifications

Length (ft):	5
Color:	Black
Gauge:	10/4
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.50 x 5.00 x 13.00
Unit Weight (lbs):	1.83
Master Carton Type:	Bin-Box
Master Carton Measurements (DxWxH):	14.43 x 8.40 x 10.65
Master Carton Weight (lbs):	16.51
Master Carton Pack Quantity:	8
Master Carton Cube (cu. ft.):	0.75

D100406 - 6ft. 10/4 SRDT Black 30Amp Dryer Cord

Features

- Cord includes strain relief kit
- 4-wire cord fits most homes built after 1996
- Ring terminals for secure connection



Unit UPC: 752560 880058

Master Carton UPC: 50752560 880053

Specifications

Length (ft):	6
Color:	Black
Gauge:	10/4
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.50 x 5.00 x 13.00
Unit Weight (lbs):	2.24
Master Carton Type:	Bin-Box
Master Carton Measurements (DxWxH):	14.43 x 6.04 x 10.10
Master Carton Weight (lbs):	14.89
Master Carton Pack Quantity:	6
Master Carton Cube (cu. ft.):	0.51

BERGEN INDUSTRIES, INC.

GARBAGE DISPOSAL CORDS



PS16303R - 3ft. 16/3 SPT-3 Gray Garbage Disposal Cord w/ Right Angle Plug

Features

- 13A/ 125V/ 1625W
- 3 Conductor SPT-3 Wire
- Right Angle U-Ground Plug

Unit UPC: 752560 882007

Master Carton UPC: 50752560 882002

Specifications

- Length (ft): 3
- Color: Gray
- Gauge: 16/3
- Wire Type: SPT-3
- Certifications: UL or equivalent
- Product Packaging: Sleeve
- Master Carton Pack Quantity: 60



PS16306R - 6ft. 16/3 SPT-3 Gray Garbage Disposal Cord w/ Right Angle Plug

Features

- 13A/ 125V/ 1625W
- 3 Conductor SPT-3 Wire
- Right Angle U-Ground Plug

Unit UPC: 752560 882021

Master Carton UPC: 50752560 882026

Specifications

- Length (ft): 6
- Color: Gray
- Gauge: 16/3
- Wire Type: SPT-3
- Certifications: UL or equivalent
- Product Packaging: Sleeve
- Master Carton Pack Quantity: 40



PS16303 - 3ft. 16/3 SPT-3 Gray Garbage Disposal Cord w/ Straight Plug

Features

- 13A/ 125V/ 1625W
- 3 Conductor SPT-3 Wire
- U-Ground Plug

Unit UPC: 752560 882014

Master Carton UPC: 50752560 882019

Specifications

- Length (ft): 3
- Color: Gray
- Gauge: 16/3
- Wire Type: SPT-3
- Certifications: UL or equivalent
- Product Packaging: Sleeve
- Master Carton Pack Quantity: 60



PS16306 - 6ft. 16/3 SPT-3 Gray Garbage Disposal Cord w/ Straight Plug

Features

- 13A/ 125V/ 1625W
- 3 Conductor SPT-3 Wire
- U-Ground Plug

Unit UPC: 752560 882038

Master Carton UPC: 50752560 882033

Specifications

- Length (ft): 6
- Color: Gray
- Gauge: 16/3
- Wire Type: SPT-3
- Certifications: UL or equivalent
- Product Packaging: Sleeve
- Master Carton Pack Quantity: 40