

## The Next Generation of Fittings

# SPEC-flexconnectors<sup>TM</sup>





Does NOT Restrict and Reduce Conduit ID Like "Screw In" Styles

The Only Connector that Easily Installs ON FMC WITHOUT a Tool!

## TURN IT ON with SPEC-flexconnectors

1/2", 3/4", 1" Trade Sizes
Available in Aluminum or Zinc Plated Steel

AMERICAN FITTINGS
Corporation
800 221 5268

Since 1946

800.221.5268 americanfittingscorp.com

Fair Lawn, New Jersey

Saves Labor on Every Connection
No Screw or Crimp Required to Install
Simply, Turn It On Your FMC
No Screws to Pinch or Pierce Conduit
Maintains Full Integrity of the Conduit
Exceeds UL Pullout Requirements by 300%
Fully-Machined Solid Steel or Aluminum
Count-On a Safe Burr-less Wire Pull
Connects to Box with Furnished Locknut
Available With & Without Insulated Throat
Adapter Available for FMC to Rigid Pipe or EMT

Made in the USA

© 2013 AMERICAN FITTINGS

Made in the USA Since 1946

### SPEC-flexconnectors Installs On FMC with a

Industrial Specfication Grade Connector Fittings for Flexible Metal Conduit




Saves Labor on Every Connection
No Screw or Crimp Required to Install
No Screws to Pinch or Pierce Conduit
NOT a Thin Wall Die Cast Fitting
Maintains Full Integrity of Conduit ID & OD
Count-On a Safe Burr-less Wire Pull
Allows More Room Inside Conduit For Wire
Exceeds UL Pullout Requirements by 300 %
Fully-Machined Solid Steel or Aluminum



Industrial Grade Locknut Furnished Adapters Available to Connect FMC to Rigid Pipe or EMT

Made in the USA Full USA Material Certs for ARRA and Buy American Act



#### Fitting Without Insulated Throat

Cat #	Trade Size	Material	Α	В	С	D
FLX50	1/2"	Steel*	1 5/32"	1 1/8"	1 9/16"	1"
FLX50AL	1/2"	Aluminum	1 5/32"	1 1/8"	1 9/16"	1"
FLX75	3/4"	Steel*	1 7/16"	1 3/8"	1 9/16"	1"
FLX75AL	3/4"	Aluminum	1 7/16"	1 3/8"	1 9/16"	1"
FLX100	1"	Steel*	1 11/16"	1 5/8"	1 5/8"	1"
FLX100AL	1"	Aluminum	1 11/16"	1 5/8"	1 5/8"	1"

Fitting With Insulated Throat - B added to Cat #

Cat #	Trade Size	Material	Α	В	С	D
FLX50B	1/2"	Steel *	1 5/32"	1 1/8"	1 9/16"	1"
FLX50BAL	1/2"	Aluminum	1 5/32"	1 1/8"	1 9/16"	1"
FLX75B	3/4"	Steel *	1 7/16"	1 3/8"	1 9/16"	1"
FLX75BAL	3/4"	Aluminum	1 7/16"	1 3/8"	1 9/16"	1"
FLX100B	1"	Steel *	1 11/16"	1 5/8"	1 5/8"	1"
FLX100BAL	1"	Aluminum	1 11/16"	1 5/8"	1 5/8"	1"

Consult Factory for Sizes Not Shown

\* Steel is Zinc Plated for Full Corrosion Resistance

americanfittingscorp.com