



The Leviton Load Center

The Complete Package



The Complete Package

From the size of the enclosure to the selection of individual circuit breakers and accessories, Leviton guarantees quality materials and adherence to the highest standards of manufacturing for years of reliable service.

LOAD CENTERS | 1-phase, 3-wire, 120/240 VAC, 22kA short-circuit rating



NEMA 1 - Indoor

Amp Rating	# of Spaces/ Circuits	Enclosure Catalog Number*	Flush/Surface Mount Standard	Cover & Door Assembly with Observation Window
Main Breaker Factory Installed				
100	20	LP210-MB	LDC20	LDC20-W
125	20	LP212-MB	LDC20	LDC20-W
150	20	LP215-MB	LDC20	LDC20-W
200	20	LP220-MB	LDC20	LDC20-W
100	30	LP310-MB	LDC30	LDC30-W
125	30	LP312-MB	LDC30	LDC30-W
150	30	LP315-MB	LDC30	LDC30-W
200	30	LP320-MB	LDC30	LDC30-W
150	42	LP415-MB	LDC42	LDC42-W
200	42	LP420-MB	LDC42	LDC42-W
225	42	LP422-MB	LDC42	LDC42-W
Main Lugs Only				
125	20	LP212-ML	LDC20	LDC20-W
200	30	LP320-ML	LDC30	LDC30-W
225	42	LP422-ML	LDC42	LDC42-W

* Order Cover & Door Assembly separately



NEMA 3R - Outdoor

Amp Rating	# of Spaces/ Circuits	Catalog Number
Main Breaker Factory Installed		
100	20	LP210-3B
125	20	LP212-3B
200	20	LP220-3B
150	30	LP315-3B
200	30	LP320-3B
200	42	LP420-3B
225	42	LP422-3B
Main Lugs Only		
125	20	LP212-3L
200	30	LP320-3L
225	42	LP422-3L



Meter Main, OH/UG Service Entrance with Distribution Section and Feed-Through Lugs

Amp Rating	# of Spaces/ Circuits	Catalog Number	Bypass	Cover
150	8	LP815-MC*	None	Ringless
200	8	LP820-MC*	None	Ringless
150	8	LP815-HMC	Horn	Ringless
200	8	LP820-HMC	Horn	Ringless
150	8	LP815-LMC*	Lever	Ringless
200	8	LP820-LMC*	Lever	Ringless
150	8	LP815-5MC*	Lever with 5th Jaw Installed	Ringless
200	8	LP820-5MC*	Lever with 5th Jaw Installed	Ringless
150	8	LP815-RMC	None	Ring Type
200	8	LP820-RMC	None	Ring Type

* Meter Equipment Group (MEG) Approved



Meter-Load Center Combination, All-in-one, UG Service Entrance, EUSERC

Amp Rating	# of Spaces	Catalog Number	Bypass	Cover
150	30	LP315-MC	None	Ring Type
200	30	LP320-MC	None	Ring Type
200	42	LP420-MC	None	Ring Type

BRANCH CIRCUIT BREAKERS | Hydraulic-magnetic trip, 120/240 VAC, 10kA short-circuit rating*



Standard

Amp Rating	1-Pole	2-Pole
15	LB115	LB215
20	LB120	LB220
25	LB125	LB225
30	LB130	LB230
35	-	LB235
40	-	LB240
45	-	LB245
50	-	LB250
60	-	LB260
70	-	LB270
80	-	LB280
90	-	LB290
100	-	LB200
110	-	LB211
125	-	LB212



AFCI

Amp Rating	1-Pole
15	LB115-AF
20	LB120-AF



AFCI/GFCI - Dual Function

Amp Rating	1-Pole
15	LB115-DF
20	LB120-DF



GFCI - 5 mA Ground Fault Protection of Personnel

Amp Rating	1-Pole	2-Pole
15	LB115-GF	LB215-GF
20	LB120-GF	LB220-GF
25	LB125-GF	LB225-GF
30	LB130-GF	LB230-GF
40	-	LB240-GF
50	-	LB250-GF
60	-	LB260-GF



GFPE - 30 mA Ground Fault Protection of Equipment

Amp Rating	1-Pole	2-Pole
15	LB115-EP	LB215-EP
20	LB120-EP	LB220-EP
25	LB125-EP	LB225-EP
30	LB130-EP	LB230-EP
40	-	LB240-EP
50	-	LB250-EP
60	-	LB260-EP

* Series Rated 22kA with Leviton main circuit breaker; see Series Ratings Tables for additional Ratings

MAIN CIRCUIT BREAKERS | Hydraulic-magnetic trip, 120/240 VAC, 22kA short-circuit rating



Amp Rating	2-Pole
100	LM100
125	LM125
150	LM150
200	LM200
225	LM225

ACCESSORIES

Locking & Latching Devices



Description	Catalog Number
Handle padlock device for branch circuit breakers	LBHPL
Handle padlock device for main circuit breakers	LMHPL
Door locking latch kit for indoor load centers	LDRLK
Door latch kit without lock for indoor load centers	LDRLA

Lugs, Ground and Neutral Bar Kits



Description	Catalog Number
Field-installable main & pass-thru lugs, 6 - 300	LL630
Ground lug, 6 - 2/0	LLGND
Neutral lug, 6 - 300	LLNLT
Phase/neutral load side lug, 14 - 4	LLPHN
Ground bar kit, 11 positions, 14 - 4	LGBKT
Neutral bar kit, 14 - 1/0	LNBKT

Outdoor & Meter Combination Load Center Accessories



Description	Catalog Number
Conduit hub, 1"	LHUB1
Conduit hub, 2 1/2"	LHUB2
Closing plate	LCLPT
5th Jaw	L5JAW
5th Jaw with neutral	L5JAW-N
Ground connector	LGDMC
Sealing ring	LRING

Miscellaneous



Description	Catalog Number
Manual transfer interlock kit	LITLK
Angle iron bracket for flush mount load centers	LBRKT
Circuit Identification Sticker (qty. 5)	LSTIK
Filler Plates (qty. 10)	LFPLT
Terminal covers for main circuit breaker	LTCVR
Bonding strap kit	LPBSK
Cover screw kit (qty. 6)	LDCSK

Leviton Manufacturing Co., Inc. Global Headquarters

201 North Service Road, Melville, NY 11747-3138

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line: 1-800-824-3005

Mon-Fri 8am-10pm EST, Saturday 9am-7pm EST

Visit our Website at: www.levitonloadcenter.com

© 2018 Leviton Manufacturing Co., Inc. All rights reserved.

