

**BURNDY® BURNDYWeld® Accessories**



**BURNDY® BURNDYWeld® Cable Cleaning Brush**

Recommended for cleaning heavily oxidized cables

- V-shape brushes clean a wide range of cable sizes
- Handle holds two stiff wire bristle brushes
- Brushes are rotatable for longer life

WESCO Part No.	Mfr.'s Model No.
781810-40324	B38013500

**BURNDY® BURNDYWeld® Handle Clamps**

WESCO Part No.	Mfr.'s Model No.	Description
781810-40259	B106	Handle Clamp — for Molds Having a Price Key 4, 7, 17, 22, or 24
781810-40260	B107	Handle Clamp — for Molds Having a Price Key 5, 6, 8, or 23

**BURNDY® BURNDYWeld® Card Cloth Brush**

For cleaning large conductors and bus bar

- Features short stiff bristles
- For cable only; do not use on molds

WESCO Part No.	Mfr.'s Model No.
781810-40329	B38030600

**BURNDY® BURNDYWeld® Packing Materials**

Necessary when making BURNDYWeld® connections to rebar

- Special, patented cooper wool — bag has enough to handle 40 to 50 connections
- Ceramic fiber material — enough for one connection only

WESCO Part No.	Mfr.'s Model No.
<b>Copper Wool</b>	
781810-40351	B38406000
<b>Ceramic Fiber Pad for Rebar Connection</b>	
781810-40352	B38406100
781810-40353	B38406200
781810-40354	B38406300
781810-40355	B38406400

**BURNDY® BURNDYWeld® Gloves**

WESCO Part No.	Mfr.'s Model No.
781810-40382	B38485500

**BURNDY® BURNDYWeld® Duct Seal**

Prevents molten weld metal from leaking out of mold

- Can be used to prolong mold use
- Also used around 7-strand cable to prevent leaking

WESCO Part No.	Mfr.'s Model No.	Size
781810-40356	B38412900	1-lb. Package
781810-40357	B38412905	5-lb. Package

**BURNDY® BURNDYWeld® Mold Cleaners**

Use to clean slag from molds that are not split through the crucible

WESCO Part No.	Mfr.'s Model No.	Description
781810-40401	B40031901	For Cartridge Sizes #15-#65
781810-40402	B40031903	For Cartridge Sizes #90-#500

**BURNDY® BURNDYWeld® Weld Metal**

WESCO Part No.	Mfr.'s Model No.	Description
<b>Weld Metal</b>		
781810-40228	15	#15 Weld Metal — Standard Cartridge
781810-40236	25	#25 Weld Metal — Standard Cartridge
781810-40242	32	#32 Weld Metal — Standard Cartridge
781810-40246	45	#45 Weld Metal — Standard Cartridge
781810-40252	65	#65 Weld Metal — Standard Cartridge
781810-40256	90	#90 Weld Metal — Standard Cartridge
781810-40225	115	#115 Weld Metal — Standard Cartridge
781810-40229	150	#150 Weld Metal — Standard Cartridge
781810-40234	200	#200 Weld Metal — Standard Cartridge
781810-40237	250	#250 Weld Metal — Standard Cartridge
781810-40250	500	#500 Weld Metal — Standard Cartridge
<b>Steel Discs</b>		
781810-40315	B37032001	¾" Steel Discs — 15-65 Weld Metal
781810-40316	B37032002	1" Steel Discs — 90-115 Weld Metal
781810-40317	B37032003	1½" Steel Discs — 150-500 Weld Metal

**BURNDY® BURNDYWeld® Tools**

WESCO Part No.	Mfr.'s Model No.	Description
781810-40326	B38030200	Tool Kit — Includes: Flint Igniter, 8" File, Crimping Tool, Mold Cleaning Brush, 6" Screwdriver, Wire Brush, and Card Cloth Brush
781810-40332	B38030900	Flint Igniter — Used to Ignite Starting Powder
781810-40333	B38030901	Replacement Flints
781810-43040	B38090400	36" Flint Extension
781810-40328	B38030500	Wire Brush

**BURNDY® BURNDYWeld® Vertical Magnetic Clamps**

Use to hold a mold in position on a vertical steel surface

WESCO Part No.	Mfr.'s Model No.	Fits Molds with Price Key	For Use with Weld Types
<b>Magnetic Clamps with B106 Handle</b>			
781810-40406	B40443100	4 and 17	BCS-3, 4, 7, and 23

**BURNDY® BURNDYWeld® Vertical Chain Clamp**

Holds a mold in position on vertical pipe up to 4" in diameter

WESCO Part No.	Mfr.'s Model No.	Fits Molds with Price Key	For Use with Weld Types
<b>B106 Handle Clamp with Vertical Chain</b>			
781810-40397	B10632	4, 17, 22, and 24	BCS-3, 4, 7, 23, and BCRC-6

**BURNDY® BURNDYWeld® Black Case Sales Kit**

WESCO Part No.	Mfr.'s Model No.
781810-98998	BWSALESKIT

**BURNDY® BURNDYWeld® Natural Bristle Brush**

- Use to clean mold between shots

WESCO Part No.	Mfr.'s Model No.
781810-40349	B38392200

**BURNDY® BURNDYWeld® Offset Copper Lugs**

Designed for use with BCB-1 Type Molds

- Made from electrolytic grade copper bar stock

WESCO Part No.	Mfr.'s Model No.	Lug Size	No. of Bolt Holes	Size T	W
781810-40364	B38415800	¼ x 1	2	½	¼ 1
781810-40366	B38416400	¼ x 1½	2	½	¼ 1½

**BURNDY® BURNDYWeld® Shim Stock**

- Copper construction
- 0.0108" x 1½" x 3"

WESCO Part No.	Mfr.'s Model No.	Pkg. Qty.
781810-40337	B38032900	100 Pieces per Box

Termination, Tape, Splicing, & Marking

