

OFL LED

Floodlights

Value Without Compromise

The OFL LED floodlights from Lithonia Lighting deliver the best value in lighting, from a brand you can trust. Superior performance and robust design make this product suitable for any general purpose floodlighting application.

Performance You Can Trust

Delivering up to 16,900 lumens, the OFL LED floodlights are the ideal solution to replace up to 400W metal halide floodlights. An integral visor minimizes high-angle glare and directs the light where it needs to go, further reducing unwanted spill light.

Built to Last

The OFL LED is built to last, with an expected service life of over 13 years. The robust die-cast aluminum housing can withstand the elements and rigors of daily use. The engineered, thermal vent between the LEDs and the other electrical components help keep temperatures low, which further extends the life of the product.

Readily Available Stock

Getting the product to the job site quickly is key. The OFL LED floodlights are stocked in all five Acuity Brands distribution centers, in all configurations.



OFL1 with
Knuckle Mount

OFL2 with
Slipfitter Mount



Quick Facts:

- Replaces 70W – 400W MH
- Lumen packages from 2,200–16,900 lumens
- Input watts from 21W–151W
- Knuckle, yoke or slipfitter mounting options available
- Wire guard and vandal guard accessories available
- Available in 4000K or 5000K CCT

OFL LED Floodlight

Ordering Information

EXAMPLE: OFL1 LED P1 40K MVOLT THK DDBXD

OFL Series					
Series	Performance Package	Color Temperature (CCT)	Voltage	Mounting	Finish
OFL1 LED	P1	40K (4000K)	MVOLT	THK (Knuckle Mount)	DDBXD (Dark Bronze)
	P2	50K (5000K)		YK (Yoke Mount)	
OFL2 LED	P2	40K (4000K)	MVOLT	IS (Slipfitter Mount)	DDBXD (Dark Bronze)
	P3	50K (5000K)		347V YK (Yoke Mount)	

See the spec sheet on www.acuitybrands.com for full ordering information.

Model	OFL1 (4000K)		OFL2 (4000K)	
Performance Package	P1	P2	P2	P3
Metal Halide Replacement	70W - 100W	150W	250W	400W
Lumens	2,295	4,450	12,280	16,900
Input Watts	21W	45W	114W	151W
LPW	109	99	112	108

OFL Accessories



Wire Guard
OFL1WG or OFL2WG



Vandal Guard
OFL1VG or OFL2VG



Slipfitter Attachment for OFL1
DSXF1/2TS

OFL Mounting Options



OFL1 with Knuckle Mount



OFL1 with Yoke Mount



OFL2 with Slipfitter Mount



OFL2 with Yoke Mount

Visit www.lithonia.com for more information