



LEANSAFE™

300lbs TYPE IA

Load Capacity

Duty Rating



NEW



Designed to lean up against walls, corners, studs, and poles



Single latch locks the rear rail to the front rail to keep the ladder in leaning mode



Curved non-marring foot pad is designed to maximize surface contact with the ground in both standard stepladder mode & leaning mode.



LEANSAFE™

Standard Stepladders shouldn't be leaned against a wall, but the new Werner LEANSAFE™ ladder is designed specifically with features to safely lean against a wall, stud, corner, or pole.



Non-Marring Rubber Bumper Pad

Dropped Rail Pivot Point

Full Aluminum Bracing

Seven-Layer Fiberglass Construction

Secure Rail Latch

Model L6206

EDGE 360

Different Rail Color for Safety

★★★★ **300** lbs. LOAD CAPACITY

Combined Weight of User and Materials
Type IA Duty Rating

FIBERGLASS

For working around electricity
Non-conductive side rails

Standard Features

- Solid rivets
- Rear horizontals every 12"
- Every step is knee braced
- Internal spreaders
- EDGE360® bracing

SPECIFICATIONS

Model No.	Size	Stepladder Mode		Leaning Mode	
		Max. Standing Height	Max. Reach Height	Max. Standing Height	Max. Reach Height
L6204	4'	1'-8"	8'-4"	10"	7'-3"
L6206	6'	3'-10"	10'	2'-10"	9'
L6208	8'	5'-9"	12'	4'-9"	11'
L6210	10'	7'-8"	14'	6'-8"	13'
L6212	12'	9'-7"	16'	8'-7"	15'

*assumes a 5'-6" person with a vertical 12" reach

www.wernerco.com/us

WERNER CO. CORPORATE HEADQUARTERS: 93 Werner Rd., Greenville, PA 16125-9499
TEL: 888-523-3370 FAX: (724) 588-0315 www.wernerco.com



LEANSAFE™

Part Number	Description	All Models Affected
38-38	Top Replacement Kit	L6204,L6206, L6208, L6210, L6212, L7304, L7306, L7308, L7310, L7312
27-97	Spreader Replacement Kit	L6204,L6206, L7304,L7306
27-98	Spreader Replacement Kit	L6208, L7308
27-99	Spreader Replacement Kit	L6210, L7310
27-100	Spreader Replacement Kit	L6212, L7312
21-53	Foot Replacement Kit	L6204, L6206, L6208, L6210, L6212, L7304, L7306, L7308, L7310, L7312
36-113	Latch Replacement Kit	L6204, L6206, L6208, L6210, L6212, L7304, L7306, L7308, L7310, L7312
LFL100	L6200/L7300 Series Label Replacement Kit	L6204, L6206, L6208, L6210, L6212, L7304, L7306, L7308, L7310, L7312
25-30	End Cap Replacement Kit	L6204, L6206, L6208, L6210, L6212, L7304, L7306, L7308, L7310, L7312

www.wernerco.com/us

WERNER CO. CORPORATE HEADQUARTERS: 93 Werner Rd., Greenville, PA 16125-9499
TEL: 888-523-3370 FAX: (724) 588-0315 www.wernerco.com