

## UL-APPROVED ADJUSTABLE RINGS

### PRODUCT FEATURES

- ▶ Can be adjusted on the jobsite for a quick installation
- ▶ Adjusts to achieve a flush finish every time
- ▶ Patented design provides strong electrical and mechanical connections to meet UL requirements
- ▶ \*For Fixture/Luminaire Support of 50 lbs or less

**INDUSTRY'S ONLY  
UL LISTED**

**4-11/16" SQ.  
ADJ. RINGS**

Cat. No.	Description	Adjustability Range	Std. Pkg.
<b>4AR1G-58</b> <span style="background-color: yellow; border: 1px solid black; border-radius: 50%; padding: 2px;">NEW</span>	1-Gang Adjustable Ring for 4" Square Boxes	5/8" to 1-1/4"	25
<b>4AR1G-34</b> <span style="background-color: yellow; border: 1px solid black; border-radius: 50%; padding: 2px;">NEW</span>	1-Gang Adjustable Ring for 4" Square Boxes	3/4" to 1-1/2"	25
<b>4AR2G-58</b> <span style="background-color: yellow; border: 1px solid black; border-radius: 50%; padding: 2px;">NEW</span>	2-Gang Adjustable Ring for 4" Square Boxes	5/8" to 1-1/2"	25
<b>5AR1G-58</b> <span style="background-color: yellow; border: 1px solid black; border-radius: 50%; padding: 2px;">NEW</span>	1-Gang Adjustable Ring for 4-11/16" Square Boxes	5/8" to 1-1/4"	25
<b>5AR2G-58</b> <span style="background-color: yellow; border: 1px solid black; border-radius: 50%; padding: 2px;">NEW</span>	2-Gang Adjustable Ring for 4-11/16" Square Boxes	5/8" to 1-1/2"	25
<b>*4ARR-34</b> <span style="background-color: yellow; border: 1px solid black; border-radius: 50%; padding: 2px;">NEW</span>	Round Adjustable Ring for 4" Square Boxes	3/4" to 1-1/2"	25
<b>3GAR-34</b> <span style="background-color: yellow; border: 1px solid black; border-radius: 50%; padding: 2px;">NEW</span>	3-Gang Adjustable Ring	3/4" to 1-1/2"	25

NEW



4AR1G-58

NEW



4AR1G-34

NEW



4AR2G-58

NEW



5AR1G-58

NEW



5AR2G-58

NEW



\* 4ARR-34

NEW



3GAR-34

## 4" SQUARE (4S) BOXES LOW-VOLTAGE PARTITIONS

- ▶ Not compatible with Adj. Rings

Cat. No.	Description	For Use with 2-Gang Rings:	Std. Pkg.
<b>4SP-100</b>	For Use With 1-1/2" Deep Boxes	Flat, 1/4", 1/2", 3/4", 1"	25
<b>4SP-200</b>	For Use With 1-1/2" Deep Boxes	5/8", 1-1/4", 1-1/2", 1-3/4", 2"	25
<b>4SDP-100</b>	For Use With 2-1/8" Deep Boxes	Flat, 1/4", 1/2", 3/4", 1"	25
<b>4SDP-200</b>	For Use With 2-1/8" Deep Boxes	5/8", 1-1/4", 1-1/2", 1-3/4", 2"	25



4SP-100



4SP-200



4SDP-100



4SDP-200