





problem fixed




EZPath®
RETROFIT DEVICE

instant compliance
FOR OVERFILLED SLEEVES





Don't stress out
about deficient overfilled sleeves!*



Shown with optional mounting hardware
included for flush mount installations.

EZPath®
RETROFIT DEVICE


Restores compliance
instantly!

* For use with sleeves from 50% to 100% visual fill.

Compliance is as easy as

WRAP

1




- ▶ Device wraps around existing condition



Single sleeves

SECURE

2




- ▶ Intumescent foam surrounds cables




Multiple sleeves

TIGHTEN

3



- ▶ Compliance is restored



Flush mount sleeves

- ▶ No deficiencies
- ▶ No fines
- ▶ No headaches
- ▶ No hassles

Rapid Remediation

The **NEW EZ-Path® Retrofit Device** is engineered for quick and easy installation. It instantly transforms overfilled sleeves to compliance in seconds.


The two-piece split device simply wraps around the cable bundle and extended sleeve. It can even accommodate an existing conduit bushing.

Once the device is secured, existing firestop materials can be left in place and the cable sleeve can remain active. Cables can be added up to 100% visual fill or removed down to 50% visual fill while still maintaining ongoing compliance.




new!

EZ-Path® RETROFIT DEVICE



Available in two convenient sizes to fit 2" and 4" trade size EMT or rigid metallic conduit sleeves.

► Firestopping
intumescent
built-right-in



Patent Pending

Transforms pre-existing deficiencies into
100% COMPLIANCE



- Easy to install and nothing to maintain
- No additional firestopping required
- For use with 50%-100% cable fill
- Works with extended or flush mount sleeves
- Attaches directly to sleeve or use optional mounting tabs included for barrier attachment
- Sold in pairs for installation on both sides of a wall
- Also approved for floor applications

Ordering Information

UPC # 730573	CAT. NO.	DESCRIPTION	QTY.	CASE QTY.	WEIGHT (Each)
00200	EZDR200	EZ-Path® Retrofit Device for 2" (2-3/16" or 2-3/8" O.D.) Sleeves - 1 pair	1	4	2.721 lbs (1.2 kg)
00201	EZPR150	EZDR200 Adapter Plate for 1.5" Sleeves - 1 pair	1	4	0.75 lbs. (0.34 kg)
00400	EZDR400	EZ-Path® Retrofit Device for 4" (4-1/2" O.D.) Sleeves - 1 pair	1	4	4.632 lbs (2.1 kg)
00401	EZPR300	EZDR400 Adapter Plate for 3" Sleeves - 1 pair	1	4	1.25 lbs. (0.57 kg)

Discover the entire family of

EZ-Path®
RATED & NON-RATED PATHWAYS



Fire and Smoke Rated Pathways

Smoke Rated Pathways



Specified Technologies Inc. stifirestop.com

For more information visit www.stifirestop.com/ez-path/retrofit
or to contact your local sales representative at 800-992-1180

ZSTI3463 - 2137



Scan to learn
more about **EZDR400 & 200**