

DAP® HIGH HEAT MORTAR



For firestopping at openings around vents, pipes, ducts, chimneys, in wood frame construction, also for patching fireplaces and wood-burning stoves. Withstands temperatures up to 2000°F. Non-combustible. ASTM E-136 rated.

STOCK NO.	UPC NO.	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
WDHM10	71233	10.1 oz. - Black	1.25	1	6.53/ea

DAP® DOW CORNING® SILICONE SEALANT



Protect and seal with 100% silicone rubber. Waterproof and flexible. Non-paintable. 50 year manufacturer durability guarantee. Meets ASTM C-920, Class 25, Type S, Grade NS.

STOCK NO.	UPC NO.	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
WDSC10	71234	Clear - 10.1 oz.	.86	1	12.50/ea
WDSW10	71235	White - 10.1 oz.	.78	1	12.78/ea
WDSG10	71238	Gray - 10.1 oz.	.78	1	12.78/ea

DAP® ALEX PLUS® EASY CAULK



Packaged in a convenient, easy-to-use aerosol can. Eliminates the need for a caulk gun, delivers a smooth and consistent bead with no messy overflow. Ideal for use in tight spaces and for smaller jobs either indoors or outdoors.

STOCK NO.	UPC NO.	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
WDEC16	71236	16 oz. - White	1.09	1	14.88/ea

DAP® BEATS THE NAIL® CONSTRUCTION ADHESIVE



For general construction, remodeling, maintenance and repair projects. Provides a high-strength, heat and water resistant bond to a variety of substrates. Meets ASTM Specification C 557. For interior/exterior use.

STOCK NO.	UPC NO.	DESCRIPTION	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
WDN1	71240	10.3 oz. - Gray	1.04	1	5.98/ea
WDN2	71241	29 oz. - Gray	2.96	1	16.98/ea

DAP® is a registered trademark
Beats The Nail® is a registered trademark
Dow Corning® is a registered trademark

CAULKING GUN

PISTON ROD WITH DOUBLE FRICTION PLATE
QUICK-RELEASE LEVER

10 oz

32 oz

STOCK NO.	UPC NO.	TUBE SIZE	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
CG1	35020	10 oz.	.90	1	7.55/ea
CG32	35050	32 oz.	1.92	1	36.20/ea