



**GREENLEE®**

A Textron Company

**MADE FOR THE TRADE!™**

**INSULATED HAND  
↑ 1000 V  
TOOLS**

**▲▲▲ 1000 V**

Precision-machined, laser-hardened steel cutting edge for extreme durability.

Ergonomic handles for greater gripping and cutting power or torque.

Heavy-duty, dual-layer insulation and impact-resistant orange coating; rated 1000 V AC.

Forged from alloy steel for durability.




Select Greenlee® Tools are covered by our Limited Lifetime Warranty.

## DID YOU KNOW?

Did you know that more than 30,000 electrical shock accidents occur each year? In fact, electrocution is the fourth leading cause of industrial fatalities after traffic, homicide and construction accidents. It is easy to see why protecting against electrical shock is so important and why there are such high standards placed upon tools and equipment that may come in contact with energized sources.

Be prepared when working on or near potentially energized sources with Greenlee's new assortment of high-quality, insulated tools that exceed ASTM F1505 and IEC 60900 standards. Each insulated tool is designed for safety and built for comfort, featuring a dual-layer of heavy-duty insulation and impact-resistant orange coating.

Select from multiple sizes of insulated lineman's pliers, screwdrivers and nut holding nutdrivers - clearly marked with the industry-standard 1000V icon ( 1000 V) so you can be assured you're working with the best, safest tools for the job at hand.



### *Greenlee's Insulated Screwdrivers are:*

- Rated to 1000V AC and exceed both ASTM and IEC standards.
- Built heavy-duty for longer life.
- Built with precision-machined, black phosphate-plated tips for accurate fastener contact.
- Ergonomically-designed for more comfort and torque.
- Backed by Greenlee's Lifetime Limited Warranty.



### *Greenlee's Insulated Nut Holding Nut Drivers are:*

- Rated to 1000V AC and exceed both ASTM and IEC standards.
- Built heavy-duty for longer life.
- Designed with precision heads and rugged, deep sockets for better screw clearance and fit.
- Ergonomically-designed for more comfort and torque.
- Load nut and tap bottom of handle on any surface to hold. Use a screw to remove the nut.
- Backed by Greenlee's Lifetime Limited Warranty.



### *Greenlee's Insulated Pliers are:*

- High leverage for greater cutting and gripping power.
- Forged from alloy steel for durability.
- Exceed IEC and ASTM standards.
- Safety orange handles provide added visibility and are easily identifiable.
- Two layer insulation provides flame and impact resistance.
- Guards protect hand from accidental contact.

# FROM GREENLEE®... THE BEST JUST GOT BETTER.

## Insulated Hand Tool Kits

### Insulated Screwdriver Kit



### Features

- Helps meet the requirements of OSHA 1910.331-335, NFPA 70E & CSA-Z462.
- Individually tested to 10,000 VAC & rated for 1,000 VAC.
- Dual layer insulation provides added safety and protection against electric shock.

#### Kit Includes:

#1x3" Insulated Screwdriver, #2x4" Insulated Screwdriver, #3x6" Insulated Screwdriver, 1/4"x4" Insulated Cabinet Tip Screwdriver, 3/16"x4" Insulated Cabinet Tip Screwdriver, 3/16"x6" Insulated Cabinet Tip Screwdriver, 3/16"x8" Insulated Cabinet Tip Screwdriver, 5/16"x6" Insulated Cabinet Tip Screwdriver, 3/8"x10" Insulated Cabinet Tip Screwdriver

CAT. NO.	DESCRIPTION
0153-01-INS	9 Piece Insulated Screwdriver Kit

### Insulated Nut Driver Kit



### Features

- Patent pending non-magnetic design – won't collect metal filings, works with stainless steel and brass.
- Helps meet the requirements of OSHA 1910.331-335, NFPA 70E & CSA-Z462.
- Individually tested to 10,000 VAC & rated for 1,000 VAC.
- Dual layer insulation provides added safety and protection against electric shock.
- 6" hollow shaft.

#### Kit Includes:

3/16"x6" Insulated Nut Driver, 1/4"x6" Insulated Nut Driver, 5/16"x6" Insulated Nut Driver, 11/32"x6" Insulated Nut Driver, 3/8"x6" Insulated Nut Driver, 7/16"x6" Insulated Nut Driver, 1/2"x6" Insulated Nut Driver

CAT. NO.	DESCRIPTION
0253-03NH-INS	7 Piece Insulated Nut Driver Kit



### Plier & Screwdriver Kit



### Features

- Helps meet the requirements of OSHA 1910.331-335, NFPA 70E & CSA-Z462.
- Individually tested to 10,000 VAC & rated for 1,000 VAC.
- Dual layer insulation provides added safety and protection against electric shock.

#### Kit Includes:

9" Insulated Side-Cutting Pliers, 8" Insulated Diagonal Cutting Pliers, 8" Insulated Long-Nose Pliers, 10" Insulated Pump Pliers, 3/16"x4" Insulated Cabinet Tip Screwdriver, 1/4"x4" Insulated Cabinet Tip Screwdriver, #2x4" Insulated Phillips Tip Screwdriver

CAT. NO.	DESCRIPTION
0159-01-INS	7 Piece Plier & Screwdriver Kit

## Individual Insulated Hand Tools

### Screwdrivers


- Individually tested to 10,000 VAC & rated for 1,000 VAC.
- Dual layer insulation provides added safety and protection against electric shock.



CAT. NO.	DESCRIPTION
0153-15INS	5/16"x6" Insulated Cabinet Tip Screwdriver
0153-17INS	3/8"x10" Insulated Cabinet Tip Screwdriver
0153-21INS	3/16"x4" Insulated Cabinet Tip Screwdriver
0153-22INS	3/16"x6" Insulated Cabinet Tip Screwdriver
0153-23INS	3/16"x8" Insulated Cabinet Tip Screwdriver
0153-25INS	1/4"x4" Insulated Cabinet Tip Screwdriver
0153-31INS	#1x3" Insulated Screwdriver
0153-33INS	#2x4" Insulated Screwdriver
0153-35INS	#3x6" Insulated Screwdriver

### Nut Holding Nut Drivers

- Exceeds the IEC 60900 and ASTM F1505 standards for insulated tools.
- Patent pending non-magnetic design – won't collect metal filings, works with stainless steel and brass.



CAT. NO.	DESCRIPTION
0253-11NH-INS	3/16"x6" Insulated Nut Driver
0253-12NH-INS	1/4"x6" Insulated Nut Driver
0253-13NH-INS	5/16"x6" Insulated Nut Driver
0253-14NH-INS	11/32"x6" Insulated Nut Driver
0253-15NH-INS	3/8"x6" Insulated Nut Driver
0253-16NH-INS	7/16"x6" Insulated Nut Driver
0253-17NH-INS	1/2"x6" Insulated Nut Driver

### Pliers

- Exceeds the IEC 60900 and ASTM F1505 standards for insulated tools.
- Dual layer insulation provides added safety and protection against electric shock.

Available November 2010.



CAT. NO.	DESCRIPTION
0151-09-INS	9" Insulated Side-Cutting Pliers
0251-08A-INS	8" Insulated Angled Diagonal Cutting Pliers
0351-08-INS	8" Insulated Long-Nose Pliers
0451-10-INS	10" Insulated Pump Pliers

### High Leverage Cable Cutter

- High leverage provides greater cutting & gripping power.
- Independently tested to meet or exceed ASTM F1505-07.

Available January 2011.



CAT. NO.	DESCRIPTION
727-INS	Insulated High Leverage Cable Cutter

### Terminal Crimping Tool

- Independently tested to meet or exceed ASTM F1505-07.
- For crimping:
  - Insulated and non-insulated splices.
  - Insulated and non-insulated disconnects.
  - Wire joints.

Available January 2011.



CAT. NO.	DESCRIPTION
KP1022-INS	Insulated Terminal Crimping Tool



**MADE FOR THE TRADE!™**

# Ordering Information

CAT NUMBER	UPC NUMBER	DESCRIPTION	QTY
0151-09-INS	13456	PLIERS, SIDECUT, 9", INSULATED, MOLDED HANDLES	1
0153-01-INS	13439	SCREWDRIVER, INSULATED, 9 PIECE KIT	1
0153-11-INS	13443	SCREWDRIVER, INSULATED, CABINET TIP, 1/4"x4"	1
0153-15-INS	13447	SCREWDRIVER, INSULATED, CABINET TIP, 5/16"x6"	1
0153-17-INS	13448	SCREWDRIVER, INSULATED, CABINET TIP, 3/8"x10"	1
0153-21-INS	13444	SCREWDRIVER, INSULATED, CABINET TIP, 3/16"x4"	1
0153-22-INS	13445	SCREWDRIVER, INSULATED, CABINET TIP, 3/16"x6"	1
0153-23-INS	13446	SCREWDRIVER, INSULATED, CABINET TIP, 3/16"x8"	1
0153-31-INS	13440	SCREWDRIVER, INSULATED, #1x3"	1
0153-33-INS	13441	SCREWDRIVER, INSULATED, #2x4"	1
0153-35-INS	13442	SCREWDRIVER, INSULATED, #3x6"	1
0159-01-INS	10627	PLIER & SCREWDRIVER, INSULATED KIT, 7 PIECE KIT	1
0251-08A-INS	13454	PLIERS, DIAGONAL, 8", INSULATED, MOLDED HANDLES	1
0253-03NH-INS	13473	NUT DRIVERS, NH, INSULATED, 7 PIECE KIT	1
0253-11NH-INS	13474	NUT DRIVER, NH, INSULATED, 3/16X6"	1
0253-12NH-INS	13475	NUT DRIVER, NH, INSULATED, 1/4X6"	1
0253-13NH-INS	13476	NUT DRIVER, NH, INSULATED, 5/16X6"	1
0253-14NH-INS	13477	NUT DRIVER, NH, INSULATED, 11/32X6"	1
0253-15NH-INS	13478	NUT DRIVER, NH, INSULATED, 3/8X6"	1
0253-16NH-INS	13479	NUT DRIVER, NH, INSULATED, 7/16X6"	1
0253-17NH-INS	13480	NUT DRIVER, NH, INSULATED, 1/2X6"	1
0351-08-INS	13455	PLIERS, LONG NOSE, 8", INSULATED, MOLDED HANDLES	1
0353-32-INS	13450	SCREWDRIVER, INSULATED, SQ TIP, #1x6"	1
0353-33-INS	13451	SCREWDRIVER, INSULATED, SQ TIP, #2x6"	1
0451-10-INS	13453	PLIERS, PUMP, 10", INSULATED, MOLDED HANDLES	1
45206I	12680	CABLE CUTTER, RATCHET, INSULATED, MOLDED HANDLES	1
45207I	12681	CABLE CUTTER, RATCHET, INSULATED, MOLDED HANDLES	1
727-INS	31402	CABLE CUTTER, HIGH LEVERAGE, INSULATED, MOLDED HANDLES	1
KP1022-INS	31403	CRIMPING TOOL, TERMINAL, INSULATED, MOLDED HANDLES	1

## Also Available:



### 45206I-Insulated Ratchet Cable Cutter with Molded Handles

- Rated to 1000 V.
- Meets IEC 60900:2004 and ASTM F1505-07 standards.
- Two-speed ratchet mechanism to adjust for light or heavy cutting.
- Copper-600 kcmil
- Aluminum-600 kcmil



### 45207I-Insulated Ratchet Cable Cutter with Molded Handles

- Rated to 1000 V.
- Meets IEC 60900:2004 and ASTM F1505-07 standards.
- Two-speed ratchet mechanism to adjust for light or heavy cutting.
- Copper-750 kcmil
- Aluminum-1,000 kcmil



**GREENLEE®**

A Textron Company

[www.greenlee.com](http://www.greenlee.com) MA-5548 09/10

4455 Boeing Drive • Rockford, IL 61109-2988 • USA • 815-397-7070

©2010 Greenlee Textron Inc. • An ISO 9001 Company • Printed in USA

Greenlee Textron Inc. is a subsidiary of Textron Inc.