

Hex Pin Tamper Proof Machine Screws Stainless Steel - PC 6680



- Machine Screws
- Button or Flat Head*
- Hex Pin Tamper Proof
- 18-8 Stainless Steel
- Invincibox™ Up To 2"

Tamper resistant screws are designed to prevent vandalism and theft. Use proper bit or driver to remove (one way, hex pin, star pin or spanner). Choose from the type head style available: Button or Flat.

CAT NO	UPC	SIZE	INSERT BIT	DRIVER	STD	WT/STD	UNIT
T63212HB	11787	6-32	6-32 x 1/2	73TR4	HPD18	100	0.24# C
T63234HB	11788		6-32 x 3/4	73TR5	HPD18	100	0.32# C
T6321HB	11789		6-32 x 1	73TR5	HPD18	100	0.39# C
T632114HB	11790		6-32 x 1-1/4	73TR5	HPD18	100	0.46# C
T632112HB	11791		6-32 x 1-1/2	73TR5	HPD18	100	0.53# C
T83212HB	11792	8-32	8-32 x 1/2	73TR7	HPD532	100	0.39# C
T83234HB	11793		8-32 x 3/4	73TR7	HPD532	100	0.50# C
T8321HB	11794		8-32 x 1	73TR7	HPD532	100	0.62# C
T832114HB	11795		8-32 x 1-1/4	73TR7	HPD532	100	0.73# C
T832112HB	11796		8-32 x 1-1/2	73TR7	HPD532	100	0.83# C
T8322HB	11797		8-32 x 2	73TR7	HPD532	100	1.06# C
T102412HB	11798	10-24	10-24 x 1/2	73TR7	HPD532	100	0.54# C
T102434HB	11799		10-24 x 3/4	73TR7	HPD532	100	0.69# C
T10241HB	11800		10-24 x 1	73TR7	HPD532	100	0.83# C
T1024114HB	11801		10-24 x 1-1/4	73TR7	HPD532	100	0.97# C
T1024112HB	11802		10-24 x 1-1/2	73TR7	HPD532	100	1.11# C
T103212HB	11803	10-32	10-32 x 1/2	73TR7	HPD532	100	0.54# C
T103234HB	11804		10-32 x 3/4	73TR7	HPD532	100	0.69# C
T10321HB	11805		10-32 x 1	73TR7	HPD532	100	0.83# C
T1032114HB	11806		10-32 x 1-1/4	73TR7	HPD532	100	0.97# C
T1032112HB	11807		10-32 x 1-1/2	73TR7	HPD532	100	1.11# C
T1412HB	11808	1/4-20	1/4 x 1/2	73TR7	HPD532	100	1.11# C
T1434HB	11809		1/4 x 3/4	73TR7	HPD532	100	1.36# C
T141HB	11810		1/4 x 1	73TR7	HPD532	100	1.61# C
T14114HB	11811		1/4 x 1-1/4	73TR7	HPD532	100	1.87# C
T14112HB	11812		1/4 x 1-1/2	73TR7	HPD532	50	1.06# C
T142HB	11813		1/4 x 2	73TR7	HPD532	50	1.31# C

* Flat head available on special order, when ordering replace suffix 'B' with 'F'.

Hex Pin Insert Bits, Hand Driver & Magnetic Bit Holders - PC 6720, 6710, 6670

- Insert Bits Hex Pin
- Hand Driver Hex Pin
- Magnetic Hand Drivers
- Magnetic Bit Holders

Hex Pin Screws must be installed or removed using a matching drive which reduces the chances of unauthorized removal. Available in Hand Drivers and Insert Bits.

CAT NO	UPC	SCREW SIZE	DRIVER	DESCRIPTION	STD	MSTR	WT/STD	UNIT
Insert Bits - PC 6720								
73TR3	22733	4-5	3/32"	Hex Pin	1	5	0.01#	Ea
73TR5	22735	6	1/8"	Hex Pin	1	5	0.01#	Ea
73TR7	22737	8,10,12,14	5/32"	Hex Pin	1	5	0.01#	Ea
73TR8	22738	5/16"	3/16"	Hex Pin	1	5	0.01#	Ea
73TR9	22739	3/8"	7/32"	Hex Pin	1	5	0.01#	Ea
Hand Driver - PC 6670								
HPD18	81487	#6	1/8"	Hex Pin	1	10	0.02#	Ea
HPD532	81488	#8-#14	5/32"	Hex Pin	1	10	0.02#	Ea
Magnetic Bit Holder - PC 6710								
MBH	16948			1/4 x 3" Magnetic Bit Holder	1	10	0.11#	Ea
Magnetic Hand Driver - PC 6720								
MHD	16949			8" Magnetic Hand Driver	1	1	0.20#	Ea