



## Pre-Construction Bracket Kit

Cat. Nos.

AEPC8

AEPI6

AEPI8

PCC55

### Installation Instructions

**This package contains:**

ABS Backplate (2)

14.5" Aluminum Wings (4)

---

#### INSTALLATION

---


**CAUTION:** NOTE THAT THIS MANUAL IS WRITTEN WITH THE ASSUMPTION THAT THE INSTALLER POSSESSES SKILL IN THE PROPER USE OF HAND AND POWER TOOLS, AND IS FAMILIAR WITH THE ENVIRONMENT BEHIND THE SURFACE OF THE WALL OR CEILING WHERE THE SPEAKERS WILL BE INSTALLED.

**TO INSTALL:**

1. Select speaker mounting location. Route speaker cable from source to this location.  
**Note: We recommend the use of 16/2 (minimum) class 3 speaker wires.**
2. Attach wings to back plate of Pre-Construction Bracket (**refer to Figures 1A and 1B**). Only two wings are required for each back plate. Select the mounting arrangement that best suites your specific application.  
**Note: The wings are designed to be shortened as required.**
3. Attach the Pre-Construction Bracket in the desired location to the underside of framing members so that after drywall installation, the bracket and the wings are sandwiched between the drywall and the framing member (ensure "FRONT" is facing into the room) (**refer to Figures 1A and 1B**). If the mounting area is too congested to use both mounting wings you can drive screws through the back plate directly into the framing member.
4. Loop the speaker wire and attach it to the wire management loops on the back of the bracket.
5. After drywall installation install speakers in holes provided by drywall installer. Follow instructions included in speaker packaging.


**Figure 1A – Ceiling Mounting**

Use holes to mount bracket with screws to framing stud




**Figure 1B– In-Wall Mounting**

Use holes to mount bracket with screws to framing stud



**Figure 2 (Ceiling Mounting Depicted)**



**LIMITED 2 YEAR WARRANTY AND EXCLUSIONS**

Leviton warrants to the original consumer purchaser and not for the benefit of anyone else that this product at the time of its sale by Leviton is free of defects in materials and workmanship under normal and proper use for two years from the purchase date. Leviton's only obligation is to correct such defects by repair or replacement, at its option, if within such two year period the product is returned prepaid, with proof of purchase date, and a description of the problem to **Leviton Manufacturing Co., Inc., Att: Quality Assurance Department, 59-25 Little Neck Parkway, Little Neck, New York 11362-2591**. This warranty excludes and there is disclaimed liability for labor for removal of this product or reinstallation. This warranty is void if this product is installed improperly or in an improper environment, overloaded, misused, opened, abused, or altered in any manner, or is not used under normal operating conditions or not in accordance with any labels or instructions. **There are no other or implied warranties of any kind, including merchantability and fitness for a particular purpose**, but if any implied warranty is required by the applicable jurisdiction, the duration of any such implied warranty, including merchantability and fitness for a particular purpose, is limited to two years. **Leviton is not liable for incidental, indirect, special, or consequential damages, including without limitation, damage to, or loss of use of, any equipment, lost sales or profits or delay or failure to perform this warranty obligation.** The remedies provided herein are the exclusive remedies under this warranty, whether based on contract, tort or otherwise.

For Technical Assistance Call:  
1-800-824-3005 (U.S.A. Only)  
[www.leviton.com](http://www.leviton.com)