





58-C-1




58-C-4




58-C-5




58-C-6




58-C-7




58-C-11



58-C-16



58-C-30




NC501-SC


4" x 2 1/8" Utility Box Covers

Cat. No.	Dia. Hole (in.)	Description	Std. Ctn.
Raised 1/4"			
58-C-1	—	Blank	100
58-C-4	1 1/2"	For 4-wire twist-lock single flush receptacle	25
58-C-5	1 1/2"	For single receptacle	25
58-C-6	—	With 1/2" KO	25
58-C-7	—	For duplex flush receptacle	100
58-C-11	—	With 1/2" bushed hole	25
58-C-16	—	For single GFCI receptacle	25
58-C-30	—	For one toggle switch	100
NC501-SC	—	1/2" Romex Clamp Hit Lock Connector	500

Includes captivated Phillips head screws.



68361-1/2




68371-1/2


4 1/8" x 2 1/2" Utility Boxes

Cat. No.	Ea. Side Conduit	Knockouts		Std. Ctn.
		Ea. End Conduit	Bottom Conduit	
1 5/16" deep—with conduit KOs—17.0 cubic inch capacity				
68361-1/2*	3-1/2"	1-1/2"	2-1/2"	25
2 1/16" deep—with conduit KOs—18.8 cubic inch capacity				
68371-1/2*	3-1/2"	1-1/2"	2-1/2"	50

* Factory provided raised ground screw location.




68-C-1




68-C-5



68-C-6



68-C-7




68-C-30

4 1/8" x 2 1/2" Utility Box Covers Raised 3/16"

Cat. No.	Dia. Hole (in.)	Description	Std. Ctn.
68-C-1	—	Blank	25
68-C-5	1 1/2"	For single receptacle	25
68-C-6	—	With 1/2" KO	25
68-C-7	—	For duplex flush receptacle	25
68-C-30	—	For one toggle switch	25

Includes captivated Phillips head screws.



Steel City

T&B Catalog Number: 58 C 1 W/OBC
UPC Number: 78599103216
Description: 58 C 1 COVER WITHOUT BAR CODE LABEL

Status: Active

Packaging

T&B Sold in UM:	EACH
T&B Weight per UOM:	10.25 lbs. per 100

General Information

Country of Origin:	UNITED STATES
Harmonized Code:	7326908587

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com