

ANCHORING DEVICES



(STUD ANCHOR) WEDGE ANCHORS

STEEL ZINC CHROMATE AND STAINLESS STEEL

A powerful product when strength is needed, eliminates drilling oversized holes; exact hole depth not required. This spring stainless steel band, when locked, acts like a fish hook that digs into concrete. Then 3 to 4 turns of the nut expands the wedge.

STOCK NO.	UPC NO.	DRILL & BODY DIAMETER/LENGTH	THREAD LENGTH	MIN. DEPTH IN LENGTH	WT. PER PKG.	STD. PKG.	SUGGESTED TRADE LIST PRICE PER
STEEL							
JTS1134	80893	1/4 x 1 3/4	3/4	1 1/8	3.12	100	66.85/c
JTS1214	80894	1/4 x 2 1/4	3/4	1 1/8	3.68	100	75.40/c
JTS103	80895	1/4 x 3 1/4	3/4	1 1/8	4.63	100	85.65/c
JTS3218	80896	3/8 x 2 1/4	7/8	1 1/2	8.05	100	108.98/c
JTS3234	81165	3/8 x 2 3/4	1 1/8	1 1/2	9.30	100	114.80/c
JTS303	80898	3/8 x 3	1 1/8	1 1/2	9.92	100	117.83/c
JTS312	80899	3/8 x 3 3/4	1 1/8	1 1/2	11.70	100	134.40/c
JTS385	81614	3/8 x 5	1 1/8	1 1/2	7.45	50	154.70/c
JTS3612	81615	3/8 x 6 1/2	1 1/4	1 5/8	9.85	50	210.46/c
JTS4234	81166	1/2 x 2 3/4	1 1/4	2 1/4	9.10	50	184.60/c
JTS4334	81770	1/2 x 3 3/4	1 1/4	2 1/4	11.00	50	206.40/c
JTS4414	81622	1/2 x 4 1/4	1 1/4	2 1/4	6.12	25	214.40/c
JTS4512	81623	1/2 x 5 1/2	1 1/4	2 1/4	7.28	25	266.00/c
JTS407	81624	1/2 x 7	1 1/4	2 1/4	9.55	25	323.72/c
JTS5312	81630	5/8 x 3 1/2	2	2 3/4	9.22	25	343.52/c
JTS5412	81631	5/8 x 4 1/4	2	2 3/4	10.48	25	377.40/c
JTS505	81632	5/8 x 5	2	2 3/4	11.60	25	395.20/c
JTS506	81633	5/8 x 6	2	2 3/4	19.00	25	432.52/c
JTS6414	81640	3/4 x 4 1/4	2	3 1/4	12.09	20	516.65/c
JTS6434	81641	3/4 x 4 3/4	2	3 1/4	13.27	20	541.50/c
JTS6512	81642	3/4 x 5 1/2	2	3 1/4	14.75	20	606.75/c
JTS6614	81643	3/4 x 6 1/4	2	3 1/4	8.25	10	672.30/c
STAINLESS STEEL 18-8 TYPE							
JTS1134SS	80900	1/4 x 1 3/4	3/4	1 1/8	1.55	50	164.16/c
JTS1214SS	80901	1/4 x 2 1/4	3/4	1 1/8	1.85	50	188.08/c
JTS103SS	80902	1/4 x 3 1/4	3/4	1 1/8	2.50	50	214.80/c
JTS3218SS	80903	3/8 x 2 1/4	7/8	1 1/2	4.02	50	304.60/c
JTS303SS	80904	3/8 x 3	1 1/8	1 1/2	5.07	50	358.96/c
JTS312SS	80905	3/8 x 3 3/4	1 1/8	1 1/2	5.96	50	517.16/c
JTS385SS	95250	3/8 x 5	1 1/8	1 1/2	7.46	50	523.26/c NEW
JTS3612SS	95255	3/8 x 6 1/2	1 1/4	1 5/8	4.94	25	923.64/c NEW
JTS4234SS	82126	1/2 x 2 3/4	1 1/4	2 1/4	4.11	25	592.52/c
JTS4334SS	82127	1/2 x 3 3/4	1 1/4	2 1/4	5.77	25	686.60/c
JTS4512SS	95260	1/2 x 5 1/2	1 1/4	2 1/4	14.56	50	1,285.66/c NEW
NEW STAINLESS STEEL 316 TYPE							
JTS1034SS	90298	1/4 x 3 1/4	3/4	1 1/8	5.02	100	PLEASE CALL NEW
JTS3033SS	90305	3/8 x 3	1 1/8	1 1/2	5.08	50	PLEASE CALL NEW

LARGER DIAMETERS & LENGTHS AVAILABLE BY SPECIAL REQUEST.



Metallics Avanti Screw Manufacturing Facility in Bristol, CT



None of our competitors selling to the Electrical, Plumbing and HVAC Distribution trade can claim they manufacture screws.

There is no doubt: We know the American fastener market and are ahead of our competitors. Our Avanti Screw, Inc., fastener manufacturing facility in Bristol, CT, provides you an American fastener company who makes a portion of its product, sold through electrical, plumbing and HVAC distributors.