


ANCHORING DEVICES



(STUD ANCHOR)

WEDGE ANCHORS

STEEL ZINC CHROMATE AND STAINLESS STEEL

A powerful product when strength is needed. Eliminates drilling oversized holes; exact hole depth not required.

A spring stainless steel band, when locked, acts like a fish hook that digs into concrete.

Then 3 to 4 turns of the nut expands the wedge.

STOCK NO.	JAR UPC NO.	DIAMETER/ LENGTH	THREAD LENGTH	MIN. DEPTH IN LENGTH	WEIGHT	STD. PKG.	SUGGESTED TRADE LIST PRICE PER 100
STEEL							
JTS1134	80893	1/4 x 1 3/4	3/4	1 1/8	3.00	100	61.04/c
JTS1214	80894	1/4 x 2 1/4	3/4	1 1/8	4.00	100	68.86/c
JTS103	80895	1/4 x 3 1/4	3/4	1 1/8	5.11	100	78.23/c
JTS3218	80896	3/8 x 2 1/4	7/8	1 1/2	8.40	100	99.52/c
JTS3234	81165	3/8 x 2 3/4	1 1/8	1 1/2	10.33	100	104.86/c
JTS303	80898	3/8 x 3	1 1/8	1 1/2	11.00	100	107.61/c
JTS312	80899	3/8 x 3 3/4	1 1/8	1 1/2	13.33	100	122.76/c
JTS385	81614	3/8 x 5	1 1/8	1 1/2	8.09	50	141.32/c
JTS3612	81615	3/8 x 6 1/2	1 1/4	1 5/8	10.07	50	192.22/c
JTS4234	81166	1/2 x 2 3/4	1 1/4	2 1/4	9.66	50	168.62/c
JTS4334	81770	1/2 x 3 3/4	1 1/4	2 1/4	12.00	50	188.52/c
JTS4414	81622	1/2 x 4 1/4	1 1/4	2 1/4	7.00	25	195.76/c
JTS4512	81623	1/2 x 5 1/2	1 1/4	2 1/4	8.00	25	242.84/c
JTS407	81624	1/2 x 7	1 1/4	2 1/4	9.00	25	295.60/c
JTS5312	81630	5/8 x 3 1/2	2	2 3/4	9.00	25	313.72/c
JTS5412	81631	5/8 x 4 1/4	2	2 3/4	11.00	25	344.64/c
JTS505	81632	5/8 x 5	2	2 3/4	15.00	25	360.88/c
JTS506	81633	5/8 x 6	2	2 3/4	19.00	25	395.00/c
JTS6414	81640	3/4 x 4 1/4	2	3 1/4	12.00	20	471.70/c
JTS6434	81641	3/4 x 4 3/4	2	3 1/4	14.00	20	494.45/c
JTS6512	81642	3/4 x 5 1/2	2	3 1/4	16.00	20	554.15/c
JTS6614	81643	3/4 x 6 1/4	2	3 1/4	9.60	10	613.90/c
STAINLESS STEEL							
JTS1134SS	80900	1/4 x 1 3/4	3/4	1 1/8	3.00	50	139.46/c
JTS1214SS	80901	1/4 x 2 1/4	3/4	1 1/8	4.00	50	159.74/c
JTS103SS	80902	1/4 x 3 1/4	3/4	1 1/8	5.11	50	182.46/c
JTS3218SS	80903	3/8 x 2 1/4	7/8	1 1/2	8.40	50	258.28/c
JTS303SS	80904	3/8 x 3	1 1/8	1 1/2	11.00	50	304.92/c
JTS312SS	80905	3/8 x 3 3/4	1 1/8	1 1/2	13.33	50	439.33/c
JTS4234SS	82126	1/2 x 2 3/4	1 1/4	2 1/4	9.66	25	503.36/c
JTS4334SS	82127	1/2 x 3 3/4	1 1/4	2 1/4	12.00	25	625.10/c

LARGER DIAMETERS & LENGTHS AVAILABLE ON SPECIAL REQUEST.

TIE WIRE WEDGE ANCHOR

ZINC WITH STAINLESS STEEL CLIP



For various overhead suspension applications

STOCK NO.	JAR UPC NO.	DIAMETER/ LENGTH	MIN. DEPTH IN LENGTH	WEIGHT	STD. PKG.	SUGGESTED TRADE LIST PRICE 100
JTWA214	80906	1/4 x 2 3/16	1 3/8	2.46		99.16/c