



Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

COLORED LENSES



PRODUCT DESCRIPTION

2" diameter, for use with MR16 lamps and device holders. Available in Red (L112), Blue (L132), and Green (L133).

ORDERING INFORMATION

Model	Example
L112	L112
L112 Red	
L132 Blue	
L133 Green	

OPTICAL LENSES



PRODUCT DESCRIPTION

2" diameter, for use with MR16 lamps and device holders. Prismatic Spread (L110), Frost (L111), Diffuse (L113), UV Filter (L114), Linear Spread (L115).

ORDERING INFORMATION

Model	Example
L110	L110
L110 Prismatic	
L111 Frost	
L113 Diffuse	
L114 UV Filter	
L115 Linear Spread	

DICHROIC LENSES



PRODUCT DESCRIPTION

2" diameter, for use with MR16 lamps and device holders. Red (L120), Yellow (L122), Green (L123), Daylight (L124), Blue (L125), Cosmetic (L127).

ORDERING INFORMATION

Model	Example
L120	L120
L120 Red	
L122 Yellow	
L123 Green	
L124 Daylight	
L125 Blue	
L127 Cosmetic	

ACCESSORIES

900 TWO DEVICE HOLDER



PRODUCT DESCRIPTION

Mounts onto MR16 lamp and accepts all 2" Alfa lenses and #990-00 Louver. Can be used with #980, #992S and #992QJ Shades.

ORDERING INFORMATION

Model	Hardware Finish	Example
900	ALU	900-ALU
	ALU Aluminum	
	BLK Black	
	STN Satin Nickel	

9000 WIDE TWO DEVICE HOLDER




PRODUCT DESCRIPTION

Use only with #SP201 Cosmos Fixture. Accepts all 2" lenses and #990-00 Louver.

ORDERING INFORMATION

Model	Hardware Finish	Example
9000	BLK	9000-BLK
	BLK Black	
	CHR Chrome	
	STN Satin Nickel	
	WHT White	

990-00 LOUVER



PRODUCT DESCRIPTION

Egg-crate Louver for use with #900 and #9000 Holders.

ORDERING INFORMATION

Model	Hardware Finish	Example
990-00	ALU	990-00-ALU
	ALU Aluminum	
	BLK Black	



ACCESSORIES

990 LOUVER



PRODUCT DESCRIPTION

Egg-crate Louver with holder. Snaps on front of MR16 lamp. Can be used with #992 shades.

ORDERING INFORMATION

Model	Hardware Finish	Example
990	BLK-BLK	990-BLK-BLK
	BLK-BLK Black-Black	
	CHR-CHR Chrome-Chrome	
	CHR-BLK Chrome-Black	

991 COLORED RINGS




PRODUCT DESCRIPTION

High temperature silicone rings. Snaps on front of MR16 lamps.

ORDERING INFORMATION

Model	Hardware Finish	Example
991	BLK	991-BLK
	BLK Black	
	BLU Blue	
	RED Red	
	WHT White	
	YLW Yellow	

992QJ PERFORATED METAL SHADE




PRODUCT DESCRIPTION

Small Shade can be used with or without #900 Holder. Rests on back lip of MR16 lamp.

ORDERING INFORMATION

Model	Hardware Finish	Example
992QJ	BLK	992QJ-BLK
	BLK Black	
	BLU Blue	
	CHR Chrome	
	GRN Green	
	RED Red	
	WHT White	
	YLW Yellow	

992M MESH SHADE



PRODUCT DESCRIPTION

Small Mesh Shade can be used with or without #900 Holder. Rests on back lip of MR16 lamp.

ORDERING INFORMATION

Model	Hardware Finish	Example
992M	CHR	992M-CHR
	CHR Chrome	

992S SOLID SHADE




PRODUCT DESCRIPTION

Solid Shade can be used with or without #900 Holder. Rests on back lip of MR16 lamp.

ORDERING INFORMATION

Model	Hardware Finish	Example
992S	BLK	992S-BLK
	BLK Black	
	CHR Chrome	
	STN Satin Nickel	
	WHT White	

980 LARGE MESH SHADE



PRODUCT DESCRIPTION

Use with #900 Two-Device Holder. Works with all MR16 lamps.

ORDERING INFORMATION

Model	Hardware Finish	Example
980	BLK	980-BLK
	BLK Black	
	CHR Chrome	

**99600 CANOPY COVER
FOR JUNCTION BOX****PRODUCT DESCRIPTION**

Allows floating power feed to feed into ceiling junction box. Use with cable feeds, ARPF1, ARPF1-12, and CTL01.

ORDERING INFORMATION

Model	Hardware Finish	Example
99600	BLK	99600-BLK
	BLK Black	
	BRZ Bronze	
	CHR Chrome	
	STN Satin Nickel	
	WHT White	

**9999 TC FIXTURE
HARDWARE FITTING****PRODUCT DESCRIPTION**

Mounts to fixture arms and attaches to cable.

ORDERING INFORMATION

Model	Hardware Finish	Example
9999	CHR	9999-CHR
	CHR Chrome	

**ARRL-1M TRACK
INSULATOR****PRODUCT DESCRIPTION**

Use with MonoTrack. Clear flexible plastic. 40" L. Allows use of MonoTrack in municipalities with codes against open 12V systems.

ORDERING INFORMATION


Model	Example
ARRL-1M	ARRL-1M

**DEBUZZ 300 WATT
IN-LINE DEBUZZING
COIL****PRODUCT DESCRIPTION**

For use with magnetic transformers. Reduces noise associated with dimming. Fits in most standard fixture junction boxes. For use on the hot wire on the primary side of the transformer.

ORDERING INFORMATION

Model	Example
DEBUZZ	DEBUZZ

**MAEZ ANCHOR
MOUNTING KIT****PRODUCT DESCRIPTION**

For mounting MonoTrack and QJS track supports on soft surfaces like drywall.

ORDERING INFORMATION

Model	Hardware Finish	Example
MAEZ	BRZ	MAEZ-BRZ
	BRZ Bronze	
	CHR Chrome	
	STN Satin Nickel	

**G3 LAMP SHIELD
CAPSULE****PRODUCT DESCRIPTION**

Frost soda lime glass.

ORDERING INFORMATION

Model	Example
G3	G3

**MA1420 1/4-20
MOUNTING ADAPTER****PRODUCT DESCRIPTION**

Adapts MonoTrack and QJS track supports for mounting on 1/4-20 threaded rod.

ORDERING INFORMATION

Model	Hardware Finish	Example
MA1420	STN	MA1420-STN
	STN Satin Nickel	

**QJ2 QUICK JACK
CONNECTOR****PRODUCT DESCRIPTION**

For Pendant Cordsets. Max. 75W.

ORDERING INFORMATION

Model	Hardware Finish	Example
QJ2	BRZ	QJ2-BRZ
	BRZ Bronze	
	CHR Chrome	
	STN Satin Nickel	



ACCESSORIES

RSJ EXTENSION JOINER



PRODUCT DESCRIPTION

For adding together multiple RSE support extensions.

ORDERING INFORMATION

Model	Hardware Finish	Example
RSJ	CHR	RSJ-CHR
	CHR Chrome	
	NKL Nickel	

RE3 SWIVEL EXTENSION



PRODUCT DESCRIPTION

Accepts all Quick Jack fixtures. Max. 50W.

ORDERING INFORMATION

Model	Hardware Finish	Example
RE3	BLK	RE3-BLK
	BLK Black	
	CHR Chrome	
	STN Satin Nickel	
	WHT White	

RE100-RE500 EXTENSIONS



PRODUCT DESCRIPTION

Accepts all Quick Jack fixtures. Max. 50W.

ORDERING INFORMATION

Model	Hardware Finish	Example
RE100	BLK	RE100-BLK
RE100	BLK Black	
RE200	CHR Chrome	
RE300	STN Satin Nickel	
RE500	WHT White	

ARECAP END CAP (1 PAIR)



PRODUCT DESCRIPTION

For MonoTrack Track Section. Works for all MonoTrack finishes. Bronze matches Vintage Bronze finish MonoTrack.

ORDERING INFORMATION

Model	Hardware Finish	Example
ARECAP	BRZ	ARECAP-BRZ
	BRZ Bronze	
	CLR Clear	

SP120 10" RIGID QUICK JACK PENDANT STEM



PRODUCT DESCRIPTION

See compatible shades below; not included.

Max. 50W lamp: MR8, MR11, or MR16.

Compatible shades: G14, G16, G17, G18, G21, G24, G25, G26, G28, G28M, G33, G51, G52, G61, G62, G65, G67, G97

10" Long

ORDERING INFORMATION

Model	Hardware Finish	Example
SP120	STN	SP120-STN
	CHR Chrome	
	STN Satin Nickel	

SP338 CURLY QUICK JACK CORDSET



PRODUCT DESCRIPTION

Repositionable stem with threaded fitter. See compatible shades below; not included. Max. 50W lamp: JC, MR8, MR11, or MR16.

Compatible shades: G14, G16, G17, G18, G21, G24, G25, G26, G28, G28M, G33, G51, G52, G61, G62, G65, G67, G97

22" Long

ORDERING INFORMATION

Model	Hardware Finish	Example
SP338	STN	SP338-STN
	STN Satin Nickel	



ACCESSORIES

TLQJA QUICK JACK ADAPTER FOR JUNO TRAC 12® AND JUNO TRAC 12/25®



PRODUCT DESCRIPTION

Adapts any Quick Jack fixture or pendant for use on Trac 12® or Trac 12/25®. 50W max.

ORDERING INFORMATION

Model	Hardware Finish	Example
TLQJA	BL	TLQJA-BL
	BL Black	
	SL Silver	
	WH White	

TFQJA QUICK JACK ADAPTER FOR JUNO FLEX 12®



PRODUCT DESCRIPTION

Adapts any Quick Jack fixture or pendant for use on Flex 12®. 50W max.

ORDERING INFORMATION

Model	Hardware Finish	Example
TFQJA	SL	TFQJA-SL
	BL Black	
	SL Silver	
	WH White	

T537QJ 75W QJS TRANSFORMER ADAPTER FOR 120V TRACK - "BOAT STYLE"



PRODUCT DESCRIPTION

For use with all Juno one and two circuit Trac-Master® & Trac-Lite® systems. Integral electronic 12V transformer. For all QJS fixtures/pendants using the Quick Jack connector.

1 3/8" Height 1 1/2" Width 6" Length

ORDERING INFORMATION

Model	Hardware Finish	Example
T537QJ	BL	T537QJ-BL
	BL Black	
	SL Silver	
	WH White	

T538QJ 75W QJS TRANSFORMER ADAPTER FOR 120V TRACK - "BLOCK STYLE"



PRODUCT DESCRIPTION

Surface mounted. Power taps are on opposite sides of transformer case. Equipped with 25A secondary breaker. 120V input, 24V output.

1 3/8" Height 1 1/2" Width 6" Length

ORDERING INFORMATION

Model	Hardware Finish	Example
T538QJ	BL	T538QJ-BL
	BL Black	
	SL Silver	
	WH White	

CTT23 12V TRANSFORMER ADAPTER FOR 3 WIRE NON-JUNO LINE VOLTAGE TRACK



PRODUCT DESCRIPTION

For use with most non-Juno 3 wire track. Internal electronic 12V transformer. For all QJS fixtures/pendants using the Quick Jack Connector.

1 3/4" Height 1 5/8" Width 5 1/8" Length

ORDERING INFORMATION

Model	Hardware Finish	Example
CTT23	BLK	CTT23-BLK
	BLK Black	
	WHT White	