

ILLUMINA[®] BS101LED

INSTALLATION INSTRUCTION

INDUSTRIAL
VAPOR TIGHT



Beghelli Canada
3900 14th Avenue
Markham, Ontario L3R 4R3 Canada
P: (905) 948-9500
F: (905) 948-8673
www.BeghelliCanada.com




Beghelli USA
3250 Corporate Way
Miramar, Florida 33025 USA
P: 800 726 4316 / P: 954 442 6600
F: 954 442 6677
www.BeghelliUSA.com



Beghelli Mexico
Av El Marques No. 70, Interior 4
76246 Mpio. El Marquez
Queretano, QRO. Mexico
P: +52 442-221-6439 / F: +52 442-221-6215
www.BeghelliMexico.com

ILLUMINA[®] BS101LED INDUSTRIAL

- 50W MODEL
- 120V to 277V INPUT
- HT (AC ONLY)
- 4FT LENGTH



SERIES:	BS101LED
OPERATION:	HT (AC ONLY)
LED / COLORTEMP.:	WT35 (3500K) WT41 (4100K) WT57 (5700K)
INPUT:	120V TO 277V INPUT

IMPORTANT SAFEGUARDS

When using electrical equipment, basic safety precautions should always be followed including the following:

READ AND FOLLOW ALL SAFETY INSTRUCTIONS.

1. Do not let power cords touch hot surfaces.
2. Do not mount near gas or electric heaters.
3. Always mount equipment in a location that is not subjected to tampering by unauthorized personnel.
4. The use of accessory equipment not recommended by Beghelli, may cause an unsafe condition, and will void the warranty.
5. Do not use this equipment other than its intended purpose.
6. Servicing of this equipment should be performed by qualified service personnel.

SAVE THESE INSTRUCTIONS!

First make sure power is turned off!

1. Remove diffuser / lens.
2. Remove the reflector and mounting hardware bag.
3. Install conduit fitting.
4. Securely mount the fixture hardware provided. The fixture can be snapped onto the hardware as illustrated.
5. Prepare fixture for wiring / hang reflector from internal clips.
6. Connect AC supply and ground as labeled on the provided wire leads. CAP unused wire!

WARNING


No user serviceable parts. Refer service to a qualified service technician. Read instructions prior to installing and/or operating this device. Installation should be performed by a licensed electrician/installer in accordance with local codes.

CAUTION! Failure to insulate unused wire may result in a shock hazard or unsafe condition as well as equipment failure. Route wires and secure them in place.


7. Insert LED reflector.
8. Ensure the reflector lip engages the tab channels on the housing before snapping the reflector in position.
9. Install diffuser clips. Reposition the diffuser/lens and snap each of the eight (8) clips into place (a "clack" sound is made).
10. Turn on AC.

SAVE THESE INSTRUCTIONS!


1. REMOVE DIFFUSER / LENS




2. REMOVE LED REFLECTOR FROM HOUSING BE CAREFUL TO NOT TOUCH THE LEDs!




3. EXTRACT MOUNTING HARDWARE, INSTALL CONDUIT FITTING (included)



4. CONNECT TO POWER




5. INSTALL DIFFUSER CLIPS




- LABELED WIRE LEADS ARE PROVIDED FOR LINE / HOT, NEUTRAL / COMMON AND GROUND.
- LABELS WILL INDICATE THE RATED INPUT VOLTAGE: 120V TO 277V 60HZ.
- EXACT POWER SUPPLY AND WIRING CONFIGURATION MAY DIFFER FROM IMAGE ABOVE: **FOLLOW ACTUAL WIRE LABELS.**





6. INSTALL DIFFUSER/LENS



7. SECURE DIFFUSER/LENS WITH CLIPS




DIMENSIONS




INSTALL MOUNTING HARDWARE


SURFACE MOUNT




CHAIN HANG MOUNT (CH)




SINGLE PENDANT MOUNT (SPK)




WALL MOUNT




FIXTURE REMOVAL (IF NECESSARY)




AIRCRAFT CABLE MOUNTING



PENDANT MOUNTING




TRUNION MOUNT (TM)




NOTE: FOR BEAM MOUNTING
IN PARKING GARAGES.

PIVOT MOUNT (PM)



DIMMING WIRING DIAGRAM



DIMMING

0-10V WALL DIMMER (provided by others)

For dimmer switch wiring details, please refer
to dimmer manufacturer's installation guide.
(Dimmer not supplied by Beghelli)

NOTE: WIRE LOCATIONS WILL VARY. REFERENCE WIRES BY
COLOR NOT LOCATION



Beghelli Canada
3900 14th Avenue
Markham, Ontario L3R 4R3 Canada
P: (905) 948-9500
F: (905) 948-8673
www.BeghelliCanada.com



Beghelli USA
3250 Corporate Way
Miramar, Florida 33025 USA
P: 800 726 4316 / P: 954 442 6600
F: 954 442 6677
www.BeghelliUSA.com



Beghelli Mexico
Av El Marques No. 70, Interior 4
76246 Mpio. El Marquez
Queretano, QRO. Mexico
P: +52 442-221-6439 / F: +52 442-221-6215
www.BeghelliMexico.com