



# MUSTANG

TRADITIONAL SERIES

## Wall Lights

- USA Manufacturing at Import Prices
- Rugged traditional aluminum die-cast housing
- Lifespan: 100,000 hours
- Lens assembly is designed to provide high efficiency and to target the light where needed
- Installation: Fixture retains the same knock-out sizes and positions as previous models, reducing wiring costs

# Atlas

Lighting Products®



### 20 Watt LED Wall Light



#### AWT20

19 Input Watts  
110 LpW Efficacy  
2,133 Total Lumens  
4500K Color Temperature  
84 Color Rendering Index

### 30 Watt LED Wall Light



#### AWS30

30 Input Watts  
129 LpW Efficacy  
3,769 Total Lumens  
4500K Color Temperature  
83 Color Rendering Index

### 40-60-80 Watt LED Wall Light



#### AWM40

43 Input Watts  
133 LpW Efficacy  
5,805 Total Lumens  
4500K Color Temperature  
83 Color Rendering Index

#### AWM60

62 Input Watts  
128 LpW Efficacy  
7,871 Total Lumens  
4500K Color Temperature  
82 Color Rendering Index

#### AWM80

79 Input Watts  
129 LpW Efficacy  
10,120 Total Lumens  
4500K Color Temperature  
83 Color Rendering Index



# CHOOSING THE RIGHT LIGHT

		BETTER	BEST
	IMPORT	MUSTANG SERIES	Atlas Lighting Products®
Footcandles on Ground	Least	Less	More
Light Quality	Worst	Better	Best
Glare in Face	More	Less	Least
Offensive Light	More	Less	Least
Thermal Temps	Hottest Running	Cool Running	Coollest Running
Life	50,000	100,000	200,000+
Manufactured & Tested	MANUFACTURED IN CHINA	MANUFACTURED & TESTED IN USA*	MANUFACTURED & TESTED IN USA*
Availability	Stock Out Risk	Always in Stock	Always in Stock
Value	Lower	Higher	Highest

## IMPORT



**WHEN ALL YOU NEED IS LIGHT**  
Born in the USA - Priced at Import Levels



Mustang products break away from the pack of lower priced import style wall lights. By assembling these units in America, not only are US manufacturing jobs created and the economy strengthened, but it also enhances product quality, allows for faster response time to orders and eliminates stock outs due to container shipments.



**WHEN LIGHT QUALITY MATTERS**  
Best in Class Performance & Longevity



When light quality, performance and product life matters, the Atlas Classic wall lights remain the best choice in the market today. The positioning of the LEDs and the high efficiency reflector results in more light being directed to the desired location while eliminating glare, offensive and lost light.

\*The majority of Atlas Lighting Products are assembled in USA facilities by an American Workforce utilizing both Domestic and Foreign components