

30A, 125V, 2 Pole, 3 Wire Grounding, Receptacles and Plugs

IP20
SUITABILITY




30A 125V
NEMA 5-30R
UL CSA
2 HP



30A 125V
NEMA 5-30P
UL CSA
2 HP

Description	Cord Diameter	Catalog Number	
Receptacle, black RTP.	-	HBL9308	-
Receptacle, orange, isolated ground ^A .	-	IG9308	-
Plug, nylon, angle, 4-position.	.625"-1.187" (15.9-30.1)	-	HBL9309*



HBL9308

30A, 125V, 2 Pole, 3 Wire Grounding, Receptacles and Plugs

IP20
SUITABILITY




30A 125V
NEMA TT-30R
UL Listed
2 HP



30A 125V
NEMA TT-30P
UL Listed
2 HP

Description	Cord Diameter	Catalog Number	
Receptacle, black RTP. Travel Trailer use only.	-	HBLTT30R	-
Plug, nylon, angle. Travel Trailer use only.	.625"-1.187" (15.9-30.1)	-	HBLTT30P



IG9308

30A, 250V, 2 Pole, 3 Wire Grounding, Receptacles and Plugs

IP20
SUITABILITY




30A 250V
NEMA 6-30R
UL CSA
2 HP



30A 250V
NEMA 6-30P
UL CSA
2 HP

Description	Cord Diameter	Catalog Number	
Receptacle, black RTP.	-	HBL9330	-
Receptacle, orange, isolated ground ^A .	-	IG9330	-
Plug, nylon, angle, 4-position	.625"-1.187" (15.9-30.1)	-	HBL9331*



HBL9331

30A, 277V AC, 2 Pole, 3 Wire Grounding, Receptacles and Plugs

IP20
SUITABILITY




30A 277V AC
NEMA 7-30R
UL CSA
3 HP



30A 277V AC
NEMA 7-30P
UL CSA
3 HP

Description	Cord Diameter	Catalog Number	
Receptacle, black RTP.	-	HBL9315	-
Plug, nylon, angle, 4-position.	.625"-1.187" (15.9-30.1)	-	HBL9319*



HBL9315

30A, 125/250V, 3 Pole, 3 Wire Non-Grounding, Receptacles and Plugs

IP20
SUITABILITY




30A 125/250V
NEMA 10-30R
UL Listed
2(2) HP



30A 125/250V
NEMA 10-30P
UL Listed
2(2) HP

Description	Cord Diameter	Catalog Number	
Receptacle, black phenolic.	-	HBL9350	-
Receptacle, surface mount aluminum housing.	-	HBL9395	-
Plug, Insulgrip [®] , nylon.	.625"-1.00" (15.9-25.4)	-	HBL9337C
Plug, nylon, angle, 4-position.	.625"-1.187" (15.9-30.1)	-	HBL9333



HBL9350

Note: RTP is an abbreviation for reinforced thermoplastic polyester.
^ASee section N for additional information on isolated ground devices.
^{*}Not Fed. Spec. Listed.
 See page A-49 for accessories.

Dimensions in Inches (mm)