























Project: \_\_\_\_\_

Fixture Type: \_\_\_\_\_

Location: \_\_\_\_\_

Contact/Phone: \_\_\_\_\_

Trim Series	Dimensions	Aperture	Catalog No.	Housing/Lamp Compatibility
 <b>Gimbal Ring in Baffle</b>		5-3/4"	<b>224W-WH</b> - White Baffle, White Trim <b>224B-WH</b> - Black Baffle, White Trim	IC2: 75W PAR38, Medium Side Prong TC2/TC2R: 150W PAR38, Medium Side Prong APT2: 150W PAR38, 3 Side Prong
 <b>Cylinder Spotlight in Baffle</b>			<b>226W-WH</b> - White Cylinder Adjustable with White Baffle, White Trim <b>226B-WH</b> - Black Cylinder Adjustable with Black Baffle, White Trim	IC2/TC2/TC2R: 60W PAR16 IC22/IC22W/IC22S/IC22R: 60W PAR16 IC23/IC23W: 60W PAR16 APT2: 60W PAR16
 <b>R/PAR20 Regressed Eyeball</b>			<b>228-WH</b> - White Trim	IC2/TC2/TC2R: 50W PAR20, 50W R20 IC21/IC21R: 50W PAR20, 50W R20 IC22/IC22W/IC22S:/IC22R 50W PAR20, 50W R20 IC23/IC23W: 50W PAR20, 50W R20 APT2: 50W PAR20, 50W R20
 <b>R/PAR20 Regressed Eyeball in Baffle</b>			<b>248W-WH</b> - White Baffle, White Trim	IC2/TC2/TC2R: 50W PAR20, 50W R20 IC21/IC21R: 50W PAR20, 50W R20 IC22/IC22W/IC22S/IC22R: 50W PAR20, 50W R20 IC23/IC23W: 50W PAR20, 50W R20 APT2: 50W PAR20, 50W R20
 <b>PAR/BR30 Regressed Eyeball</b>			<b>229-ABZ</b> - Classic Aged Bronze Trim <b>229-BL</b> - Black Trim <b>229-SC</b> - Satin Chrome Trim <b>229-WH</b> - White Trim	IC2/TC2/TC2R: 75W PAR30L, 65W BR30 IC21/IC21R: 75W PAR30L, 65W BR30 IC22/IC22W/IC22S/IC22R: 75W PAR30L, 65W BR30 IC23/IC23W: 50W PAR20, 50W R20 APT2: 75W PAR30, 75W PAR30L, 65W BR30
 <b>PAR/BR30 Regressed Eyeball in Baffle</b>			<b>249W-WH</b> - White Baffle, White Trim <b>249B-WH</b> - Black Baffle, White Trim	IC2/TC2/TC2R: 75W PAR30L, 65W BR30 IC21/IC21R: 75W PAR30L, 65W BR30 IC22/IC22W/IC22S/IC22R: 75W PAR30L, 65W BR30 IC23/IC23W: 50W PAR20, 50W R20 APT2: 75W PAR30, 75W PAR30L, 65W BR30

Trim Series	Dimensions	Aperture	Catalog No.	Housing/Lamp Compatibility
 <p><b>PAR30 Adjustable Tapered Baffle</b></p>	 <p>7 5/8"</p>	5-3/4"	<b>264W-WH</b> - White Baffle, White Trim <b>264B-WH</b> - Black Baffle, White Trim	IC2/TC2/TC2R: 75W PAR30 IC22/IC22W/IC22S/IC22R: 50W PAR30 IC23/IC23W: 50W PAR30 APT2: 75W PAR30
 <p><b>PAR30 Adjustable Tapered Cone</b></p>	 <p>7 5/8"</p>	5-3/4"	<b>267B-WH</b> - Black Alzak®, White Trim <b>267C-WH</b> - Clear Alzak®, White Trim <b>267G-WH</b> - Gold Alzak®, White Trim <b>267HZ-WH</b> - Haze, White Trim <b>267WHZ-WH</b> - Wheat Haze, White Trim	IC2/TC2/TC2R: 75W PAR30 IC22/IC22W/IC22S/IC22R: 50W PAR30 IC23/IC23W: 50W PAR30 APT2: 75W PAR30
 <p><b>Low Voltage Pinhole with Baffle</b></p>	 <p>7 5/8"</p>	3-1/2"	<b>424B-WH</b> - Low Voltage Trim with Transformer, Black Baffle, White Trim	IC2: 35W MR16 TC2/TC2R: 50W MR16 APT2: 50W MR16
 <p><b>Low Voltage Cylinder Spotlight in Baffle</b></p>	 <p>7 5/8"</p>		<b>427W-WH</b> - Low Voltage Trim with Transformer, White Baffle, White Bezel, White Trim	IC2/TC2/TC2R: 50W MR16 APT2: 50W MR16
 <p><b>AVIO™ Square Gimbal Ring</b></p>	 <p>7 7/8"</p>		<b>XR30101BL</b> - Black Trim <b>XR30101GP</b> - Graphite Trim <b>XR30101SL</b> - Silver Trim <b>XR30101WH</b> - White Trim	IC2/TC2/TC2R: 75W PAR30 IC21/IC21R: 75W PAR30 IC22/IC22W/IC22S/IC22R: 75W PAR30