



Shown actual size: Skylark dimmer and 1-gang Claro wallplate in White (WH).

Product family features





- Rocker switch returns light to your favorite light level
- Slide up to brighten, down to dim (adjust light to suit any activity)
- **eco-dim®** model available
- 1000 W preset dimmers have voltage compensation which maintains stable light levels, despite line voltage variations
- 100% factory tested
- Coordinating Claro® and Stainless Steel wallplates only available separately
- Custom engraving available for wallplates, see pg. 155

Control types


 Single-pole (one location)

 3-way or 4-way (two or more locations)

Direct load type compatibility

-  Incandescent/halogen lighting
-  Magnetic low-voltage lighting
-  Electronic low-voltage lighting
-  Fluorescent lighting
-  LED lighting
-  Dimmable compact fluorescent
-  Ceiling fans
-  Ceiling fan/lights

Load type requiring load interface

 Neon/cold cathode lighting

Lighting load interfaces may be applicable for some additional load type, voltage and capacity combinations.

For additional information, see pg. 174.

Dimmers

Slide-to-off dimmers



- Slide up to on/brighten; down to dim/off

Dimmers with on/off switch and locator light



- Rocker switch turns on/off
- Slide up to brighten; down to dim
- Includes amber locator light

Dimmers with on/off switch



- Rocker switch turns on/off
- Slide up to brighten; down to dim
- **eco-dim®** model guarantees at least 15% energy savings compared to a standard switch

Fan and fan/light controls

Slide-to-off fan controls



- Slide up to on/increase speed; down to decrease/off
- 3-quiet fan speeds for increased comfort
- For use with only one ceiling paddle fan
- Quiet 3-speed designed to prevent motor hum
- Fully variable model also available

Slide-to-off fan controls with on/off light switch



Fan control (top)

- Slide up to on/increase fan speed; down to decrease fan speed/off
- 3-quiet fan speeds for increased comfort
- For use with only one ceiling paddle fan
- Quiet 3-speed designed to prevent motor hum

Switch (bottom)

- Rocker switch turns light on/off

Dual devices

Dual slide-to-off dimmers (two loads)



Dimmers (left/right)

- Slide up to on/brighten; down to dim/off

Dual slide-to-off fan control and dimmer



Fan control (left)


- Slide up to on/increase speed; down to decrease/off
- 3-quiet fan speeds for increased comfort
- Quiet 3-speed designed to prevent motor hum
- Fully variable available for use with multiple paddle or exhaust fans

Dimmer (right)

- Slide up to on/brighten; down to dim/off



Connections overview

Load connections*



Control types (for 2 or more locations)

Dim from one location, switch from the others



For more information on ballasts, visit www.lutron.com/ballasts.

For more information on LED drivers, visit www.lutron.com/LED.

***For illustration purposes only.** Consult model number pages for specific voltage and capacity information.

Fan control model numbers

Fan controls

Slide-to-off fan controls—quiet 3-speed

Single-pole	SFSQ-F- CC ³
120V 1.5A	

Single-pole	SFSQ-F-HO- CC ³
120V 2.0A	

For use with only one ceiling paddle fan.

SFSQ-F-HO- for use with Hunter Original Series.

Slide-to-off fan control—fully variable

Single-pole	SFS-5E- CC ³
120V 5A	

For use with multiple ceiling paddle fans or exhaust fans.

Fan/light controls

Fan control—quiet 3-speed and dimmer

Single-pole fan control	S2-LFSQ- CC ³
120V 1.5A (left)	

120V single-pole dimmer 300W (right)

For use with only one ceiling paddle fan.

Fan control—fully variable and dimmer

Single-pole fan control	S2-LF- CC ³
120V 2.5A (left)	

120V single-pole dimmer 300W (right)

For use with multiple ceiling paddle fans.

Fan control/light switch

Fan control—quiet 3-speed and switch

Single-pole fan control	SFSQ-LF- CC ³
120V 1.5A (top)	

120V single-pole switch 360W (bottom) (incandescent/halogen loads only)
--

CC³: Gloss color codes, see pg. 105
(Wallplates not included, order separately,
see pg. 160)

All models must be derated if ganged unless
otherwise noted, see pg. 170.

***Requires neutral wire connection.**