

OUTDOOR SENSORS

Gotcha!Plus™

THE BETTER SENSOR



Proven reliability with the features professionals trust.

Completely Assembled And Pre-Wired For Quick Installation

500 watt Switching Capacity

New!

Easy to read controls

6000 volt Surge Protection

Double Look Down Lens

Temperature Compensation

Protected Manual Override with Auto Reset

White or Black Finish

5 Year Warranty

Vandal resistant grills coming in 2008



Full color packaging has product features and specifications plus a comprehensive Installation Manual.




The Gotcha is RAB's "Better" sensor with 500 watt switching capacity. For RAB's "Best" sensors, see SUPER STEALTH & STEALTH with superb reliability, 1000 watt capacity, choice of 110°, 200° and 360° models and a 10 year warranty on pages 22-29.



STL200H page 28



STL360HBW page 24



Reliable, affordable sensor protection.

Specifications

- UL Listing:**
Suitable for wet locations
- Switching Capacity:**
5 amps, 500W Incandescent @ 120 volts
150W Fluorescent @ 120 volts
- Voltage:**
120 volts AC, 60Hz
- Power Consumption:**
1 watt
- Time Adjustment:**
10 seconds to 5 minutes
- Surge Protection:**
Withstands up to 6000 volts

- Photoelectric Control:**
Deactivates lights during daylight
- Detector Sensitivity:**
Adjustable from 100% to 50%
- Wall Switch Manual Override:**
Two flip logic prevents activation by momentary power outages.
Resets to auto after 6 hours or at dawn.
No extra wiring needed.
- Patents:**
RAB sensor and fixture designs are protected under U.S. and international intellectual property laws.

- Floodlights:**
Made of tough, corrosion-resistant polycarbonate. Molded silicone gasket.

Info Online 24/7

- www.rabweb.com
Wiring Diagrams
Installation Instructions
Product Specifications

Gotcha! Sensor

Gotcha Sensor with 110° view, surge protection, 500 watt switching capacity, auto test logic and manual override. New vandal resistant lens.

Finish: ● Black
○ White



Gotcha! Floodlight Kit

Gotcha Sensor with two weatherproof, corrosionproof floodlights, molded gaskets and corrosionproof universal cover plate. New vandal resistant lens. Lamps not supplied.

Finish: ● Black
○ White



Buzz Bulb


Screws into medium base outdoor floodlights. Emits a piercing 100 decibel screech when powered. When used along with a sensor, it becomes a powerful prowler deterrent.

Finish: ○ Ivory



Completely Assembled
And Pre-Wired
For Quick Installation

Detection Pattern



Catalog Numbers

Black	White
GT500	GT500W

Black	White
GT500R	GT500RW

Ivory
SA1BB



RAB Quality Inspectors check a production run. Customers consistently rate RAB #1 in Product Quality.

Dimensions

