

Please go to www.quoizel.com for product cleaning tips. Go to the **Care + Maintenance** selection.

Tools Required: Flathead screwdriver, Phillips screwdriver, pliers, wire cutters, wire strippers, electrical tape, safety glasses.

Light Source: (3) LED G9 4.5W Bulbs

Estimated Assembly Time: 20-30 minutes

Preparation: Identify and inspect all parts before beginning installation. Check package content list and diagrams below to be sure all parts are present. If any parts are missing or damaged, do not attempt to assemble, install, or operate the fixture. Contact customer service for replacement parts.

Please go to Quoizel.com to see the G9 LED bulb specifications provided with your fixture.


⚠ Warnings and Cautions

Turn off electricity at circuit breaker or main fuse box before installation. Consult a licensed electrician if in doubt.

These instructions are provided for your safety. It is very important you read them completely before installing the fixture. We strongly recommend that a licensed, professional electrician perform the installation.

Disconnect fixture from power source before replacing bulbs. Make sure bulbs are given sufficient time to cool before removal. Do not subject glass parts to any shock while in operation or shattering may result.

Package Contents



(Step 2 Continued)

Crossbar (AA) by unscrewing the Hex Nut (DD) and the Lock Washer (CC) and then screwing the Nipple (BB) in or out of the Crossbar (AA) until the correct length is achieved. Once the backplate of Fixture Body (D) is secure, remove the Lock Knob (EE) and Fixture Body (D) and proceed to step 3.

STEP 3 - Wire Connections

A. Use standard wire connectors (not included) to make all wire connections. Twist connectors until wires are tightly joined together. Wrap each connection with approved electrical tape and carefully stuff all the connected wires into the Outlet Box.





Figure 3

Hardware Contents



STEP 1 - Install Crossbar and Nipple

A. Secure the Crossbar (AA) to the Outlet Box with Outlet Box Screws. Tighten until snug.

* Pliers is required on this step.

B. Thread the Hex Nut (DD) onto one end of the Nipple (BB). Place the Lock Washer (CC) over the Hex Nut end of the Nipple (BB) and then thread the Nipple (BB) into the center lock hole of the Crossbar (AA). Using pliers, thread the Hex Nut (DD) against the Crossbar (AA) and hand tighten until snug.




Figure 1

STEP 4 - Install Fixture Body

A. Carefully tuck all wires into the outlet box and position the backplate of the Fixture Body (D) over the outlet box. Attach the backplate of the Fixture Body (D) over the Nipple (BB) and secure with the Lock Knob (EE). Hand tighten until snug.




Figure 4

STEP 2 - Fit Fixture Body to Crossbar Assembly

A. Fit the Fixture Body (D) over the Nipple (BB) on the Crossbar (AA) and secure with the Lock Knob (EE). The Backplate of the Fixture Body (D) should be snug against the wall and the Lock Knob (EE). If not, adjust the length of the Nipple (BB) on the




Figure 2

STEP 5 - Install Shade and Bulb

A. Place the Shade (C) and the Steel Collar (B) over the Socket as shown. By using the Socket Collar Tool (F), thread the Socket Collar (A) onto the Socket to secure them together. Hand tighten until snug.




Figure 5

Thank you for purchasing a Quoizel product.
Need assistance with parts or assembly? Call Quoizel customer service at 1-800-645-3184
or visit us on-line at www.quoizel.com

(Step 5 Continued)




B. Install either the G9 Xenon bulb as specified (not provided) or install the G9 LED bulbs (provided) if the fixture purchased is the LED model.

Note: This fixture is rated to use 60W maximum G9 Xenon bulbs. You may use a lower wattage G9 Xenon or if you purchased the LED model it is supplied with G9 LED bulbs.

Your fixture is now assembled and ready to use. Enjoy!

ERN8603IBLED

FINISH: IMPERIAL BRONZE



(3) 4.5W Maximum LED G9 Bulbs

NOTE: ALL DIMENSIONS ARE ROUNDED UP TO THE NEAREST 1/4"

NO.	PART NUMBER	REPLACEMENT PART DESCRIPTION	QTY.
1	I12442LED	BULB 4.5W LED G9 DIM WHITE	3
2	G2927SH	SHADE	3
3	M2296LK	LOCK KNOB	1

Thank you for purchasing a Quoizel product.
 Need assistance with parts or assembly? Call Quoizel customer service at 1-800-645-3184
 or visit us on-line at www.quoise.com