

# INSTALLATION INSTRUCTIONS

For Model 3306-84 (New. 11/18/2015)

## READ AND SAVE THESE INSTRUCTIONS

**WARNING! SHUT POWER OFF AT FUSE OR CIRCUIT BREAKER.**

**AVERTISSEMENT! COUPER LE COURANT AU NIVEAU DES FUSIBLES OU DU DISJONCTEUR.**

### PREPARING FOR INSTALLATION (Fig. 1)

1. Shut off the power at the fuse box or circuit breaker box and remove the old fixture from the ceiling, including the mounting hardware.
2. Carefully unpack your new fixture and lay out all the parts in a clear area. Take care not to lose any small parts necessary for installation.
3. Thread the nipple (E) into the crossbar (C) until snug. Note: The length of the nipple (E) into the crossbar (C) may be adjusted if necessary.
4. Use the lock washer (B) and hex nut (A) to secure the nipple (E) into the crossbar (C).
5. Take this crossbar (C) assembly and mount it to ceiling outlet box with mounting screws (D) (Size: #8-32N\*L0.5"). The side of crossbar marked with "GND" must face out.
6. Attach the nipple (J) by screwing in coupling (O) on the fixture body (T).
7. Secure one side of the metal bars (L) to the housing (K) by using short screws (M), secure the other side of metal bars (L) to fixture body (T) by using long screws (N).
8. Determine the desired hanging height and thread rods (F1, F2 and F3) to the nipple (I) of the housing (K). Then attach loop (H1) by screwing in to rod (F1). Note: remove the nipple if installing with one 6" rod only.
9. Attach the quick link (G) to loop (H1) and loop (H2) on the canopy (F), carefully feed the wire over loop (H1), quick link (G) and loop (H2).

### CONNECTING THE WIRES (Fig. 3)

10. At this point, connect the electrical wires as shown in figure 3, making sure that all wire connectors are secured. If your outlet has a ground wire (green or bare copper), connect the fixture's ground wire to it. Otherwise, connect the fixture's ground wire directly to the circular strap using the green screw provided.
11. Tuck the wire connectors neatly into the ceiling Junction Box and then raise the canopy all the way to the ceiling.
12. Place the canopy (F) over the nipple (E), and secure the canopy (F) against the ceiling using knurled cap (S).
13. Install light bulb(s) (not included) in accordance with the fixture's specification. **(DO NOT EXCEED THE MAXIMUM WATTAGE RATING!) (NE PAS DEPASSER LA PUISSANCE NOMINALE MAXIMALE!).**
14. Place glass shade (R) through the bulb (Q) and tighten the glass shade onto socket cup (P) by twisting it clockwise.

Your installation is now complete. Return power to the outlet box and test the fixture.

**Note:** Illustration (Fig. 1) on this manual is for installation purposes only. It may or may not be identical to the fixture purchased.

Fig. 1





Fig. 2



LA-2507E