



Assembly Instructions: 9942-7 SL (Aiyana)

WARNING- Porcelain flowers are extremely fragile. Please handle with care! Refer to instruction sheet for detailed handling, guidelines.

IMPORTANT:

- ALL INSTALLATION WORK SHOULD BE DONE BY ACCREDITED PROFESSIONAL.
- SHUT OFF POWER SUPPLY AT FUSE OR CIRCUIT BREAKER!
- USE ONLY THE SPECIFIED BULBS. DO NOT EXCEED THE MAXIMUM WATTAGE!

For Customer Service, contact the place of purchase to arrange for replacement parts.




PREPARING FOR INSTALLATION

Carefully remove all of the contents from the carton. See the important notes above. Shut off the power at the circuit breaker and completely remove the old fixture from the ceiling, including the old mounting strap.

From the parts bag remove the mounting strap assembly. One end of nipple (C) should be attached to mounting strap (A) with a washer and hex nuts in place. You may need to tighten the nuts that hold the screws in place. Pull the house wires through the center of mounting strap (A). Place mounting strap (A) over the junction box and secure in place with mounting screws (B) and a screw driver. Tighten the screws securely.

By measuring, determine the correct amount of cable wire needed for proper hanging height. To shorten the fixture, trim the wires to the desired length plus at least 8 to 10 inches. Put the wire through the hole in the side of the canopy.



CONNECTING THE WIRES

Have an assistant support the fixture's weight while completing the wiring. Cut away excess wire. Thread the fixture's wires through canopy loop and nipple. Attach the fixture's wires to the power supply wires from the junction box. Connect black to smooth/black/transparent (L) wire; white to ribbed/white/transparent (N) wire; ground to ground (green or copper). Twist the ends of the wire pairs together, and then twist on a wire connector. Make sure all twists are in the same direction. If there is no ground wire (green or copper) from the junction box, locate ground screw (E) on mounting strap (A) and wrap the fixture ground wire around the green ground screw (E). Use a screwdriver to secure ground screw (E) onto the mounting bracket/mounting strap. Tuck all wires neatly into the junction box.

FINISHING THE INSTALLATION

Push the canopy up to the ceiling so that nipple (C) protrudes through the hole in the canopy. Secure the canopy to the ceiling by threading decorative nut (D) onto the threads of nipple (C).

Note: Complete the following steps after the fixture has been hung. Install halogen bulbs, glass (S), glass (L1), and glass (L2) in accordance with the diagram above.

Bulb Note: Use a tissue or paper towel to hold the bulb and push down into the socket. Oils and dirt can cause the bulb life to shorten. Rubbing alcohol is recommended to clean the bulbs when needed.

Your installation is now complete. Turn on the power and test the fixture.

CLEANING TIPS

Treat the fixture gently! Regular cleaning will reduce the need for deep cleaning. For regular cleaning, turn off the light and wipe down the fixture with a clean lint-free cotton or microfiber cloth. Never spray cleaner directly onto the fixture.

