



While-In-Use-Weatherproof Covers

T&B Catalog Number:

CKMU
04226900465
Active

UPC Number:

Status:

Description:



Single Gang While-In-Use Universal Medium Horizontal Cover, 3-1/4 Inch Internal Depth, Silver, Aluminum, For use with Duplex, GFI, Single Receptacle, and Switch

Features

- Die-cast metal construction provides long-lasting durability
- Combination box or device-mounting design provides flexibility in installation.
- NEMA 3R rating ensures protection against falling rain, sleet and external ice formation when used with appropriate device boxes
- Clear UL and CSA markings speed approval by inspectors
- Wide range of cover depths and receptacle configurations accommodate almost every common plug and cord size when combined with included adapter plates
- Combination box or device mounting design provides flexibility in installation

Application

- Residential-Holiday and landscape lighting, wells and sump pumps, sprinkler systems, plug-in timers, garages and patios
- Commercial-Vending machines, car washes, outdoor signs, restaurant kitchens, greenhouses and nurseries, marinas, garages and lumberyards
- Industrial-Manufacturing areas, food processing, water treatment plants, security cameras, laboratories, wash down areas and loading docks
- Recreational-Pools and spas, parks, playgrounds, zoos, RV connections, athletic fields, ball parks, stadiums, outdoor stages, amphitheaters and golf courses
- Complies with National Electrical Code Article 406.8 (B) for unattended in use plugs in wet locations.
- Protects receptacles, switches and plugs for single gang and two gang configurations in dry and wet locations

General

Material	Die Cast Aluminum
Finish	Powder-coated
Color	Silver
Number of Gangs	One

Dimension Information

Inside Depth (inches) 3 1/4

Packaging

Package in Units 3
T&B Sold in UOM Each
T&B Weight Per UOM 0.82 lbs. Each

Application Support

T&B Sales Drawings wsd-000494
T&B Instruction Sheets ta04207-tb2
US Cutsheet PDF Catalog Link Available on Website
Product Brochure-Weatherproof While-in- Use Kits Available on Website

Notes

Less than .004 copper content

Certifications



File Nbr:
E 28688

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com