



Liquidtight Flexible Non-Metallic Conduit & Fittings

T&B Catalog Number:

15009-100

UPC Number:

03448123335

Status:

Active

Description:

1-1/4 Inch Gray Liquidtight Flexible Non-metallic Conduit, 100 Foot Coil

Features

| |
|---|
| Non-conductive and non-corrosive. |
| Lightweight for easy handling, transportation and installation. |
| Crush, abrasion and strain resistant. |
| Provides superior wire protection |
| Smooth interior ideal for pulling cable, no jagged edges. |
| Maintains internal I.D. even in tight radius bends. |
| Resistant to oil, acid, ozone, and alkaline. |
| UL listed for outdoor use and sunlight resistant. |
| UL listed for use as indicated in Article 356.2 of the NEC and Section 12-1300 of the Canadian Electrical Code, Part 1. |
| Suitable for use at conduit temperatures of 80 degree C dry, 60 degree C wet and 60 degree C oil resistant as required by Section 15-6 of ANSI/NFPA 79 and UL 1660. |
| Sequentially market footage |

Application

| |
|------------------------------|
| Control and Motor |
| Air conditioning and heating |
| Computer power distribution |
| Machine Tools |
| Console wiring |
| Transformer connections |
| Outdoor lighting |

General

| | |
|----------|--------------|
| Material | Non-Metallic |
| Color | Gray |

Dimension Information

| | |
|-----------------------|-------|
| Size (inches) | 1 1/4 |
| Average O.D. (inches) | 1.645 |
| Average I.D. (inches) | 1.385 |
| Nominal Size (inches) | 1 1/4 |
| Coil Length (feet) | 100 |

Packaging

| | |
|--------------------|--------------------|
| T&B Order Multiple | 100 |
| Package in Units | 100 |
| T&B Sold in UOM | Feet |
| T&B Weight Per UOM | 35.38 lbs. per 100 |

Application Support

Product Overview-Carflex Liquidtight Flex-Available on Website
ible Tubing

Notes

Available in black and gray.

Customer cut lengths available.

Certifications

RoHS Compliance

Yes

Certifications



File Nbr:

E95745

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com