

16" Round Flush Mount

LED 54075142

22 Watt 1700lms Round Flush Mount Specifications




The ETi 22 watt 1700 lumen LED round flush mount fixture offers exceptional performance for precision lighting applications, while reducing energy and maintenance cost when compared with conventional light sources. Lasting over 10 times longer, these flush mount fixtures are high quality replacements for incandescent flush mount fixtures and is available in 4000°K. They are UL listed for use in damp and dry locations. ENERGY STAR rated. Suitable for installations from – 4° F to 95° F.

KEY FEATURES & BENEFITS

- 22 Watts
- Multi-volt 100-277V
- 1700 lumen, 4000K CCT
- Non-dimmable
- UL damp location rated
- No UV, IR or mercury
- Warranty 5 years or 50,000 hours



FIXTURE DIMENSIONS



SKU# 54075142

Dimension A = 16.0"

Dimension B = 4.6"

This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. For FCC Part 15 user information, please see www.etiled.us/fcc15b

APPLICATION INFORMATION

Designed to be used anywhere a standard incandescent fixture is used. Typically used in bedrooms, hallways, kitchens, living rooms and recreational rooms. The LED round flush mount fixture carries a 3 year warranty.



855-384-7754 www.etiled.us

16" Round Flush Mount

LED 54075142

SPECIFICATION DATA

Project _____

Item Number _____


Prepared by _____ Date _____

ORDERING INFORMATION

Item Number	Description	Wattage	Input Voltage (VAC)	Average Rated Life ¹	Typical Lumens ²	CCT ³	CRI ⁴	Power Factor	R9	Duv	CBCP	Beam	Operating Frequency
54075142	LED22w FLUSH-MOUNT 840100-277 NDIM	22	100-277	50,000	1700	4000K	82	>.95	28.6	.0011	472	120	50/60Hz
¹ Hours lifetime with 70% lumen maintenance													
² Thermally stable typical lumens (±10%)													
³ Thermally stable CCT (±10%)													
⁴ Color rendering index/Ra													

SHIPPING INFORMATION

Item Number	Item UPC	Item Dimensions (H x L x W)	Item Weight (lbs)	Inner Pack Qty	Inner Carton Bar Code	Inner Carton Dimensions (H x L x W)	Inner Pack Weight (lbs)	Master Pack Qty	Master Carton Bar Code	Master Dimensions (H x L x W)	Master Pack Weight (lbs)
54075142	836607 008824	16" x 16" x 4.6"	2	N/A	N/A	N/A	N/A	4	50836607 008829	21.2" x 18.3" x 17.7"	15



**The Americas Headquarters
720 Corporate Woods PKWY
Vernon Hills, IL 60061**

855-384-7754 www.etiled.us