

BRUSHLESS
MOTORS



LONGER
MOTOR LIFE

MORE
POWER

MORE
RUN-TIME

LEARN MORE ▶



[Home](#) > ... > [Hammers](#) > [Rotary Hammers](#) > M18™ Cordless LITHIUM-ION 7/8" SDS Plus Rotary Hammer Kit


M18™ Cordless LITHIUM-ION 7/8" SDS Plus Rotary Hammer Kit 2605-22

0.0 **Be the first to Write a Review**

The M18™ Cordless LITHIUM-ION 7/8" SDS Plus Rotary Hammer delivers industry leading durability, with Up to 2X Longer Life than competitive cordless rotary hammers. By combining an exclusive motor design with maximized component size, the new tool delivers superior performance with up to 35% Harder Hitting. Powered by groundbreaking RED LITHIUM™ Battery Technology, the tool delivers 0-1,400 RPM, 0-4,800 BPM and up to 40% more run-time than the competition. Combined with 1.8 ft-lbs of impact energy, the 2605-22 also delivers up to 10% faster drilling.

Includes

- 2605-20 M18™ 7/8" Rotary Hammer
- (2) M18™ XC High Capacity RED LITHIUM™ Battery Packs
- Charger
- Side Handle
- Depth Rod
- Carrying Case



FEATURES

- Powerful Hammer Mechanism:** Delivers 1.8 ft-lbs of impact energy
- Mechanical Clutch:** Protects tool when bit binds up
- AVS - Anti Vibration System:** Delivers maximum comfort by minimizing vibration
- 3-Mode Operation:** Rotary hammer, hammer only and rotation only for maximum versatility
- Variable Position Chisel Stop:** Allows Steel to be adjusted for work in any orientation

SPECIFICATIONS

Voltage	18V
Impact Energy	1.8 ft-lbs
RPM	0-1,400
BPM	0-4,800
Max Capacity	7/8"
Thin Wall Core Bit Capacity	2-1/8"
Chipping	Yes
Clutch	Yes
Anti-Vibration	Yes - AVS™
Battery	RED LITHIUM™
No of Batteries Included	2
Length	11.75"
Tool Weight	7.2 lbs
Shipping Weight	16.90 lbs

RELATED ARTICLES

Milwaukee® Introduces
Cordless SDS Plus Rotary
Hammer with 2X Longer
Life

Milwaukee M18 Cordless
SDS+ Rotary Hammer
Preview

REVIEW SNAPSHOT® by PowerReviews

Not yet rated. Be the first to [Write a Review](#)


RELATED ITEMS



M18™ XC High Capacity
RED LITHIUM™ Battery



3/16" X 6" MX4 SDS+
Carbide Drill Bit



SDS Bit 1/4 in. x 4 in. x 6
in.

MORE RELATED ITEMS