



Ocal[®]

Conduit Fittings-PVC Coated
T&B Catalog Number:

UPC Number: CPL11/2-G
 70450836223
Status: Active
Description:

PVC Coated Conduit Coupling, 1-1/2 Inch/41 Metric Coupling Size, 1.91 Inch/48.41 Millimeters Minimum Length of Metal, 5.75 Inch/146.05 Millimeters Total Minimum Length Including Sleeve, Straight Threads, Pressure Sealing Sleeves, Blue Urethane Coating on Interior and Threads, Galvanized Rigid Steel, Gray

Features

- Nominal .002 in. (2 mil) blue urethane coating on interior and exterior
- Minimum .040 in. (40 mil) PVC coating is bonded to the exterior
- Straight threads (NPS)
- Molded ribs on outer coating for easy installation, up to and including 4 in.
- Pressure sealing sleeves protect your connection

General

Trade Size (inches)	1 1/2
Material	Steel
Finish	PVC Coated
Color	Dark Gray

Dimension Information

Pipe Size (inches)	1 1/2
Pipe Size (Metric Size Designator*)	41

Technical Information

Chemical Resistance Chart	Available on Website
---------------------------	----------------------

Specifications

Ocal Specification Guide-1995 Master Format-PDF	Available on Website
Ocal Specification Guide-1995 Master Format-DOC	Available on Website
Ocal Specification Guide-2004 Master Format-PDF	Available on Website
Ocal Specification Guide-2004 Master Format-DOC	Available on Website

Packaging

Package in Units	38
T&B Sold in UOM	Each
T&B Weight Per UOM	0.73 lbs. Each

Application Support

T&B Sales Drawings	wsd-000545
Ocal Specifications	Available on Website

Recommended Installation Procedures	Available on Website
Product Overview-Conduit Outlet Bodies	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

Notes

Metric size designator (ANSI C80. 1-1994)

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 46453

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com