



**Hazardous Location Fittings-PVC Coated**  
**T&B Catalog Number:**

**UPC Number:** EYS5-G  
 70450837426  
**Status:** Active  
**Description:**

PVC Double-Coated Conduit Sealing Fitting, EYS Series for Hazardous Locations, for Sealing in Vertical or Horizontal Position, Female Hub, Hub Size 1-1/2 Inch/41 Metric, Turning Radius 2.00 Inch/50.80 Millimeters, Ductile Iron, Gray

**Features**

All hubs have a minimum of five full threads, integral bushings to protect conductor insulation from damage, and large access openings for easier packing of sealing material.  
 Seals are approved to be used with Crouse Hinds® Sealing Compound and Fiber.

**Application**

Restricts the passage of gases, vapors and flames at atmospheric pressure and normal ambient temperatures

**General**

Trade Size (inches)	1 1/2
Material	Ductile Iron
Finish	PVC Coated
Color	Dark Gray

**Dimension Information**

Pipe Size (inches)	1 1/2
Pipe Size (Metric Size Designator*)	41
Hub Size (inches)	1 1/2
Dimension A (inches)	5.69
Dimension B (inches)	2.45
Dimension C (inches)	3.00
Turning Radius (inches)	3.62

**Technical Information**

Chemical Resistance Chart Available on Website

**Specifications**

Ocal Specification Guide-1995 Master Format-PDF	Available on Website
Ocal Specification Guide-1995 Master Format-DOC	Available on Website
Ocal Specification Guide-2004 Master Format-PDF	Available on Website
Ocal Specification Guide-2004 Master Format-DOC	Available on Website

**Packaging**

Package in Units	6
T&B Sold in UOM	Each
T&B Weight Per UOM	3.75 lbs. Each

### Application Support

Ocal Specifications	Available on Website
Recommended Installation Procedures	Available on Website
Product Overview-Conduit Outlet Bodies	Available on Website
NEMA Standards-RN 1	Available on Website
NEC 310-16 - Conductors for General Wiring	Available on Website
NEC Table 8	Available on Website

### Notes

Metric size designator (ANSI C80. 1-1994)  
Dimensions are of uncoated fittings

### Certifications

RoHS Compliance Yes

### Certifications



File Nbr:  
E 193396

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com